

# Specifications

Photo is representative



## Eaton XTCE065D00C

Eaton XT IEC contactor, 65A, 415 Vac, 50 Hz, 480 Vac, 60 Hz, 0NO-0NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE065D00C
<b>UPC</b>	782116486601
<b>PRODUCT LENGTH/DEPTH</b>	2.244 in
<b>PRODUCT HEIGHT</b>	5.945 in
<b>PRODUCT WIDTH</b>	4.567 in
<b>PRODUCT WEIGHT</b>	2.4 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	UL Listed CSA Certified IEC 60947 EN 60947
<b>CATALOG NOTES</b>	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

### Product specification

<b>AMPERAGE RATING</b>	65A
<b>HP RATING - MAX</b>	5, 10, (1/3PH @ 115 V)
<b>NUMBER OF POLES</b>	Three
<b>TYPE</b>	Full v contactor
<b>FREQUENCY RATING</b>	50-60
<b>FRAME SIZE</b>	55 mm
<b>TERMINALS</b>	Screw
<b>COIL</b>	412-4
<b>COIL VOLTAGE</b>	415-4
<b>CONTACT CONFIGURATION</b>	0 NO, 0 NC
<b>CONTINUOUS AMPERE RATING</b>	65 A
<b>SERIES</b>	XT IE
<b>OPERATION</b>	Non-r