

# Eaton XTCE065DS1A

Catalog Number: XTCE065DS1A

Eaton XT IEC contactor, 65A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/20, 25, 50, 60 hp(1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE065DS1A

### UPC

786685365121

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_D 3D Model Xchange](#)

[XTCE\\_D 3D Inventor](#)

[XTCE\\_D AutoCAD 2D Footprint](#)

[XTCE\\_D 2D Drawing Xchange](#)

[XTCE\\_D 2D PDF](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE065DS1A](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton XTCE065DS1A

Catalog Number: XTCE065DS1A

Eaton XT IEC contactor, 65A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/20, 25, 50, 60 hp(1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE065DS1A

### UPC

786685365121

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

65A

### HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

55 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

65 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

XTCE\_D 3D Model Xchange

XTCE\_D 3D Inventor

XTCE\_D AutoCAD 2D Footprint

XTCE\_D 2D Drawing Xchange

XTCE\_D 2D PDF

### Specifications and datasheets

Eaton Specification Sheet - XTCE065DS1A

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)