

defaultTaxonomyAttributeLabel

Amperage Rating

65A

HP rating - max

5, 10, 15/ 20, 25, 50, 60 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

55 mm

Terminals

Screw terminals

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

65 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_D 3D Model Xchange](#)

[XTCE_D 2D PDF](#)

[XTCE_D 2D Drawing Xchange](#)

[XTCE_D AutoCAD 2D Footprint](#)

[XTCE_D 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE065DS1A](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)