

Eaton XTCE080FS1A

Catalog Number: XTCE080FS1A

Eaton XT IEC contactor, 80 A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15, 15/25, 30, 60, 75 hp(1/3PH@115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

General specifications



Product Name

Eaton XT IEC contactor

Catalog Number

XTCE080FS1A

UPC

786685365138

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

1 lb

Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Amperage Rating

80A

HP rating - max

7.5, 15, 15/ 25, 30, 60, 75 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

90 mm

Terminals

Screw terminals

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

80 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

XTCE_F AutoCAD 2D Footprint

XTCE_F 3D Inventor

XTCE_F 2D Drawing Xchange

XTCE_F 2D PDF

XTCE_F 3D Model Xchange

Specifications and datasheets

Eaton Specification Sheet - XTCE080FS1A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)