

Eaton XTCE115GS1A

Catalog Number: XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



Photo is representative

General specifications

Product Name

Eaton XT IEC contactor

UPC

786685365152

Product Height

1 in

Product Weight

1 lb

Catalog Number

XTCE115GS1A

Product Length/Depth

1 in

Product Width

1 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

defaultTaxonomyAttributeLabel

Amperage Rating

115A

HP rating - max

10, 25, 25/ 40, 50, 100, 100 hp (1/3PH
@ 115,200,230/200,230,460,575 V)

Number Of Poles

Three-pole

Type

Full voltage non-reversing contactor

Frequency rating

50-60 Hz

Frame size

90 mm

Terminals

Screw terminals

Coil

110-120 Vac, 50/60 Hz

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Continuous ampere rating

115 A

Series

XT IEC

Operation

Non-reversing

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_G 2D Drawing Xchange](#)

[XTCE_G 3D Model Xchange](#)

[XTCE_G 2D PDF](#)

[XTCE_G 3D Inventor](#)

[XTCE_G AutoCAD 2D Footprint](#)

Specifications and datasheets

[Eaton Specification Sheet - XTCE115GS1A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)