

Specifications



Photo is representative

Eaton XTCE115GS1A

Eaton XT IEC contactor, 115A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, Frame G, 90 mm, 50-60 Hz, 10, 25, 25/40, 50, 100, 100 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE115GS1A
UPC	786685365152
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified UL Listed EN 60947 IEC 60947

Product specifications

AMPERAGE RATING	115A
HP RATING - MAX	10, 25, 25/ 40, 50, 100, 100 hp (1/3PH @115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	90 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	115 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

CATALOGS

[Motor Control and
Protection, IEC Contactors
and Starters, Volume 5,
Tab 1](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -
XTCE115GS1A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

