

# Eaton XTCE150GS1A

Catalog Number: XTCE150GS1A

Eaton XT IEC contactor, 150A, Side-mounted, 110V 50 Hz, 120 Vac, 60 Hz, 1NO-1NC, 150A, Frame G, 90 mm, 50-60 Hz, 10, 25, 30/40, 60, 125, 125 hp (1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



Photo is representative

## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

XTCE150GS1A

### UPC

786685365169

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

UL Listed

EN 60947

IEC 60947

## defaultTaxonomyAttributeLabel

### Amperage Rating

150A

### HP rating - max

10, 25, 30/ 40, 60, 125, 125 hp (1/3PH  
@ 115,200,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage non-reversing contactor

### Frequency rating

50-60 Hz

### Frame size

90 mm

### Terminals

Screw terminals

### Coil

110-120 Vac, 50/60 Hz

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

1 NO, 1 NC

### Continuous ampere rating

150 A

### Series

XT IEC

### Operation

Non-reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCE\\_G 2D PDF](#)

[XTCE\\_G 3D Model Xchange](#)

[XTCE\\_G AutoCAD 2D Footprint](#)

[XTCE\\_G 3D Inventor](#)

[XTCE\\_G 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCE150GS1A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)