

Specifications



Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR080F11A
UPC	782116356126
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	4.7 lb
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified IEC 60947 EN 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @ 115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - XTCR080F11A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

