

BURNDY Catalog Number YA26
UPC Number 7818105026000
Description 2/0 CU 1-HOLE LONG 3/8
Status Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle Straight
 Length (in) 2.77
 Tongue Type Standard
 Barrell Style Chamfered
 Bolt Hole Size (in) 0.39
 Barrel Type Long
 Thickness 0.12
 B Length (in) 1.50
 Pad Width (in) 0.83
 Strip Length 1-9/16

General

Number of Holes 1
 Product Description Copper Compression lug, 1 Hole w/o Inspection Window, 2/0 AWG, 3/8" Stud, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Copper Stranded (Range) 2/0 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 3/8
 Color Code Black
 Plated (Yes or No) Y
 Index Number 13
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number YA26
UPC Number 7818105026000
Description 2/0 CU 1-HOLE LONG 3/8
Status Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle Straight
 Length (in) 2.77
 Tongue Type Standard
 Barrell Style Chamfered
 Bolt Hole Size (in) 0.39
 Barrel Type Long
 Thickness 0.12
 B Length (in) 1.50
 Pad Width (in) 0.83
 Strip Length 1-9/16

General

Number of Holes 1
 Product Description Copper Compression lug, 1 Hole w/o Inspection Window, 2/0 AWG, 3/8" Stud, Long Barrel, Tin Plated

Conductor(s)

Flex (Class G) Size - Range N/A
 Flex (Class H) Size - Range N/A
 Flex (Class I) Size - Range N/A
 Copper Solid Size (Range) N/A
 DLO Size (Range) N/A
 Copper Stranded (Range) 2/0 AWG

Physical

Type of Plating Tin - Electro Plated
 Bolt Hole Size 3/8
 Color Code Black
 Plated (Yes or No) Y
 Index Number 13
 Product Material Copper

Approvals / Certifications

UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175