



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA2CA9  
 7818100367300  
 2 STR AL 2-HOLE 1/2  
 Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle Straight  
 Strip Length 1-1/8  
 Length (in) 4.73  
 Tongue Type Standard  
 Bolt Hole Size (in) 0.52  
 Thickness 0.16  
 B Length (in) 1.12  
 Pad Width (in) 0.88  
 E - in 1.75

**General**

Number of Holes 2  
 Product Description Aluminum Compression Lug, 2 Hole w/o Inspection Window, 2 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated

**Conductor(s)**

Aluminum Size (Range) 2 AWG  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 2 AWG

**Physical**

Type of Plating Tin - Electro Plated  
 Bolt Hole Size 1/2  
 Color Code Pink  
 Plated (Yes or No) Y  
 Index Number 348  
 Product Material Aluminum

**Approvals / Certifications**

UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL468A-468B

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175