



BURNDY Catalog Number
UPC Number
Description
Status

YAV25LTC14FX
 7818100227022
 1/0FLEX 1/4STUD
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 Strip Length

Dimensional

Straight
 1.75
 Standard
 Chamfered
 0.27
 Standard
 0.12
 0.69
 0.83
 11/16

Number of Holes
 Product Description

General

1
 Copper Compression Lug, 1 Hole
 w/ Inspection Window, 1/0 Flex,
 1/4" Stud, Short Barrel, Tin Plated

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

Conductor(s)

1/0 AWG
 1/0 AWG
 1/0 AWG
 N/A
 1/0 (275/#24) DLO
 1/0

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin
 1/4
 Pink
 Y
 12
 Copper

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS

Approvals / Certifications

Y
 Y
 Compliant
 N
 N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175