



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YGHA292N  
7818102203822  
CU 250 HVY DUTY GRD TERM  
Active

**Web Use**  
BURNDY Product Line

Thickness  
B Length (in)  
D - in  
Pad Width (in)  
Stud Size (Fraction)  
E - in

**Dimensional**

0.34  
1.18  
3.00  
1.28  
1/2  
1.75

**General**

Product Description

Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 250 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel

**Conductor(s)**

Copper Solid Size (Range)  
Copper Stranded (Range)

N/A  
250 kcmil

**Physical**

Type of Plating  
Connector Type  
Plated (Yes or No)  
Index Number

Unplated  
Terminal  
N  
18

**Approvals / Certifications**

Rated for Direct Burial  
UL Listed  
CSA Certified  
ROHS Compatible  
UL Recognized  
CULUS  
Industry Standards

Y  
Y  
Y  
Compliant  
N  
N  
UL468A-468B,UL467,IEEE 837

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
Monday - Friday  
Phone: 800-346-4175