



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS8CLBOX #8 STR Cu Butt Splice *Burndy LLC*

Catalog Number	YS8CLBOX
Manufacturer	Burndy LLC
Description	8 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Red Color Code, 49 Die Index.
Weight per unit	0.0110 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	49
Material	Copper
pallet quantity	60000
Voltage Rating	35

Material, Color, and Finish

Color Code	RED
Finish	Tin-Plated

Descriptions

Description	#8 STR CU BUTT SPLICE
extra long description	BUR YS8CLBOX 8 STR. CU. BUTT SPLICE
Long Description	8 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, RED Color Code, 49 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Conductor Type: Commercial Stranded Copper, Die Index: 49 Element A, Color Code: Red, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MRTC, Y2MR Tool, (1), MD7-34R Tool, W8CVT Die, (1), MD6, OUR840 Tool, X8CRT Die, (1), Y35, Y39, Y750, Y46 Tool, U8CRT Die, (1), Dieless To

Manufacturer Information

Brand	BURNDY
GTIN	00781810022092
Manufacturers Part Number	YS8CLBOX
UPC	781810022092

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Weight Per each	0.011

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B