



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ZOM66FB6 1-18W 30K 66" FB Zoom Fan

Craftmade International I

Catalog Number	ZOM66FB6
Manufacturer	Craftmade International I
Description	The Zoom 66" Damp-Rated Indoor/Outdoor Ceiling Fan Is The Ideal Combination Of Design and Engineered Performance. The Zoom By Craftmade Features Custom Abs Blades Powered By An Energy-Saving, Six-Speed Reversible DC Motor, Two Controls For Wall or Handheld Use, Integrated Dimmable Led Light and Dual-Mount Capability For Flat or Sloped Ceiling Installation.
Weight per unit	19.8 (lbs/each)
Product Category	20231010102840

Features

bulb type	Disk
Category	Fans
Safety Rating	Damp
Voltage	120.00

Material, Color, and Finish

Finish	Black
Style	Contemporary Modern

Descriptions

Description	1-18W 30K 66" FB ZOOM FAN
Long Description	The Zoom 66" damp-rated indoor/outdoor ceiling fan is the ideal combination of design and engineered performance. The Zoom by Craftmade features custom ABS blades powered by an energy-saving, six-speed reversible DC motor, two controls for wall or handheld use, integrated dimmable LED light and dual-mount capability for flat or sloped ceiling installation.
Product Type	66"Ceiling Fan

Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881221539
Manufacturers Part Number	ZOM66FB6
UPC	647881221539

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Damp Location

Packaging

Carton	1
Weight Per each	19.84