



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ZOM66FB6 1-18W 30K 66" FB Zoom Fan

*Craftmade International I*

Catalog Number	ZOM66FB6
Manufacturer	Craftmade International I
Description	The Zoom 66" Damp-Rated Indoor/Outdoor Ceiling Fan Is The Ideal Combination Of Design and Engineered Performance. The Zoom By Craftmade Features Custom Abs Blades Powered By An Energy-Saving, Six-Speed Reversible DC Motor, Two Controls For Wall or Handheld Use, Integrated Dimmable Led Light and Dual-Mount Capability For Flat or Sloped Ceiling Installation.
Weight per unit	19.8 (lbs/each)
Product Category	20231010102840

### Features

bulb type	Disk
Category	Fans
Safety Rating	Damp
Voltage	120.00

### Material, Color, and Finish

Finish	Black
Style	Contemporary Modern

### Descriptions

Description	1-18W 30K 66" FB ZOOM FAN
Long Description	The Zoom 66" damp-rated indoor/outdoor ceiling fan is the ideal combination of design and engineered performance. The Zoom by Craftmade features custom ABS blades powered by an energy-saving, six-speed reversible DC motor, two controls for wall or handheld use, integrated dimmable LED light and dual-mount capability for flat or sloped ceiling installation.
Product Type	66"Ceiling Fan

### Manufacturer Information

Brand	CRAFTMADE
GTIN	00647881221539
Manufacturers Part Number	ZOM66FB6
UPC	647881221539

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Damp Location

### Packaging

Carton	1
Weight Per each	19.84