
ROUND CEILING NON-METALLIC CABLE BOXES

SADDLE BOX® 4 in. Round Ceiling Fan and Fixture Box - For Nonmetallic Sheathed Cable or Conduit SADDLE BOX®, 12.5 Cu. in.

A81.1



Catalog #: 7120-1

APPLICATIONS

RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires Provide excellent protection for wiring system or devices

PRODUCT FEATURES

RACO® Nonmetallic cable boxes provide the installer with a cost alternative that is lightweight and easy to install

Self-clamping wire entry clamps
Round fixture boxes offer an optional front-mounted grounding screw

For use wherever fans (Cat. #7120, 7120-1, 7120VB only) or lighting canopies are to be installed

N/A

UL LISTED

File E 195963

COMPLIANCES

Boxes are listed for Applications (Electrical Codes), UL Green Book

Boxes are listed for mechanical properties, including the 2-hour Fire Rating, (building codes) UL Orange Book Federal Manufacturer's number 28488

FIRE RESISTANCE

2-hour fire rating, UL Orange Book

US PATENTS

5234119

OTHER PATENTS

Mexico 179,825

GENERAL PRODUCT INFORMATION

Wiring System: Nonmetallic Sheathed Cable

Color Black Country of Origin: USA

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.: 70 Fixture (Static) Lbs.: 210

CONFIGURATION

Cable Clamps: Side Knockout(s): Bottom Knockouts(s):

DRAWING DIMENSIONS

2-5/8 in. Dimension A:

PRODUCT MEASUREMENTS

2-5/8 in. Depth: Cubic Inches (cm3): 12.5 (204.8) Wt. Ea. (Lbs.): Product Length (in.): 0.258 2.60 3.90 4.00 Product Width (in.): Product Height (in.):

PACKAGING

Minimum Pack Qty.: 24 Std. Pkg.: 24 Product UPC-A Labeled: Yes Weight (Lbs. Per/C): 25.80

 Ship Carton Length (in.):
 15.50

 Ship Carton Width (in.):
 6.25

 Ship Carton Height (in.):
 8.25

 Ctn Weight (Lbs.):
 6.19

 Pallet Qty:
 2520

 UPC Number:
 050169712016

 I2of5:
 50050169712011