

# INVISILED® ACCESSORIES

Indoor mounting accessories

# WAC LIGHTING

Responsible Lighting®

|   |   |        |                     |  |   |  |
|---|---|--------|---------------------|--|---|--|
|     |    | 5 feet | <b>LED-T-CH</b>     | Aluminum Channel                         | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH-EC</b>  | End caps for Aluminum Channel            |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|     |    | 5 feet | <b>LED-T-CH1</b>    | Deep Aluminum Channel                    | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH1-EC</b> | End caps for Deep Aluminum Channel       |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|     |    | 5 feet | <b>LED-T-CH2</b>    | 45° Angled Aluminum Channel              | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH2-EC</b> | End caps for 45° Angled Aluminum Channel |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |  | 2 pcs  | <b>LED-T-CL3-PT</b> | 2 Adjustable Clips                       | Used to mount any aluminum channel<br>Includes 2 pieces, 4 screws                                       | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 2 pcs  | <b>LED-T-CL2-PT</b> | 2 Adjustable Clips                       | Used to mount any aluminum channel<br>Adjusts 50° from center either way<br>Includes 2 pieces, 4 screws | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |  | 3 feet | <b>LED-T-RC</b>     | Retrofit Channel                         | Can be bent to create fixed curves  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 10 pcs | <b>LED-T-CL</b>     | Clip                                     | Holds an indoor tape from the underside<br>Includes 10 pieces, 10 screws                                | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 10 pcs | <b>LED-T-CL1</b>    | Curve Clip                               | Runs over an indoor tape to secure the angled tape<br>Includes 10 pieces, 10 screws                     | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |

## LED-T-\_\_\_\_\_

Example: **LED-T-CL3-PT**

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050





Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISIBLE® ACCESSORIES

Outdoor mounting accessories

# WAC LIGHTING

Responsible Lighting®

|   |        |                     |                 |  |                                |
|---|--------|---------------------|-----------------|--|--------------------------------|
|  | 5 feet | <b>LED-TO24-CH5</b> | Clear Channel   | Rigid, non-flexible channel for mounting to a straight, solid surface.   | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C1</b>  | Mounting Clip 1 | For installation on non-flat surfaces where there is no edge contact. 2 clips per ft are recommended for straight runs.    | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C2</b>  | Mounting Clip 2 | For installation on non-flat surfaces, allows for contact on one edge. 2 clips per ft are recommended for straight runs.   | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C3</b>  | Mounting Clip 3 | For installation on non-flat surfaces, allows for contact on both edges. 2 clips per ft are recommended for straight runs. | Pro Outdoor<br>Palette Outdoor |

## LED-TO24-\_\_\_\_\_

Example: **LED-TO24-C2**

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES

Indoor non-color changing electronic accessories

# WAC LIGHTING

Responsible Lighting®

| Type  | Model  | Input            | Output                     | Max Run            | Dim        | Compatibility   |
|---|--|------------------|----------------------------|--------------------|------------|---|
|  <p>Remote<br/><i>Includes a 6 foot lead wire</i></p>  | <b>EN-2460-RB2-T</b><br><b>EN-24100-RB2-T</b>  | 120VAC<br>120VAC | 24VAC / 60W<br>24VAC / 96W | 30 feet<br>40 feet | ELV<br>ELV | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Plug-in<br/><i>Includes a 6 foot lead wire</i></p>   | <b>EN-2460-P-AR-T</b><br><b>EN-24100-P-AR-T</b>  | 120VAC<br>120VAC | 24VAC / 60W<br>24VAC / 96W | 30 feet<br>40 feet | ELV<br>ELV | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Remote 277V<br/><i>Includes a 6 foot lead wire</i></p>   | <b>EN-24100-277-RB2-T</b>  | 277VAC           | 24VDC / 96W                | 40 feet            | 0-10V      | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Touch Panel and Motion Sensor<br/><i>Includes a Touch Panel, an Occupancy Sensor, and a Controller</i><br/><i>AC/DC input at 12V(60W Max) or 24V(96W Max)</i><br/><i>Connect on secondary side of driver/transformer</i></p> | <b>CT-6A-R2</b>  |                  |                            |                    |            | Pro, Pro2, Pro3,<br>LITE, Classic<br>Daylight to Sunset,<br>Palette |
|  <p>In Wall Rated Extension Cable<br/><i>Extends distance between a hard wired power supply or a wiring box to a tape section.</i></p>  | <b>LED-TC-WEXT-144</b><br><b>LED-TC-WEXT-144-WT</b><br><b>LED-TC-WEXT-240</b><br><b>LED-TC-WEXT-240-WT</b> |                  |                            |                    |            | Black 12 ft<br>White 12 ft<br>Black 20 ft<br>White 20 ft            |
|  <p>In Wall Rated Joiner Cable<br/><i>Connects tape sections. 2 female ends. 1 male to male connector included</i></p>   | <b>LED-TC-WIC-144</b><br><b>LED-TC-WIC-144-WT</b><br><b>LED-TC-WIC-240</b><br><b>LED-TC-WIC-240-WT</b>     |                  |                            |                    |            | Black 12 ft<br>White 12 ft<br>Black 20 ft<br>White 20 ft            |
|  <p>Lead Wire<br/><i>Alternative lengths for plug-in power supplies</i></p>  | <b>LED-TC-P-2</b><br><b>LED-TC-P-2-WT</b><br><b>LED-TC-P-12</b><br><b>LED-TC-P-12-WT</b>                   |                  |                            |                    |            | Black 2 ft<br>White 2 ft<br>Black 12 ft<br>White 12 ft              |
|  <p>Extension Cable<br/><i>Extends distance between a hard wired power supply or a wiring box to a tape section</i></p>  | <b>LED-TC-EXT-144</b><br><b>LED-TC-EXT-144-WT</b>  |                  |                            |                    |            | Black 12 ft<br>White 12 ft  |
|  <p>Low Voltage Wiring Box With Feed<br/><i>Neatly houses connectos for up to two wires with 12" female feed</i></p>   | <b>LED-TC-B-2</b><br><b>LED-TC-B-2-WT</b>  |                  |                            |                    |            | Black L: 1½ in<br>White W: ¾ in<br>H: 7⁄8 in                        |
|  <p>Low Voltage Wiring Box<br/><i>Neatly houses connections for up to two wires</i></p>  | <b>LED-T-B</b>   |                  |                            |                    |            | L: 1½ in<br>W: ¾ in<br>H: 7⁄8 in                                    |
|  <p>Wiring Box With Switch<br/><i>Use when spanning a large gap in a system layout without leaving exposed wiring. Optional switch included</i></p>  | <b>TB-S</b>  |                  |                            |                    |            | L: 6¼ in<br>W: 1½ in<br>H: 1¼ in                                    |

Compatible with Pro, Pro2, Pro3, LITE, Classic

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050



Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISIBLE® ACCESSORIES

Indoor non-color changing electronic accessories

# WAC LIGHTING


Responsible Lighting®

|   |                       |       |        |
|---|-----------------------|-------|--------|
|  <p>Joiner Cable</p> <p>Connects tape sections</p> | <b>LED-TC-IC2</b>     | Black | 2 in   |
|   | <b>LED-TC-IC2-WT</b>  | White | 2 in   |
|   | <b>LED-TC-IC6</b>     | Black | 6 in   |
|   | <b>LED-TC-IC6-WT</b>  | White | 6 in   |
|   | <b>LED-TC-IC12</b>    | Black | 12 in  |
|   | <b>LED-TC-IC12-WT</b> | White | 12 in  |
|   | <b>LED-TC-IC36</b>    | Black | 36 in  |
|   | <b>LED-TC-IC36-WT</b> | White | 36 in  |
|   | <b>LED-TC-IC72</b>    | Black | 72 in  |
|   | <b>LED-TC-IC72-WT</b> | White | 72 in  |
|  <p>Male to male connector</p>                     | <b>LED-TC-MM</b>      | Black | 50 Qty |

Compatible with Pro, Pro2, Pro3, LITE, Classic, Palette  
Change directionality of tape runs and reuse cut ends of tape.

|  |   |                |
|--|---|----------------|
|  <p>3-Way "Y" Connector</p> <p>Connects tape sections</p> | <b>LED-TC-Y</b><br><b>LED-TC-Y-WT</b>   | Black<br>White |
|  <p>4-Way "X" Connector</p> <p>Connects tape sections</p> | <b>LED-TC-X</b><br><b>LED-TC-X-WT</b>   | Black<br>White |
|  <p>"L" Connector</p> <p>Connects tape sections</p>     | <b>LED-TC-L</b><br><b>LED-TC-L-WT</b>   | Black<br>White |
|  <p>End cap</p> <p>1 cut and 1 male end cap</p>         | <b>LED-TC-EC</b><br><b>LED-TC-EC-WT</b> | Black<br>White |

Compatible with Pro, Pro2, Pro3, LITE, Classic, Palette

|  |   |                 |
|--|---|-----------------|
|  <p>Signal Wire</p> <p>Links master and slave controllers. Can be combined for longer lengths</p> | <b>LED-TC24-SW60</b><br><b>LED-TC24-SW120</b> | 60 in<br>120 in |
|--|---|-----------------|

Compatible with Palette

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050



Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES


Indoor color changing electronic accessories

# WAC LIGHTING

Responsible Lighting®




| Type                      | Model   | Input  | Output      | Max Run | Dim | Compatibility  |
|---------------------------|---|--------|-------------|---------|-----|--|
| Remote<br>Color changing  |  <b>EN-2460D-C</b>   | 120VAC | 24VDC / 60W | 40 feet | ELV | Includes a 6 foot lead wire<br>Daylight to Sunset, Palette |
| Plug-in<br>Color changing |  <b>EN-2460D-C-P</b> | 120VAC | 24VDC / 60W | 40 feet | ELV | Includes a 6 foot lead wire<br>Daylight to Sunset, Palette |







Wireless controller (accessory for wired controller)  
**LED-TO24-WS**



Wired controller  
**LED-TC-CTR-MSD**



|                               |  |   |   |   |
|-------------------------------|--|---|---|---|
| Wired controller              |  <b>LED-TC-CTR-MSD</b> | 4 function wired controller with master and slave options   | Allows brightness control, preset color selection, or playing a rotation of color transitions with variable speed control | Daylight to Sunset, Palette                                   |
| Wireless Controller           |  <b>LED-TO24-WS</b>   | 4 function wireless controller (Requires wired controller)  | Allows brightness control, preset color selection, or playing a rotation of color transitions with variable speed control | Daylight to Sunset, Palette                                   |
| Touch Panel and Motion Sensor |  <b>CT-6A-R2</b>      | Includes a Touch Panel, an Occupancy Sensor, and a Controller<br>AC/DC input at 12V(60W Max) or 24V(96W Max)<br>Connect on secondary side of driver/transformer |   | Pro, Pro2, Pro3, LITE, Classic<br>Daylight to Sunset, Palette |

|                     |  |   |                                    |  |
|---------------------|--|---|------------------------------------|--|
| Signal Wire         |  <b>LED-TC24-SW60</b><br><b>LED-TC24-SW120</b>  | 60 in<br>120 in                         | Links master and slave controllers | Daylight to Sunset, Palette                                    |
| Joiner Cable        |  <b>LED-TC-IC2</b><br><b>LED-TC-IC6</b><br><b>LED-TC-IC12</b><br><b>LED-TC-IC36</b><br><b>LED-TC-IC72</b> | 2 in<br>6 in<br>12 in<br>36 in<br>72 in | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic,<br>Daylight to Sunset, Palette |
| 3-Way "Y" Connector |  <b>LED-TC-Y</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic,<br>Daylight to Sunset, Palette |
| 4-Way "X" Connector |  <b>LED-TC-X</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic,<br>Daylight to Sunset, Palette |
| "L" Connector       |  <b>LED-TC-L</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic,<br>Daylight to Sunset, Palette |
| End cap             |  <b>LED-TC-EC</b>   |   | 1 cut end cap and 1 male end cap   | Pro, Pro2, Pro3, LITE, Classic,<br>Daylight to Sunset, Palette |

Example: **LED-TC-IC6**

**WAC Lighting**  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

**Headquarters/Eastern Distribution Center**  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050
















**Western Distribution Center**  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES

Outdoor electronic accessories

# WAC LIGHTING

Responsible Lighting®

| Type   | Model  | Input   | Output  | Max Run | Dim | Compatibility   |
|--|--|---|---|---------|-----|---|
| Remote Damp Location            | <b>EN-OD24100-RB2-T</b>  | 120VAC  | 24VAC / 96W   | 30 feet | ELV | Includes a 6 foot lead wire<br>Minimum load of 1W<br><i>Pro Outdoor</i>                                   |
| Remote Wet Location             | <b>EN-O24100-RB2-T</b>   | 120 - 277VAC  | 24VDC / 96W   | 30 feet | No  | Class 2 rated<br>Includes a 6 foot lead wire<br>Minimum load of 1W<br><i>Pro Outdoor, Palette Outdoor</i> |
| Master Controller               | <b>LED-TO24-CM</b>   | 4" x 2" x 1½"   | Powers one run up to 40'.<br>Connects and controls all slave controllers for runs over 40'  |         |     | <i>Palette Outdoor</i>  |
| Slave Controller                | <b>LED-TO24-CS</b>   | 4" x 2" x 1½"   | Connects to Master Controller for runs over 40'.<br>Uses a separate 120V power supply. Powers up to another 40'.<br>A Slave Controller is needed for every 40' extension  |         |     | <i>Palette Outdoor</i>  |
| Wireless Controller (optional)  | <b>LED-TO24-WS</b>   | 4" x 2½" x 5/8"   | Wireless connection to Master Controller<br>Use to switch from color changing to white light<br>Play/Pause the color changing effect<br>Control the brightness and speed of the color changing effect<br>Uses 2 AAA batteries |         |     | <i>Palette Outdoor</i>  |
| Touch Panel and Motion Sensor   | <b>CT-6A-R2</b>  | Includes a Touch Panel, an Occupancy Sensor, and a Controller<br>AC/DC input at 12V(60W Max) or 24V(96W Max)<br>Connect on secondary side of driver/transformer |   |         |     | <i>Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette</i>   |
| End cap                        | <b>LED-TO24-EC</b>   | Use to terminate every run to protect against contaminants.<br>Seal cut end with silicone after adding end cap.   |   |         |     | <i>Pro Outdoor, Palette Outdoor</i>   |
| 3-Way "Y" Connector           | <b>LED-TO24-Y</b>  | Connects tape sections  |   |         |     | <i>Pro Outdoor</i>  |
| 4-Way "X" Connector           | <b>LED-TO24-X</b>  | Connects tape sections  |   |         |     | <i>Pro Outdoor</i>  |
| Joiner Cable                  | <b>LED-TO24-IC6</b><br><b>LED-TO24-IC12</b><br><b>LED-TO24-IC72</b><br><b>LED-TO24-IC120</b>                 | 6 in<br>12 in<br>72 in<br>120 in  | Extends distance between Power Supply and Master Controller.  |         |     | <i>Pro Outdoor</i>  |
| RGB 3-Way "Y" Connector       | <b>LED-TO24-Y-RGB</b>  | Connects tape sections  |   |         |     | <i>Palette Outdoor</i>  |
| RGB 4-Way "X" Connector       | <b>LED-TO24-X-RGB</b>  | Connects tape sections  |   |         |     | <i>Palette Outdoor</i>  |
| RGB Joiner Cable              | <b>LED-TO24-IC6-RGB</b><br><b>LED-TO24-IC12-RGB</b><br><b>LED-TO24-IC72-RGB</b><br><b>LED-TO24-IC120-RGB</b> | 6 in<br>12 in<br>72 in<br>120 in  | Use to connect two sections of InvisILED® Outdoor Palette tape.   |         |     | <i>Palette Outdoor</i>  |
| Signal wire                   | <b>LED-TO24-SW60</b><br><b>LED-TO24-SW120</b>  | 5 feet<br>10 feet   | Connects Master Controller and Slave Controller.  |         |     | <i>Palette Outdoor</i>  |
| DMX Signal Wire               | <b>LED-TO24-MW60</b><br><b>LED-TO24-MW120</b>  | 5 feet<br>10 feet   | Connects DMX system to Master Controller.   |         |     | <i>Palette Outdoor</i>  |

Example: **LED-TO24-WS**

**WAC Lighting**  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

**Headquarters/Eastern Distribution Center**  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

**Western Distribution Center**  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES

Indoor mounting accessories

# WAC LIGHTING

Responsible Lighting®

|   |   |        |                     |  |   |  |
|---|---|--------|---------------------|--|---|--|
|     |    | 5 feet | <b>LED-T-CH</b>     | Aluminum Channel                         | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH-EC</b>  | End caps for Aluminum Channel            |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|     |    | 5 feet | <b>LED-T-CH1</b>    | Deep Aluminum Channel                    | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH1-EC</b> | End caps for Deep Aluminum Channel       |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|     |    | 5 feet | <b>LED-T-CH2</b>    | 45° Angled Aluminum Channel              | Includes a diffuser, two end caps, and five screws  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |    | 2 pcs  | <b>LED-T-CH2-EC</b> | End caps for 45° Angled Aluminum Channel |   | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |  | 2 pcs  | <b>LED-T-CL3-PT</b> | 2 Adjustable Clips                       | Used to mount any aluminum channel<br>Includes 2 pieces, 4 screws                                       | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 2 pcs  | <b>LED-T-CL2-PT</b> | 2 Adjustable Clips                       | Used to mount any aluminum channel<br>Adjusts 50° from center either way<br>Includes 2 pieces, 4 screws | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|   |  | 3 feet | <b>LED-T-RC</b>     | Retrofit Channel                         | Can be bent to create fixed curves  | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 10 pcs | <b>LED-T-CL</b>     | Clip                                     | Holds an indoor tape from the underside<br>Includes 10 pieces, 10 screws                                | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |
|  |  | 10 pcs | <b>LED-T-CL1</b>    | Curve Clip                               | Runs over an indoor tape to secure the angled tape<br>Includes 10 pieces, 10 screws                     | Pro, Pro2, Pro3, LITE, Classic Daylight to Sunset, Palette |

## LED-T-\_\_\_\_\_

Example: **LED-T-CL3-PT**

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050





Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISIBLE® ACCESSORIES

## Outdoor mounting accessories

# WAC LIGHTING

Responsible Lighting®

|   |        |                     |                 |  |                                |
|---|--------|---------------------|-----------------|--|--------------------------------|
|  | 5 feet | <b>LED-TO24-CH5</b> | Clear Channel   | Rigid, non-flexible channel for mounting to a straight, solid surface.   | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C1</b>  | Mounting Clip 1 | For installation on non-flat surfaces where there is no edge contact. 2 clips per ft are recommended for straight runs.    | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C2</b>  | Mounting Clip 2 | For installation on non-flat surfaces, allows for contact on one edge. 2 clips per ft are recommended for straight runs.   | Pro Outdoor<br>Palette Outdoor |
|  | 10 pcs | <b>LED-TO24-C3</b>  | Mounting Clip 3 | For installation on non-flat surfaces, allows for contact on both edges. 2 clips per ft are recommended for straight runs. | Pro Outdoor<br>Palette Outdoor |

### LED-TO24-\_\_\_\_\_

Example: **LED-TO24-C2**

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585



# INVISILED® ACCESSORIES

Indoor non-color changing electronic accessories

# WAC LIGHTING

Responsible Lighting®

| Type   | Model  | Input            | Output                     | Max Run            | Dim        | Compatibility   |
|--|--|------------------|----------------------------|--------------------|------------|---|
|  <p>Remote<br/>Includes a 6 foot lead wire</p>  | <b>EN-2460-RB2-T</b><br><b>EN-24100-RB2-T</b>  | 120VAC<br>120VAC | 24VAC / 60W<br>24VAC / 96W | 30 feet<br>40 feet | ELV<br>ELV | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Plug-in<br/>Includes a 6 foot lead wire</p>   | <b>EN-2460-P-AR-T</b><br><b>EN-24100-P-AR-T</b>  | 120VAC<br>120VAC | 24VAC / 60W<br>24VAC / 96W | 30 feet<br>40 feet | ELV<br>ELV | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Remote 277V<br/>Includes a 6 foot lead wire</p>   | <b>EN-24100-277-RB2-T</b>  | 277VAC           | 24VDC / 96W                | 40 feet            | 0-10V      | Pro, Pro2, Pro3,<br>LITE, Classic                                   |
|  <p>Touch Panel and Motion Sensor<br/>Includes a Touch Panel, an Occupancy Sensor, and a Controller<br/>AC/DC input at 12V(60W Max) or 24V(96W Max)<br/>Connect on secondary side of driver/transformer</p> | <b>CT-6A-R2</b>  |                  |                            |                    |            | Pro, Pro2, Pro3,<br>LITE, Classic<br>Daylight to Sunset,<br>Palette |
|  <p>In Wall Rated Extension Cable<br/>Extends distance between a hard wired power supply or a wiring box to a tape section.</p>  | <b>LED-TC-WEXT-144</b><br><b>LED-TC-WEXT-144-WT</b><br><b>LED-TC-WEXT-240</b><br><b>LED-TC-WEXT-240-WT</b> |                  |                            |                    |            | Black 12 ft<br>White 12 ft<br>Black 20 ft<br>White 20 ft            |
|  <p>In Wall Rated Joiner Cable<br/>Connects tape sections. 2 female ends.<br/>1 male to male connector included</p>   | <b>LED-TC-WIC-144</b><br><b>LED-TC-WIC-144-WT</b><br><b>LED-TC-WIC-240</b><br><b>LED-TC-WIC-240-WT</b>     |                  |                            |                    |            | Black 12 ft<br>White 12 ft<br>Black 20 ft<br>White 20 ft            |
|  <p>Lead Wire<br/>Alternative lengths for plug-in power supplies</p>  | <b>LED-TC-P-2</b><br><b>LED-TC-P-2-WT</b><br><b>LED-TC-P-12</b><br><b>LED-TC-P-12-WT</b>                   |                  |                            |                    |            | Black 2 ft<br>White 2 ft<br>Black 12 ft<br>White 12 ft              |
|  <p>Extension Cable<br/>Extends distance between a hard wired power supply or a wiring box to a tape section</p>  | <b>LED-TC-EXT-144</b><br><b>LED-TC-EXT-144-WT</b>  |                  |                            |                    |            | Black 12 ft<br>White 12 ft  |
|  <p>Low Voltage Wiring Box With Feed<br/>Neatly houses connectors for up to two wires with 12" female feed</p>  | <b>LED-TC-B-2</b><br><b>LED-TC-B-2-WT</b>  |                  |                            |                    |            | Black L: 1½ in<br>White W: ¾ in<br>H: 7⁄8 in                        |
|  <p>Low Voltage Wiring Box<br/>Neatly houses connections for up to two wires</p>  | <b>LED-T-B</b>   |                  |                            |                    |            | L: 1½ in<br>W: ¾ in<br>H: 7⁄8 in                                    |
|  <p>Wiring Box With Switch<br/>Use when spanning a large gap in a system layout without leaving exposed wiring. Optional switch included</p>  | <b>TB-S</b>  |                  |                            |                    |            | L: 6¼ in<br>W: 1½ in<br>H: 1¼ in                                    |

Compatible with Pro, Pro2, Pro3, LITE, Classic

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050



Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISIBLE® ACCESSORIES

Indoor non-color changing electronic accessories

# WAC LIGHTING

Responsible Lighting®

|   |                       |       |        |
|---|-----------------------|-------|--------|
|  <p>Joiner Cable</p> <p>Connects tape sections</p> | <b>LED-TC-IC2</b>     | Black | 2 in   |
|   | <b>LED-TC-IC2-WT</b>  | White | 2 in   |
|   | <b>LED-TC-IC6</b>     | Black | 6 in   |
|   | <b>LED-TC-IC6-WT</b>  | White | 6 in   |
|   | <b>LED-TC-IC12</b>    | Black | 12 in  |
|   | <b>LED-TC-IC12-WT</b> | White | 12 in  |
|   | <b>LED-TC-IC36</b>    | Black | 36 in  |
|   | <b>LED-TC-IC36-WT</b> | White | 36 in  |
|   | <b>LED-TC-IC72</b>    | Black | 72 in  |
|   | <b>LED-TC-IC72-WT</b> | White | 72 in  |
|  <p>Male to male connector</p>                     | <b>LED-TC-MM</b>      | Black | 50 Qty |

Compatible with Pro, Pro2, Pro3, LITE, Classic, Palette  
Change directionality of tape runs and reuse cut ends of tape.

|  |   |                |
|--|---|----------------|
|  <p>3-Way "Y" Connector</p> <p>Connects tape sections</p> | <b>LED-TC-Y</b><br><b>LED-TC-Y-WT</b>   | Black<br>White |
|  <p>4-Way "X" Connector</p> <p>Connects tape sections</p> | <b>LED-TC-X</b><br><b>LED-TC-X-WT</b>   | Black<br>White |
|  <p>"L" Connector</p> <p>Connects tape sections</p>     | <b>LED-TC-L</b><br><b>LED-TC-L-WT</b>   | Black<br>White |
|  <p>End cap</p> <p>1 cut and 1 male end cap</p>         | <b>LED-TC-EC</b><br><b>LED-TC-EC-WT</b> | Black<br>White |

Compatible with Pro, Pro2, Pro3, LITE, Classic, Palette

|  |   |                 |
|--|---|-----------------|
|  <p>Signal Wire</p> <p>Links master and slave controllers. Can be combined for longer lengths</p> | <b>LED-TC24-SW60</b><br><b>LED-TC24-SW120</b> | 60 in<br>120 in |
|--|---|-----------------|

Compatible with Palette

WAC Lighting  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050



Western Distribution Center  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES


Indoor color changing electronic accessories

# WAC LIGHTING

Responsible Lighting®




| Type   | Model               | Input  | Output      | Max Run | Dim | Compatibility  |
|--|---------------------|--------|-------------|---------|-----|--|
| Remote Color changing   | <b>EN-2460D-C</b>   | 120VAC | 24VDC / 60W | 40 feet | ELV | Includes a 6 foot lead wire<br>Daylight to Sunset, Palette |
| Plug-in Color changing  | <b>EN-2460D-C-P</b> | 120VAC | 24VDC / 60W | 40 feet | ELV | Includes a 6 foot lead wire<br>Daylight to Sunset, Palette |







Wireless controller (accessory for wired controller)  
**LED-TO24-WS**



Wired controller  
**LED-TC-CTR-MSD**



|   |                       |   |   |   |
|---|-----------------------|---|---|---|
| Wired controller                | <b>LED-TC-CTR-MSD</b> | 4 function wired controller with master and slave options   | Allows brightness control, preset color selection, or playing a rotation of color transitions with variable speed control | Daylight to Sunset, Palette                                   |
| Wireless Controller            | <b>LED-TO24-WS</b>    | 4 function wireless controller (Requires wired controller)  | Allows brightness control, preset color selection, or playing a rotation of color transitions with variable speed control | Daylight to Sunset, Palette                                   |
| Touch Panel and Motion Sensor  | <b>CT-6A-R2</b>       | Includes a Touch Panel, an Occupancy Sensor, and a Controller<br>AC/DC input at 12V(60W Max) or 24V(96W Max)<br>Connect on secondary side of driver/transformer |   | Pro, Pro2, Pro3, LITE, Classic<br>Daylight to Sunset, Palette |

|   |  |   |                                    |   |
|---|--|---|------------------------------------|---|
| Signal Wire          | <b>LED-TC24-SW60</b><br><b>LED-TC24-SW120</b>  | 60 in<br>120 in                         | Links master and slave controllers | Daylight to Sunset, Palette                                 |
| Joiner Cable         | <b>LED-TC-IC2</b><br><b>LED-TC-IC6</b><br><b>LED-TC-IC12</b><br><b>LED-TC-IC36</b><br><b>LED-TC-IC72</b> | 2 in<br>6 in<br>12 in<br>36 in<br>72 in | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, Palette |
| 3-Way "Y" Connector  | <b>LED-TC-Y</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, Palette |
| 4-Way "X" Connector  | <b>LED-TC-X</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, Palette |
| "L" Connector        | <b>LED-TC-L</b>  |   | Connects tape sections             | Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, Palette |
| End cap              | <b>LED-TC-EC</b>   |   | 1 cut end cap and 1 male end cap   | Pro, Pro2, Pro3, LITE, Classic, Daylight to Sunset, Palette |

Example: **LED-TC-IC6**

**WAC Lighting**  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

**Headquarters/Eastern Distribution Center**  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050
















**Western Distribution Center**  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585

# INVISILED® ACCESSORIES

Outdoor electronic accessories

# WAC LIGHTING

Responsible Lighting®

| Type   | Model  | Input   | Output  | Max Run | Dim | Compatibility   |
|--|--|---|---|---------|-----|---|
| Remote Damp Location            | <b>EN-OD24100-RB2-T</b>  | 120VAC  | 24VAC / 96W   | 30 feet | ELV | Includes a 6 foot lead wire<br>Minimum load of 1W<br><br>Pro Outdoor                                      |
| Remote Wet Location             | <b>EN-O24100-RB2-T</b>   | 120 - 277VAC  | 24VDC / 96W   | 30 feet | No  | Class 2 rated<br>Includes a 6 foot lead wire<br>Minimum load of 1W<br><br>Pro Outdoor,<br>Palette Outdoor |
| Master Controller               | <b>LED-TO24-CM</b>   | 4" x 2" x 1½"   | Powers one run up to 40'.<br>Connects and controls all slave controllers for runs over 40'  |         |     | Palette Outdoor   |
| Slave Controller                | <b>LED-TO24-CS</b>   | 4" x 2" x 1½"   | Connects to Master Controller for runs over 40'.<br>Uses a separate 120V power supply. Powers up to another 40'.<br>A Slave Controller is needed for every 40' extension  |         |     | Palette Outdoor   |
| Wireless Controller (optional)  | <b>LED-TO24-WS</b>   | 4" x 2½" x 5/8"   | Wireless connection to Master Controller<br>Use to switch from color changing to white light<br>Play/Pause the color changing effect<br>Control the brightness and speed of the color changing effect<br>Uses 2 AAA batteries |         |     | Palette Outdoor   |
| Touch Panel and Motion Sensor   | <b>CT-6A-R2</b>  | Includes a Touch Panel, an Occupancy Sensor, and a Controller<br>AC/DC input at 12V(60W Max) or 24V(96W Max)<br>Connect on secondary side of driver/transformer |   |         |     | Pro, Pro2, Pro3,<br>LITE, Classic<br>Daylight to Sunset,<br>Palette                                       |
| End cap                        | <b>LED-TO24-EC</b>   | Use to terminate every run to protect against contaminants.<br>Seal cut end with silicone after adding end cap.   |   |         |     | Pro Outdoor,<br>Palette Outdoor   |
| 3-Way "Y" Connector           | <b>LED-TO24-Y</b>  | Connects tape sections  |   |         |     | Pro Outdoor   |
| 4-Way "X" Connector           | <b>LED-TO24-X</b>  | Connects tape sections  |   |         |     | Pro Outdoor   |
| Joiner Cable                  | <b>LED-TO24-IC6</b><br><b>LED-TO24-IC12</b><br><b>LED-TO24-IC72</b><br><b>LED-TO24-IC120</b>                 | 6 in<br>12 in<br>72 in<br>120 in  | Extends distance between Power Supply and Master Controller.  |         |     | Pro Outdoor   |
| RGB 3-Way "Y" Connector       | <b>LED-TO24-Y-RGB</b>  | Connects tape sections  |   |         |     | Palette Outdoor   |
| RGB 4-Way "X" Connector       | <b>LED-TO24-X-RGB</b>  | Connects tape sections  |   |         |     | Palette Outdoor   |
| RGB Joiner Cable              | <b>LED-TO24-IC6-RGB</b><br><b>LED-TO24-IC12-RGB</b><br><b>LED-TO24-IC72-RGB</b><br><b>LED-TO24-IC120-RGB</b> | 6 in<br>12 in<br>72 in<br>120 in  | Use to connect two sections of InvisILED® Outdoor Palette tape.   |         |     | Palette Outdoor   |
| Signal wire                   | <b>LED-TO24-SW60</b><br><b>LED-TO24-SW120</b>  | 5 feet<br>10 feet   | Connects Master Controller and Slave Controller.  |         |     | Palette Outdoor   |
| DMX Signal Wire               | <b>LED-TO24-MW60</b><br><b>LED-TO24-MW120</b>  | 5 feet<br>10 feet   | Connects DMX system to Master Controller.   |         |     | Palette Outdoor   |

Example: **LED-TO24-WS**

**WAC Lighting**  
www.waclighting.com  
Phone (800) 526.2588 • Fax (800) 526.2585

**Headquarters/Eastern Distribution Center**  
44 Harbor Park Drive • Port Washington, NY 11050  
Phone (516) 515.5000 • Fax (516) 515.5050

**Western Distribution Center**  
1750 Archibald Avenue • Ontario, CA 91760  
Phone (800) 526.2588 • Fax (800) 526.2585