



**Southwire**<sup>™</sup>

TOOLS & EQUIPMENT

# 2019 LIGHTING SOLUTIONS CATALOG



BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.<sup>™</sup>

[SOUTHWIRETOOLS.COM](http://SOUTHWIRETOOLS.COM)

# OUR STORY

For over 60 years, Southwire has provided high quality electrical wire and cable to the commercial and industrial construction industries. Now, the name you trust provides durable, cutting-edge professional grade tools, designed with safety and productivity in mind. Look to Southwire® for solutions to all your electrical needs, from electrician's hand tools, meters, contractor equipment, temporary power, and extension cords.

## TABLE OF CONTENTS

Overhead Lights.....	3
Area Lights.....	11
String Lights.....	15
Flood & Work Lights.....	19
Installed Lights.....	25
Clamps and Personal Lighting.....	27

# ***OVERHEAD LIGHTS***



**BUILT FOR DURABILITY. BUILT FOR RELIABILITY. BUILT FOR WORK.™**

# OVERHEAD LIGHTS

## LED Bulb Fixtures

Hanging lights that utilize replaceable LED bulbs protected by a metal cage provide versatile solutions on the job site. These fixtures allow the user to select the lamp and light output level that best fits their application and cast light downward and outward.

**Integral hook for easy hanging**

**Replaceable bulb**

**Bulbs with varied lumen options**

**Protective cages**



## Integrated LED Fixtures

Built-in LED systems create highly efficient light output. These fixtures match those light systems with optical designs that deliver the light with precision down to where the work gets done.

**Integral hook for easy hanging**

**Rugged die cast housing**

**120 degree beam**

**Glare reducing lens**

**Integrated high performance LEDs**



## HANG-A-LIGHT

### LED TEMPORARY CAGE LIGHT WITH PLUG & RECEPTACLE 120V ONLY



111060LED

- 35,000 hour bulb life with 5000K color temperature
- Operating temp: -40 to 125 F
- 5-15 plug with 14/3 SJTW cord - 58"
- 6.5-8 lbs.
- Spring loaded hanging clamp

Description	Model #	Watts	Amp Draw	Linkable Units
7,500 Lumen LED Cage Light w/Plug and Receptacle	111060LED	60	0.5	8
10,400 Lumen LED Cage Light w/Plug and Receptacle	111080LED	80	0.8	6
13,500 Lumen LED Cage Light w/Plug and Receptacle	1110100LED	100	0.9	4
15,600 Lumen LED Cage Light w/Plug and Receptacle	1110120LED	120	1.1	3
19,500 Lumen LED Cage Light w/Plug and Receptacle	1110150LED	150	1.3	3

## HANG-A-LIGHT

### LED TEMPORARY CAGE LIGHT WITH DIRECT WIRE CORD 120-277V



1110100LED

- 35,000 hour bulb life with 5000K color temperature
- Operating temp: -40 to 125 F
- 5-15 plug with 14/3 SJTW cord - 58"
- 6.5-8 lbs.
- Spring loaded hanging clamp

Description	Model #	Watts	Amp Draw
7,500 Lumen LED Cage Light w/ Wire Whip	111060NR	60	0.8
10,400 Lumen LED Cage Light w/ Wire Whip	111080NR	80	0.9
13,500 Lumen LED Cage Light w/ Wire Whip	1110100NR	100	1.1
15,600 Lumen LED Cage Light w/ Wire Whip	1110120NR	120	1.3

## HANG-A-LIGHT

### LONG NECK LED TEMP CAGE LIGHT WITH PLUG & RECEPTACLE



1110120ECO

- 5,000K color temperature
- Operating temp: -40 to 125 F
- 14/3 SJTW cord - 58"
- 5.3-8 lbs.
- Spring loaded hanging clamp

Description	Model #	Watts	Amp Draw	Linkable Units
7,600 Lumen LED Long Neck Cage Light w/Plug and Receptacle	111080ECO	80	0.8	6
13,500 Lumen LED Long Neck Cage Light w/Plug and Receptacle	1110120ECO	120	0.9	4

### HANG-A-LIGHT REPLACEMENT BULBS

- 5,000K color temperature
- Operating temp: -40 to 125 F



111900

Description	Model #	Watts	Style	Bulb Life
7,500 Lumen Bulb	111960	60	Corncob	35,000
10,400 Lumen Bulb	111980	80	Corncob	35,000
13,500 Lumen Bulb	111900	100	Corncob	35,000
15,600 Lumen Bulb	1119120	120	Corncob	35,000
19,500 Lumen Bulb	111950	150	Corncob	35,000
7,600 Lumen Bulb	111980L	80	Long Neck	25,000
13,500 Lumen Bulb	1119120L	120	Long Neck	30,000

# OVERHEAD LIGHTS

## INTEGRATED LED CAGE LIGHTS

- 50,000 hour life
- Operating temp: -40° to 125° F



T50100W & T50078

Description	Model #	IP Rating	Color Temperature	Watts	Voltage	Cord Length	Connection type
6,500 Lumen Temporary Low Bay LED Light, Plug	TL60WP	IP65	6,500K	60	120	10'	5-15 Plug
6,500 Lumen Temporary Low Bay LED Light, Plug	TL100WP	IP65	6,500K	60	120/277	10'	5-15 Plug
8200 Lumen Temporary Low Bay LED Light, Plug	T50078		5,000K	78	120	3'	5-15 Plug
8200 Lumen Temporary Low Bay LED Light, Direct Wire	T50079		5,000K	78	120/277	3'	Direct Wire
15,000 Lumen Temporary High Bay LED, Plug	111200LED		5,000K	150	120	5'	5-15 Plug
6,300 Lumen Jobsite LED Lantern	T50060W	IP64	5,000K	60	120	10'	5-15 Plug
11,000 Lumen Jobsite LED Lantern	T50100W	IP64	5,000K	100	120	10'	5-15 Plug



111105F

## METAL HALIDE AND FLUORESCENT CAGE LIGHTS

- Damp location
- 4,000K Color temperature
- 5-15 plug with 14/3 SJTW cord-60"

Description	Model #	Lamp Life	Watts	Amp Draw	Linkable Units	Temp. Rated	Weight
6,900 Lumen Temporary Fluorescent Cage Light	111105F	10,000 hr.	105	0.87	6	5 to 125 F	5 lbs.
42,000 Lumen Temporary Metal Halide Cage Light	111400PS	20,000 hr.	400	4	Modifiable	-30 to 120 F	20 lbs.



111084

## WET LOCATION, IP65 HANGING LIGHTS

- 6" rare earth magnet or eye hooks
- No exposed glass
- 120V
- 10 lbs.
- 5-15 plug with 14/3 SJTW cord - 60"

Description	Model #	Lamp Life	Watts	Color Temp.	Amp Draw	Temp. Rated
6,400 Lumen Temporary Fluorescent Wet Location Light	111084	20,000 hr.	84	3,500K	0.76	-5 to 120 F
6,000 Lumen Temporary LED Wet Location Light	111085	40,000 hr.	60	5,000K	0.54	-30 to 120 F



111984

## REPLACEMENT BULBS

Description	Model #	Works With	Bulb Life	Color Temp.	Watts
42W Fluorescent Replacement Bulb	111984	111084	20,000 hr.	3,500K	42
105W Fluorescent Replacement Bulb	111915	111105F	10,000 hr.	4,000K	105
400W Metal Halide Replacement Bulb	111903PS	111400PS	20,000 hr.	4,100K	400

## CUSTOM LIGHT FIXTURE

Create the perfect overhead light to fit your lighting needs.

Job sites are complex and having the right product at the right time can save you time and money. Garvin custom light fixtures can be designed specifically for your job.

### LUMENS

- 5,200
- 7,800
- 10,400
- 13,000
- 15,600
- 19,500
- 28,000

### CORD GAUGE

- 16
- 14
- 12

### CORD LENGTH

- 6'
- 10'
- Other \_\_\_\_\_



**NEMA  
5-15P**



**NEMA  
L5-15P**



**NEMA  
L7-15P**



Male Cord End	Female Cord End
none	none
515P-120V 15A 3 PRONG STRAIGHT BLADE	515P-120V 15A 3 PRONG STRAIGHT BLADE
L515-120V 15A TWIST LOCK	L515-120V 15A TWIST LOCK
L520-120V 20A TWIST LOCK	L520-120V 20A TWIST LOCK
L715-277V 15A TWIST LOCK	L715-277V 15A TWIST LOCK
L720-277V 20A TWIST LOCK	L720-277V 20A TWIST LOCK

## PACKAGING

- Standard skid wrapped
- Jobsite ready packaging in gaylord and fully assembled

# OVERHEAD LIGHTS

## CUSTOM TEMPORARY LED LIGHTS

- 6,500K color temperature
- 50,000 hour bulb life
- Mogul base



TL40LEDW



TL100LEDWS



TL200LEDWTL

Description	Model #	Cord	Watts/Volt
5,200 Lumen Cage Light w/ LED Corncob Bulb	TL40LED	None	40W/120-277V
	TL40LEDW	6' w/ 5-15P Plug	40W/120V
	TL40LEDWS	6' Direct Wire	40W/120-277V
	TL40LEDWTL	6' w/ L7-15P Twist Lock Plug	40W/277V
	TL40LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	40W/120V
7,800 Lumen Cage Light w/ LED Corncob Bulb	TL60LED	None	60W/120-277V
	TL60LEDW	6' w/ 5-15P Plug	60W/120V
	TL60LEDWS	6' Direct Wire	60W/120-277V
	TL60LEDWTL	6' w/ L7-15P Twist Lock Plug	60W/277V
	TL60LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	60W/120V
10,400 Lumen Cage Light w/ LED Corncob Bulb	TL80LED	None	80W/120-277V
	TL80LEDW	6' w/ 5-15P Plug	80W/120V
	TL80LEDWS	6' Direct Wire	80W/120-277V
	TL80LEDWTL	6' w/ L7-15P Twist Lock Plug	80W/277V
13,000 Lumen Cage Light w/ LED Corncob Bulb	TL100LEDW	6' w/ 5-15P Plug	100W/120V
	TL100LEDWS	6' Direct Wire	100W/120-277V
	TL100LEDWTL	6' w/ L7-15P Twist Lock Plug	100W/277V
	TL100LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	100W/120V
15,600 Lumen Cage Light w/ LED Corncob Bulb	TL120LED	None	120W/120-277V
	TL120LEDW	6' w/ 5-15P Plug	120W/120V
	TL120LEDWS	6' Direct Wire	120W/120-277V
	TL120LEDWTL	6' w/ L7-15P Twist Lock Plug	120W/277V
19,500 Lumen Cage Light w/ LED Corncob Bulb	TL120LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	120W/120V
	TL150LED	None	150W/120-277V
	TL150LEDW	6' w/ 5-15P Plug	150W/120V
	TL150LEDWS	6' Direct Wire	150W/120-277V
28,000 Lumen Cage Light w/ LED Corncob Bulb	TL150LEDWTL	6' w/ L7-15P Twist Lock Plug	150W/277V
	TL150LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	150W/120V
	TL200LED	None	200W/120-277V
	TL200LEDW	6' w/ 5-15P Plug	200W/120V
	TL200LEDWS	6' Direct Wire	200W/120-277V
	TL200LEDWTL	6' w/ L7-15P Twist Lock Plug	200W/277V
	TL200LEDPT	1' Cord w/ 5-15P Plug and 1' Cord w/ 5-15R Receptacle	200W/120V

## CUSTOM TEMPORARY FLUORESCENT LIGHTS

- 150W
- 8,000 hour bulb life
- Mounting hook & steel cage
- 3 to 5 lbs.



TL105CFPT

Description	Model #	Cord End	Cord Length	Volts	Bulb Base
6,400 Lumen, 150W Fluorescent Temporary Light	TL105CF	None	None	120V	Medium
	TL105CFW	6' w/ 5-15P Plug	6'		
	TL105CFWS	6' Direct Wire	6'		
	TL105CFPT	1' cord w/ 5-15P Plug and 1' cord w/ 5-15R Receptacle	1"	277V	Mogul
	TL105CF277	None	None		
	TL105CF277W	6' w/ 5-15P Plug	6'		
	TL105CF277WS	6' Direct Wire	6'		

## CUSTOM MINI TEMPORARY LIGHTS

- Steel Cage
- Medium Base



TLM

Description	Model #	Cord	Volts
Mini Temporary Cage Light	TLM	None	120V-277V
	TLMW	6' Cord w/ 5-15 Plug	120V
	TLMPT	6" Cord w/ 5-15P Plug and 5-25R Receptacle	120V
	TLMAGW	Magnetic w/ 6' Cord w/ 5-15 Plug	120V

## DIRECT WIRE BOX MOUNTED TEMPORARY LIGHTS

- Steel cage
- Medium bulb base
- Includes mounting plates for square and round boxes
- Dire wire



TLCO

Description	Model #	Bulb
1,000 Lumen Box Mount Temp Cage Light	TLCO	9W
Box Mount Wall Sconce Temp Cage Light	TLMU	NA

# OVERHEAD LIGHTS

## REPLACEMENT BULBS

- 6,500K color temperature
- LED bulbs are IP64



LED100

Description	Model #	Watts/Volts	Bulb Life	Bulb Base
6,400 Lumen, Fluorescent Bulb	C105651MED	105W/120V	8,000 Hr.	Medium
6,400 Lumen, Fluorescent Bulb	C105652MOG	105W/277V	8,000 Hr.	Mogul
5,200 Lumen, LED Corncob Bulb	LED40	40W/120V-277V	50,000 Hr.	Medium
7,800 Lumen, LED Corncob Bulb	LED60	60W/120V-277V	50,000 Hr.	Medium
10,400 Lumen, LED Corncob Bulb	LED80	80W/120V-277V	50,000 Hr.	Mogul
13,000 Lumen, LED Corncob Bulb	LED100	100W/120V-277V	50,000 Hr.	Mogul
15,600 Lumen, LED Corncob Bulb	LED120	120W/120V-277V	50,000 Hr.	Mogul
19,500 Lumen, LED Corncob Bulb	LED150	120W/120V-277V	50,000 Hr.	Mogul
28,000 Lumen, LED Corncob Bulb	LED200	200W/120V-277V	50,000 Hr.	Mogul

## HANGING ACCESSORIES



CPMH1

Description	Model #
Heavy Duty Light Fixture Hook with Set Screw and Lock Nut	CPMH1
Heavy Duty Light Fixture Hook with Set Screw, Lock Nut, and Gasket	CPMH1-VT
Zinc Fixture Support Chain with Steel Plate	JC-100

## CUSTOM LIGHT ACCESSORIES



TLPS

Description	Model #
Light Pollution Shield, 13" (Works with Medium Base Fixtures)	TLPS
Light Pollution Shield, 15" (Works with Mogul Base Fixtures)	TLPS-L
Temp Light Lockable Acrylic Guard	TLSGLK

# AREA LIGHTS



# AREA LIGHTS



For 20 years the Wobblelight has been providing reliable lighting to the job site. The self-righting design paired with the heavy duty housing guarantees these products will give years of service in even the toughest environments.

**360 degrees of light**

**Integrated handle**

**Robust housing**

**Covered plug**

**No hot surfaces**

**Self righting design**





111301LED

## LED WOBBLE LIGHTS

- 120V
- 5,000K color temperature
- Operating temp: -40° to 125° F
- 5-15 plug



Description	Model #	Body Style	Watts	Lamp Life	Linkable Units	Amp Draw	Cord Type	IP Rating	Weight
9,000 lumen 27" LED Wobblelight	111206	27"	80W	35,000 Hr.	-	0.7A	5', 18/2 SJTW	-	14 lbs
12,000 lumen 36" LED Wobblelight	111301LED	31"	150W	50,000 Hr.	6 Max	1.25A	16/3 SJ00W	IP54	31 lbs
15,000 lumen 36" LED Wobblelight	111303LED	31"	220W	50,000 Hr.	-	1.8A	16/3 SJ00W	IP55	31 lbs



111102

## METAL HALIDE WOBBLE LIGHTS

- 120V
- 4,000K color temperature
- Operating temp: -40° to 125° F
- Built in 5-15 plug + receptacle (no cord included)
- Assembled in USA



Description	Model #	Body Style	Watts	Lamp Life	Linkable Units	Amp Draw	Cord Type	IP Rating	Weight
15,000 lumen 36" Metal Halide Wobblelight	111102	36"	175W	10,000 Hr.	5 Max	1.9A	-	-	29 lbs
40,000 lumen 36" Metal Halide Wobblelight	111104	36"	400W	20,000 Hr.	3 Max	4A	-	-	33 lbs



111302

## HALOGEN WOBBLE LIGHTS

- 120V
- 4,000K color temperature
- Operating Temp: -20° to 120° F
- Built in 5-15 Plug (no cord included)
- Assembled in USA



Description	Model #	Body Style	Watts	Lamp Life	Linkable Units	Amp Draw	Cord Type	IP Rating	Weight
8,000 lumen 36" Halogen Wobblelight	111302	36"	500W	2,000 Hr.	2	4.5A	-	-	28 lbs



111205

## FLUORESCENT WOBBLE LIGHTS

- 120V
- 2,700K color temperature
- Operating Temp: -20° to 120° F
- Built in 5-15 plug (5ft. cord)



Description	Model #	Body Style	Watts	Lamp Life	Linkable Units	Amp Draw	Cord Type	IP Rating	Weight
5,000 lumen 27" Fluorescent Wobblelight	111205	27"	85W	8,000 Hr.	-	.6	18/2 SJTW	-	13.5 lbs

## WOBBLE ACCESSORIES AND REPLACEMENT BULBS

(ADDITIONAL REPLACEMENT PARTS AVAILABLE)

Description	Model #	Works With
9,000 LM LED Bulb	111980JR	11206
85W Fluorescent Bulb	111908	11205
500W Halogen Bulb	111904	111302
175W Metal Halide Bulb	111901	111102
400W Metal Halide Bulb	111903	111104
Nylon Reflector Shield	111807	111203, 111204, 111205, 111206
Nylon Reflector Shield	111808	111301LED, 111303LED, 111302, 111102, 111104
Replacement Reflector Dome and Cap	111801	111302, 111102, 111104
Replacement Reflector Dome and Cap	1113186	111301LED, 111303LED

# AREA LIGHTS

## LED AREA LIGHTS, 120V

- Various mounting and hanging options available



111508

Description	Model #	Lumens	Light Temperature	IP Rating	Linkable	Watts	Cord	Features
ProLight™ 360 LED Light Kit	111508	15,000	5,000K	IP65		120W	5' - 18/3 SJTW Cord	Included: Floor Stand Tripod Mount, Hook, Two Earth Magnets
ProLight™ 360 LED Light Kit with Tripod	111509	15,000	5,000K	IP65		120W	5' - 18/3 SJTW Cord	Included: Floor Stand Tripod Mount, Hook, Two Earth Magnets Heavy Duty Tripod
6,300 Lumen LED Lantern	T50060W	6,300	5,000K	IP64	Up to 14	60W	16/3 SJTW 10 ft.	Includes floor stand and ceiling mount
7,500 Lumen LED Lantern	TLU-60	7,500				60W		Included: Hook, Magnet, Tri-pod Adapter, and Paint Shield
11,000 Lumen LED Lantern	T50100W	11,000	5,000K	IP64	Up to 8	100W	16/3 SJTW 10 ft.	Male and female plug for linking multiple
12,000 Lumen LED Lanterns	TLU-100	12,500				100W	10' Cord	Included: Hook, Magnet, Tri-pod Adapter, and Paint Shield

\*Available Feb 2019

## FLUORESCENT AREA LIGHTS, 120V



E712600

Description	Model #	Lumens	Light Temperature	IP Rating	Watts	Amp Draw	Cord	Features
Eco Uplight Fluorescent Tripod light	E712600	3,250	4,000K	44	36	.33	18/3 SJTW	Carry strap

# ***STRING LIGHTS***



# STRING LIGHTS

## LED String Lights

Shine light along hundreds of feet with the ease utilizing these convenient and easy to install integrated LED string lights. With no bulb to break or replace, these products are low profile and will provide service for years.

50' and 100'

Daisy chain up to 1000'

No bulbs

IP65

Durable construction

Uplight



## LED STRING LIGHTS

- 5000K Light Color Temperature
- 800 Lumens per head
- 5-15 plug + receptacle
- IP65
- 100 Lumens of uplight
- 700 Lumens of down light



7164SW

Description	Model #	Cord Type	Head Count	Linkable Units	Weight
50' - 14/3, 4,000 Lumen, LED String Light	7164SW	14/3 SJTW	5	20	
100' - 14/3, 8,000 Lumen, LED String Light	7165SW	14/3 SJTW	10	10	

## STRING LIGHTS WITH PLASTIC CAGE, 120V

- Medium base, A-23 sockets
- Integrated plug and receptacle



7145SW

Description	Model #	Cord Type	Socket #	Linkable Units	Weight
100' - 14/2, Medium Duty String Light with Plastic Cage	7145SW	14/2 SJTW	10	-	
50' - 14/3, Medium Duty String Light with Plastic Cage	11107050	14/3 SJTW	5	8	10 lbs
100' - 14/3, Medium Duty String Light with Plastic Cage	11107100	14/3 SJTW	10	5	20 lbs
50' - 12/3, Heavy Duty String Light with Plastic Cage	7548SW	12/3 SJTW	5		
100' - 12/3, Heavy Duty String Light with Plastic Cage	7549SW	12/3 SJTW	10		

## STRING LIGHTS WITH LED BULBS AND PLASTIC CAGE, 120V

- 1,500 lumens bulbs
- Medium base, A-23 socket
- 30,000 Hr. bulb life
- Integrated plug and receptacle



111100

Description	Model #	Cord Type	Socket #	Linkable Units	Weight
50' - 14/3, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	131050	14/3 SJTW	5	8	10 lbs
100' - 14/3, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	131100	14/3 SJTW	10	5	20 lbs
100' - 14/2, Heavy Duty String Light with Plastic Cage and 1,500 Lumen Bulbs	111100	14/2 SJTW	10	-	20 lbs

## STRING LIGHTS WITH METAL CAGE, 120V

- Medium base, A-23 sockets
- STW options with extra hard cable projection
- Meets OSHA and NEC requirements
- Integrated plug and receptacle



7538SW

Description	Model #	Cord Type	Socket #	Linkable Units	Bottom Cage Shield	Weight
50' - 12/3, Medium Duty String Light with Metal Cage	7538SW	12/3 SJTW	5		No	
100' - 12/3, Medium Duty String Light with Metal Cage	7539SW	12/3 SJTW	10		No	
50' - 12/3, Heavy Duty String Light with Metal Cage	11109050	12/3 STW	5	5	Yes	13 lbs
100' - 12/3, Heavy Duty String Light with Metal Cage	11109100	12/3 STW	10	5	Yes	28 lbs

# STRING LIGHTS



121050

## STRING LIGHTS WITH LED BULBS AND METAL CAGE, 120V

- 1,500 lumen bulbs
- Medium base, A-23 sockets
- 30,000 Hr. bulb life
- Meets OSHA and NEC requirements
- Integrated plug and receptacle

Description	Model #	Cord Type	Socket #	Linkable Units	Weight
50' - 12/3, String Light with Metal Cage and 1,500 Lumen Bulbs	121050	12/3 STW	5	8	13 lbs
100' - 12/3, String Light with Metal Cage and 1,500 Lumen Bulbs	121100	12/3 STW	10	5	28 lbs

## STRING LIGHTS REPLACEMENT PARTS



Description	Model #	Works With
1,500 Lumen LED Replacement Bulb	111917	All socketed string light models
Plastic replacement Cage	73010000	
Metal Replacement Cage	72002000	

# ***FLOOD & WORK LIGHTS***



BUILT FOR DURABILITY. BUILT FOR RELIABILITY. BUILT FOR WORK.™ | 19

# FLOOD & WORK LIGHTS

## SLIM SERIES LED WORK LIGHT

These heavy duty directional lights will put the light right where it is needed. The Slim Series gives multiple brightness and mounting options to fit the changing demands each day brings.

**1,500 to 10,000 lumen models available**

**180 degree pivoting head**

**IP65 indoor outdoor use**

**Pure white 5,000K LED light**

**Durable aluminum body construction**



## SLIM SERIES LED WORK LIGHT

- Aluminum body
- IP65, indoor or outdoor use
- Operating temp: -40° to 122° F
- 5,000K LED with 50,000 Hr. life
- 120V, 5' - 18/3 SJTW cord



411050

Description	Model #	Lumens	Watts	Stand
1,500 Lumen LED Slim Work Light	411015	1,500	15W	Floor Stand
1,500 Lumen LED Slim Work Light w/ Tripod	411215	1,500	15W	Tripod
3,000 Lumen LED Twin Head Slim Light w/ Tripod	411315	1,500 x2	30W	Tripod
3,000 Lumen LED Slim Work Light	411030	3,000	30W	Floor Stand
3,000 Lumen LED Slim Work Light w/ Magnetic Base	411430	3,000	30W	Magnetic Disc Base
3,000 Lumen LED Slim Work Light w/ Tripod	411230	3,000	30W	Tripod
6,000 Lumen LED Twin Head Slim Light w/ Tripod	411330	3,000 x2	60W	Tripod
5,000 Lumen LED Slim Work Light	411050	5,000	50W	Floor Stand
5,000 Lumen LED Slim Work Light w/ Magnetic Base	411450	5,000	50W	Magnetic Disc Base
5,000 Lumen LED Slim Work Light w/ Tripod	411250	5,000	50W	Tripod
10,000 Lumen LED Twin Head Slim Light w/ Tripod	411350	5,000 x2	100W	Tripod



515100

## PROLIGHT™ 6,000 SERIES LED WORK LIGHT

- IP55
- Operating temp: -40° to 120° F
- 5,000K LED with 30,000 Hr. life
- 120V, 5' - 16/2 SJTW Cord
- ABS housing and polycarbonate lens

Description	Model #	Lumens	Watts	Stand
6,000 Lumen LED PROLIGHT™ Work Light	515100	6,000	42W	Head Only
6,000 Lumen LED PROLIGHT™ w/ Floor Stand	515101	6,000	42W	Floor Stand
6,000 Lumen LED PROLIGHT™ Work Light w/ Tripod	515102	6,000	42W	Magnetic Sled
6,000 Lumen LED PROLIGHT™ Work Light w/ Tripod	515103	6,000	42W	Tripod
12,000 Lumen LED PROLIGHT™ Twin Head Work Light w/ Tripod	515104	6,000 x2	84W	Tripod



111500

## PROLIGHT™ XLE SERIES LED HEAVY DUTY WORK LIGHT

- IP65 indoor or outdoor use
- Operating temp: -30° to 120° F
- 5,000K LED with 50,000 Hr. life
- Aluminum body, tempered glass, and protective cage
- 120V, 5' - 18/3 SJTW Cord

Description	Model #	Lumens	Watts	Stand
6,500 Lumen LED PROLIGHT™ Work Light w/ Floor Stand	111500	6,500	50W	Floor Stand
6,500 Lumen LED PROLIGHT™ Work Light w/ Tripod	111505	6,500	50W	Tripod
6,500 Lumen LED PROLIGHT™ Work Light w/ Magnet	111507	6,500	50W	Magnet
13,000 Lumen LED PROLIGHT™ Twin Head Work Light	111000	6,500 x2	50W x2	Dual Head
13,000 Lumen LED PROLIGHT™ Twin Head Work Light w/ Tripod	111005	6,500 x2	50W x2	Dual Head w/ Tripod

# FLOOD & WORK LIGHTS

## PROLIGHT™ RECHARGEABLE LED WORK LIGHT

- Magnetic feet and hanging hook
- IP65, indoor or outdoor use
- Operating temp: -10° to 125° F
- 5 hour recharge time



516001

Description	Model #	Features	Lumens	Watt	Run Time	Replaceable Battery
PROLIGHT™ 100 LED Work Light	516001	Wall & car charger	800 LM - High 400 LM - Med 200 LM - Low	10	3 Hr. - High 6 Hr. - Med 12 Hr. - Low	Yes
PROLIGHT™ 100 LED Work Light Kit	516002	Kit with wall & car charger, 2 batteries, and a carrying bag	800 LM - High 400 LM - Med 200 LM - Low	10	3 Hr. - High 6 Hr. - Med 12 Hr. - Low"	Yes
PROLIGHT™ 200 LED Work Light	516003	Wall & car charger	1,700 LM - High 850 LM - Med 425 LM - Low	20	3 Hr. - High 6 Hr. - Med 12 Hr. - Low	Yes
PROLIGHT™ 200 LED Work Light Kit	516004	Kit with wall & car charger, 2 batteries, and a carrying bag	1,700 LM - High 850 LM - Med 425 LM - Low	20	3 Hr. - High 6 Hr. - Med 12 Hr. - Low	Yes
PROLIGHT™ Mini	511510	Magnetic feet 3 Modes	900 LM - High 450 LM - Low	10	5 Hr. - High 10 Hr. - Low	No
PROLIGHT™ Max	511512	Magnetic feet 3 Modes	1800 LM - High 1000 LM - Low	20	5 Hr. - High 10 Hr. - Low	No

## PROLIGHT™ 100 & 200 ACCESSORIES



416001

Description	Model #
Small ProLight Shop Bag	416003
Large ProLight Shop Bag	416004
ProLight 100 7.4V 4.4Ah Battery	416001
ProLight 200 7.4V 8.8Ah Battery	416002

## PROLIGHT™ RECHARGEABLE LED FOLDING WORK LIGHT

- Integrated lithium ion battery - 7.4V, 800 mAh
- IP65, indoor or outdoor use
- 50,000 hour LED life
- Operating temp: -10° to 125° F
- 5,000K light temperature



514125

Description	Model #	Accessories	Lumens	Watt	Run Time	Recharge Time
PROLIGHT™ Folding LED Work Light	514124	Wall Charger Car Charger	2,400 LM - High 1,200 LM - Med 800 LM - Low	30W	2.5 Hrs - High 3 Hrs. - Medium 8 Hrs. - Low	4 Hrs.
	514125	Wall Charger Car Charger Tripod				

# FLOOD & WORK LIGHTS



511000LITH

## SOLARIS LED HIGH POWERED RECHARGEABLE FLOOD LIGHTS

- Lithium Ion 14.8V, 36Ah
- IP65, Indoor or Outdoor use
- 50,000 Hour LED life
- Operating Temperature: -20° to 140° F
- 5,000K Light Temperature

Description	Model #	Lumens	Run Time	Recharge Time	Weight
Solaris Single Head LED Rechargeable Flood Light	511000LITH	16,000 LM 8,000 LM 4,000 LM 2,000 LM	2 Hr. 4 Hr. 8 Hr. 16 Hr.	7 Hrs.	12.5 Lbs



4110150

## PROLIGHT™ SLIM EXTREME LED FLOOD LIGHT

- 120V, 5' - 18/3 SJTW Cord
- IP65, Indoor or Outdoor use
- Operating Temperature: -40° to 105° F
- 5,000K LED with 50,000 Hr. Life
- Works with Tripod 311007

Description	Model #	Lumens	Watts
15,000 Lumen PROLIGHT™ Slim Extreme LED Flood Light	4110150	19,000	150W
22,000 Lumen PROLIGHT™ Slim Extreme LED Flood Light	4110220	29,000	220W
30,000 Lumen PROLIGHT™ Slim Extreme LED Flood Light	4110300	37,000	300W

*Tripod Sold Separately*



311001

## TRIPODS

Description	Model #	Max Height	Weight	Works With
Standard Tripod	311001	5'	7.5 lbs	411215, 511510, 514124, 514125, 516001, 516002, 516003, 516004
Medium Duty Tripod	311006	5'	8.5 lbs	411315, 411230, 411330, 411250, 411350, 111505, 515100, 515103, 515104
Heavy Duty Tripod	311007	6'	9.5 lbs	111005, 111508, 111509, 4110150, 4110220, 4110300

# FLOOD & WORK LIGHTS

## HALOGEN WORK LIGHTS

- 120V
- T3 bulbs are included and replaceable
- 18/3 SJTW



L33SW

Description	Model #	Lumens	Bulb	Feature
500W Halogen Work Light with S-Stand	L33SW	8,000	500W 4-5/8" T3	
700W Double Bulb Halogen Work Light with H-Stand	L5500SW	11,200	x1 500W and x1 200W T3 Bulb	Comes with replacement bulbs in built in compartment
500W Halogen Work Light with Tripod	L10SLEDSW	8,000	500W 4-5/8" T3	40"-67" Tripod
1000W Halogen Twin Head Work Light with Tripod	L14SLEDSW	16,000	500W 4-5/8" T3	40"-63" Tripod

## HALOGEN REPLACEMENT BULBS



L21

Description	Model #
500W 4-5/8" T3 Halogen Replacement Bulb	L16
6 Pack of 500W 4-5/8" T3 Halogen Replacement Bulb w/ Storage Case	L15
500W Rough Service T3 Halogen Replacement Bulb	L716SW
6 Pack 500W Rough Service T3 Halogen Replacement Bulb w/ Storage Case	L23SW

# ***INSTALLED LIGHTS***



# INSTALLED LIGHTS



111511

## LED DUSK-TO DAWN LIGHTS 120V

- Aluminum Housing and Polycarbonate Lens
- IP65, Weatherproof
- Replacement photocell
- Operating Temperature: -30° to 120° F
- 5,000K LED with 50,000 Hr. Life

Description	Model #	Lumens	Watt
3,850 Lumen LED Slim Extreme Flood Light	111511	3,850	35
6,050 Lumen LED Slim Extreme Flood Light	111512	6,050	55



111510

## DOCK LIGHTS

- 40" Reach
- Mounting information

Description	Model #	Lumens	Watt	Light Source	Light Color Temperature	Bulb Life	Features	Certification
500W Halogen Dock Light	L41HDSW	8,000 LM	500	4-5/8" T3 Bulb	3,000K	3,500 Hrs.	10' cord	UL
LED Dock Light	111510	1,700 LM	20	Integrated LED	5,000K	50,000 Hrs.	IP65	cUL
Replacement LED Dock Light Head	111515							



111513

## LED SHOP LIGHT

- Interlink up to 10 units
- Aluminum Housing
- Chain + S-hooks included

Description	Model #	Lumens	Watt	Light Color Temperature	Bulb Life	Interlinking Units	Weight
4,500 Lumen, 4' LED Shop Light	111513	4,500	42	5,000	50,000	10 Max	11.25 lbs

# ***CLAMPS & PERSONAL LIGHTING***



# CLAMPS & PERSONAL LIGHTING



56588802SW

## 100W, METAL SHIELD, HEAVY DUTY TROUBLE LIGHTS

- Built in outlet
- Metal hanging hook
- On/Off switch
- Oil and chemical resistant cord
- A23-Medium base bulb socket

Description	Model #
16/3 25' SJE0W Metal Shield Trouble Light	58578802SW
14/3 25' SJE0W Metal Shield Trouble Light	56578802SW
14/3 50' SJE0W Metal Shield Trouble Light	56588802SW



151SW

## CLAMP LIGHTS, 120V

- Vinyl coated clamp
- A23-medium base bulb socket
- Push-through switch
- Aluminum reflector

Description	Model #	Watts	Cord	Reflector
150W Clamp Light	151SW	150W Max	6' - 18/2 Cord	8-1/2" Reflector
150W Clamp Light	160SW	150W Max	6' - 18/2 Cord	5-1/2" Reflector
300W Porcelain Socket Brooder with Cage	166SW	300W	6' - 18/2 Cord	10-1/2" Reflector

# CLAMPS & PERSONAL LIGHTING



511924

## RECHARGEABLE LED HEAD LAMPS

- Lithium Ion Battery
- Auto distance dimming
- Spot and wide angle

Description	Model #	Lumens	Run Time	Recharge Time	IP Rating	Features
340 Lumen Rechargeable LED Headlamp	511924	340 - High 60 - Low	1.5 Hr. - High 130 Hr. - Low	5 Hr.	IP 66	Auto Distance Dimming, Spot and Wide Angle




514010

## LED HEAD LAMPS

- Auto distance dimming
- Spot and wide angle

Description	Model #	Lumens	Run Time	Battery Type	IP Rating	Features
180 Lumen Battery Powered LED Headlamp	514010	180 - High 35 - Low"	3 Hr. - High 130 Hr. - Low	x3 AAA	IP x4	Auto Distance Dimming, Spot and Wide Angle

## LED HEAD LAMPS AUTO DIMMING



514004

## LED FLASH LIGHTS

Description	Model #	Lumens	Run Time	Battery Type	IP Rating	Features
Carbon Fiber 500 Lumen LED Flashlight	CF004	500	7 Hour	x3 D	NA	IP44
Explorer 800 Lumen Rechargeable LED Flashlight	514004	800 LM - High 400 LM - Low	2 Hr. - High 28 Hr. - Low 7 Hr. - Strobe	Lithium Ion	5 Hrs.	IPX4
Panther XM-L Search Rechargeable Flash Light	511301	1,500 LM - High 750 LM - Low	3 Hr. - High 6 hr. - Low	Lithium Ion	5 Hr.	IP 54



514009

## INTRINSICALLY SAFE LED LIGHTS

- Lithium Ion Battery
- For use in hazardous areas
- Impact resistant construction

Description	Model #	Lumens	Run Time	Battery Type	IP Rating	Feature
125 Lumen Intrinsically Safe LED Flashlight	514007	125 LM - High 55 LM - Low	42.5 Hr. - High 80 Hr. - Low	x3 C	IP67	Waterproof
160 Lumen Intrinsically Safe LED Flashlight	514008	160 LM - High 65 LM - Low	6 Hr. - High 13 Hr. - Low	x4 AA	IP67	Waterproof
270 Lumen Intrinsically Safe Right Angle LED Flashlight	514009	270 LM - High 135 LM - Low	6.5 Hr. - High 13 Hr. - Low	x4 AA	IP54	Waterproof
200 Lumen Intrinsically Safe LED Head Lamp	514012	200 LM - High 100 LM - Low	2.5 Hr. - High 4.5 Hr. - Low	x3 AAA	IP67	Waterproof















**Southwire™**

TOOLS & EQUIPMENT

# 2019 LIGHTING SOLUTIONS CATALOG

**GET SOCIAL WITH US:**



**/SOUTHWIRETOOLS  
/SOUTHWIRETOOLSLATINO**



**@SOUTHWIRETOOLS**



**@SOUTHWIRETOOLS**



**SOUTHWIRETOOLS**

**SOUTHWIRETOOLS.COM | 1-855-SWTOOLS**

All Trademarks or Registered Trademarks (TM/®) are owned or licensed by Southwire Company.  
Any other ™/®- Trademark or Registered Trademark of Southwire Company.