

# ONQ



## STRUCTURED WIRING & CONNECTIVITY GUIDE

# 2025



#LegrandImprovingLives

 **legrand**<sup>®</sup>

ONQ



# INFRASTRUCTURE SOLUTIONS

As the industry leader in structured wiring, Legrand provides the proven, practical solutions preferred by installers and major home builders across the country. Our comprehensive ON-Q product offering — which includes wall plates, jacks, HDMI™ cables, straps, tools, modules, enclosures & home theater solutions — simplifies installations and reduces time on site. We specialize in meeting the right specifications for any project — residential or light commercial — with solutions that exceed your needs. From single-family homes to apartments, townhomes to condominiums, Legrand has the professional answer for any project.



## CONTENTS

ENCLOSURES.....	4	WALL PLATES .....	20
PLASTIC ENCLOSURES.....	4	STRAPS.....	21
METAL ENCLOSURES .....	11	SURFACE MOUNT BOXES.....	21
ACCESSORIES.....	7	PRE-MOLDED WALL PLATES & STRAPS.....	22
VIDEO & VOICE DISTRIBUTION.....	13	PRE-CONFIGURED PLATES & STRAPS .....	23
VOICE & VIDEO MODULES.....	13	HOME THEATER SOLUTIONS.....	23
HOME NETWORKING .....	14	AV CABLING.....	26
NETWORK MODULES.....	14	HDMI™ CABLES .....	26
POWER MANAGEMENT .....	15	AUDIO/VIDEO CABLES .....	27
DATA CONNECTIVITY .....	16	PATCH CABLES .....	26
LOW VOLTAGE BRACKETS .....	16	CABLE TIES & PATCH PANELS.....	28
KEYSTONE WALL PLATES.....	17	INSTALLATION TOOLS & CONNECTORS.....	29
		RESOURCES & SUPPORT.....	30

# ENCLOSURES

## DUAL-PURPOSE ENCLOSURES

- The 9" & 17" Dual-Purpose In-Wall Enclosure are engineered to provide storage of structured wiring and AV components
- Constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations
- Available in 9" or 17" sizes, perfect for areas directly behind a TV or other media locations



ENP0900NA



ENP1700NA



PART NO.	DESCRIPTION
ENP0900NA	Dual-Purpose 9" In-Wall Enclosure
ENP0905NAV1	Dual-Purpose 9" In-Wall Enclosure with 5" Mounting Plate
ENP1700NA	Dual-Purpose 17" In-Wall Enclosure
ENP1705NAV1	Dual-Purpose 17" In-Wall Enclosure with 5" Mounting Plate



AC1050  
5" Mounting Plate



ENP0905NAV1



ENP1705NAV1



# ENCLOSURES

## PLASTIC ENCLOSURES

- The ON-Q line of plastic enclosures provide Wi-Fi transparent infrastructure to properly organize, protect & support the home's wired and wireless connected systems
- Universal mounting grid maximizes compatibility with third party products without additional brackets
- Extra venting along vertical plane of door allows for superior heat dissipation
- Reversible door snaps easily into trim ring without tools, swings a full 180 degrees
- Lockable with included screws or Optional Keyed Lock (36447801)




**NEW**

DESCRIPTION	15" Enclosure	20" Enclosure	30" Enclosure	42" Enclosure
Enclosure Dimensions	16.1" L x 15.05" W x 4.13" D	22.2" L x 17.5" W x 5.5" D	32.2" L x 17.5" W x 5.5" D	44.2" L x 17.5" W x 5.5" D
Plastic Enclosure with Hinged Door & Trim Ring	ENP1550DNA	ENP2050NA	ENP3050NA	ENP4250NA
Plastic Hinged Door & Trim Ring Only	N/A	ENP2060NA	ENP3060NA	ENP4260NA
Plastic Enclosure Only	N/A	ENP2080NA	ENP3080NA	ENP4280NA
Plastic Hinged Door & Trim Ring Only (Pack of 5)	ENP15605DNA	ENP20605NA	ENP30605NA	ENP42605NA
Plastic Enclosure Only (Pack of 5) - No Cover	ENP15805DNA	ENP20805NA	ENP30805NA	ENP42805NA
Trim Ring, For Replacement Only	N/A	ENP2001NA	ENP3001NA	ENP4201NA




**AC1041**  
Fiber Management  
Spool - Pair




**AC1052CC2**  
Cable Management  
Clips - Pair



**AC1060**  
Shelf Mounting Bracket



**AC1051RCKH4**  
Forward Combo Pack -  
Keyhole Post Clips and  
Small Device Mounting Clamps



**AC1051RC20**  
Forward Small Device  
Mounting Clamps



**AC1050**  
5-Inch Mounting Plate  
with 1.5-Inch Elevation



**AC1031**  
Enclosure Power Strip



**AC1034**  
2-Inch Rubber Knockout  
Grommet 5-Pack

# ENCLOSURE INSIDE DEVICE MOUNTING ACCESSORIES



PART NO.	DESCRIPTION	DUAL PURPOSE ENCLOSURES	PLASTIC ENCLOSURES	METAL ENCLOSURES
36489601	Universal Mounting Plate, Half Width	●	●	●
36490401	Universal Mounting Plate, Full Width	●	●	●
AC1040F	Plastic Universal Mounting Plate Kit	17" ONLY	●	●
AC1042	MDU Mounting Bracket	●	●	●
AC1043	DIN Rail - Half Width	●	●	
AC1050	5" Mounting Plate with 1.5" of Elevation	●	●	
AC1050EMK	5" Elevated Mounting Plate Combo Kit	●	●	
AC1060	Shelf Mounting Bracket, 10 Pack (AC106010)	●	●	●
AC1060L5	Gateway Shelf with Gigabit Network Switch	●	●	●
AC1051RC20	Forward Small Device Mounting Clamp (Pack of 20)	COMPATIBLE WITH: AC1050, AC1060, AC1052CC		
AC1051RCKH4	Small Device Mounting Clamp & Keyhole Post Clips (Combo Pack)			
AC1051KH20	Forward Keyhole Post Clip (Pack of 20)			

## ENCLOSURE GROMMETS



PART NO.	DESCRIPTION	DUAL PURPOSE ENCLOSURES	PLASTIC ENCLOSURES	METAL ENCLOSURES
AC1034	2" Rubber Grommet Pack for Plastic Enclosures (Pack of 5)	●	●	
F2242	2.5" Grommet Ring			●
F2249	2.5" Knockout Plug			●





### LATCH AND LOCK KITS



PART NO.	DESCRIPTION	DUAL PURPOSE ENCLOSURES	PLASTIC ENCLOSURES	METAL ENCLOSURES
36447801	Replacement Lock Assembly & 2 Key Kit		●	●



### CABLE MANAGEMENT



PART NO.	DESCRIPTION	DUAL PURPOSE ENCLOSURES	PLASTIC ENCLOSURES	METAL ENCLOSURES
36349101	Velcro Tie Strap (Pack of 50)	●	●	●
AC103520	Cable Management Clips (Pack of 20)	●	●	
AC1041	Fiber Management Spools (Pair)	●	●	●
AC1052CC2	Cable Channel (Pack of 2)		●	



# ENCLOSURES

## METAL ENCLOSURES

- Flush and surface installation options
- Flanged covers hide drywall openings
- UL listed for fire and security alarm equipment
- Made in the USA
- Cable guard insert protects cables and equipment from dust, paint and debris between rough-in and trim out
- Includes 3 powder-coated openings for cable pass-through




DESCRIPTION	12" Enclosure	14" Enclosure	20" Enclosure	28" Enclosure	42" Enclosure
Enclosure Dimensions	12.13"H x 14.25" W x 3.6"D	14" H x 14.25" W x 3.6" D	20" H x 14.25" W x 3.6" D	28" H x 14.25" W x 3.6" D	42" H x 14.25" W x 3.6" D
Enclosure with Screw-On Cover	EN1200	EN1400	EN2000	EN2800	EN4200
Enclosure with Hinged Cover	N/A	EN1450	EN2050	EN2850	EN4250
Enclosure, Only	N/A	EN1480	EN2080	EN2880	EN4280
Screw On Cover, Only	N/A	EN1420	EN2020	EN2820	EN4220
Hinged Cover, Only	N/A	EN1460	EN2060	EN2860	EN4260
Enclosure Depth Extender**	N/A	N/A	N/A	36445003	36445004

\* This enclosure has five knockout locations and allows vertical alignment of two enclosures for cable pass-through.

\*\* Extenders add 2.5" of enclosure depth.


# ENCLOSURES

- Knockouts include screwdriver holes for easy removal
- Includes four self-tapping screws for mounting and optional hardware to lock the cover
- Multiple compatible video, voice, and data distribution modules available
- Flush and surface-mount installation options



## PLASTIC MDU ENCLOSURE

PART NO.	DESCRIPTION
EN0800	8" MDU Enclosure with Cover
EN0802	8" MDU Enclosure Kit (6 phone, 4 video) INCLUDES: (1) ENCLOSURE AND COVER, (1) 6-WAY PHONE MODULE TM0106, (1) 4-WAY COAX SPLITTER VM0204
EN0803	8" MDU Enclosure Kit (6 phone, 4 video) INCLUDES: (1) ENCLOSURE AND COVER, (1) 6-WAY PHONE MODULE TM0106, (1) 6-PORT CAT 5E DATA BOARD AC0506, (1) 4-WAY COAX SPLITTER VM0204
EN0804	8" MDU Enclosure Kit (6 phone, 4 video) INCLUDES: (1) ENCLOSURE AND COVER, (1) 6-WAY PHONE MODULE TM0106, (1) 6-PORT CAT 6 DATA BOARD AC0606, (1) 4-WAY COAX SPLITTER VM0204
EN0806	8" MDU Enclosure Bulk Pack (6)



## MDU ENCLOSURE MODULES

PART NO.	DESCRIPTION
AC1042	MDU Mounting Bracket
AC0506	6-Port Cat 5e Data Board (For use with EN0800)
AC0606	6-Port Cat 6 Data Board (For use with EN0800)
TM0106	6-Way Telephone Board (For use with EN0800)
VM0106	6-Way Vertical 1 GHz Splitter (For use with EN0800)
VM0108	8-Way Vertical 1 GHz Splitter (For use with EN0800)
VM0204	4-Way Vertical 2 GHz Splitter (For use with EN0800)
VM0206	6-Way Vertical 2 GHz Splitter (For use with EN0800)
VM0208	8-Way Vertical 2 GHz Splitter (For use with EN0800)

# VIDEO & VOICE DISTRIBUTION

## COMBO MODULES

DESCRIPTION	Basic 6x4 Combo (110 Punchdown)	10x8 Combo with RJ31X (RJ45)	10x8 Combo with RJ31X (110 Punchdown)	10x8 Combo with RJ31X MoCA Optimized	Trio Combo Module with Cat5e Data	Trio Combo Module with Cat6e Data
PART NO.	36440004	CO1045	CO1110	CO2110-V1	CO1156	CO1166
Telecom Outlets	6	10	10	10	6	6
Video Outlets	4	8	8	8	8	8
Telecom Connections	110 Punchdown	RJ45	110 Punchdown	110 Punchdown	110 Punchdown	110 Punchdown
RJ31X Line Seizure	N	Y	Y	Y	Y	Y
Bandwidth	1 GHz	1 GHz	1 GHz	1.675 GHz	2 GHz	2 GHz
Dimensions	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"	5 1/8" x 6 1/2"	6 3/4" x 6 1/2"	6 3/4" x 6 1/2"

## VOICE MODULES

PART NO.	DESCRIPTION
TM1110	10-Way IDC Telephone Module with RJ31X
TM1045	10-Way RJ45 Telephone Module with RJ31X
126706201V1	6-Way Basic Telecom Module with RJ31X



TM1110



TM1045



1267062-01-V1



VM1000



VM1002

## VIDEO MODULES

PART NO.	DESCRIPTION
VM1000	1x4 Enhanced Passive Video Splitter/Combiner
VM1002	1x8 Enhanced Passive Video Splitter/Combiner

## VIDEO SPLITTERS

PART NO.	DESCRIPTION
NOTE: POWER SUPPLY INCLUDED	
VM2202V1	Two-Way Digital Cable Splitter with Coax Network Support
VM2203V1	Three-Way Digital Cable Splitter with Coax Network Support
VM2204V1	Four-Way Digital Cable Splitter with Coax Network Support



VM2202V1



VM2203V1




VM2204V1

# HOME NETWORKING



AC1000



AC1001



AC1012



AC1013



AC1014



AC1015



AC1058



AC1068



AC106A6

PART NO.	DESCRIPTION
AC1000	6-Port Cat 5e Network Interface Module
AC1001	6-Port Network Interface Module (Unpopulated)
AC1012	6-Port Cat 5e Network Interface Module
AC1013	6-Port Cat 6 Network Interface Module
AC1014	12-Port Cat 5e Network Interface Module
AC1015	12-Port Cat 6 Network Interface Module
AC1058	8-Port Cat 5e Network Interface Module
AC1068	8-Port Cat 6 Network Interface Module
AC106A6	6 Port Cat 6a Network Interface Module



# POWER MANAGEMENT



PW7725



PW1030



PW1060

## POWER SUPPLIES

PART NO.	DESCRIPTION
PW7725	12VDC, 30W Power Supply
PW1030	24VDC, 30W Power Supply
PW1060	24VDC, 60W Power Supply



36456902V1



F7526



PW1006



CPT7526WHR6

## ACCESSORIES

PART NO.	DESCRIPTION
36456902V1	<b>Surge Protected Duplex Power Kit</b> INCLUDES: (1) SURGE PROTECTED DUPLEX OUTLET, (1) METAL JUNCTION BOX, AND (1) FACEPLATE NOTE: TAMPER RESISTANT
F7526	<b>Duplex Power Kit</b> INCLUDES: (1) DUPLEX OUTLET, (1) METAL JUNCTION BOX AND (1) FACEPLATE KIT NOTE: TAMPER RESISTANT
PW1006	<b>Twin Power Supply Bracket</b>
CPT7526WHR6	<b>Enclosure In-Wall Power Kit, 6ft. - White</b> INCLUDES: JUNCTION BOX WITH PRE-WIRED OUTLET, 6FT. IN-WALL RATED CABLE, POWER INPUT MODULE, 6FT. POWER CORD, DRYWALL SAW AND HARDWARE



AC1031



AC1062

## POWER MODULES

PART NO.	DESCRIPTION
AC1031	Enclosure Power Strip Module, Half Width
AC1062	6 Outlet On-Wall and Enclosure Surge Protector

# DATA CONNECTIVITY

## LOW VOLTAGE BRACKETS



## NEW CONSTRUCTION

PART NO.	DESCRIPTION
SLV1R	1-Gang, LV Bracket w/Nail, with Quick/Click'
PLV1S	1-Gang, LV Bracket w/Screw, New Const.
SLV1B	1-Gang, LV Bracket Face Mount, with Quick/Click'
SLV2B	2-Gang, LV Bracket Face Mount, with Quick/Click'
AC100901	1-Gang, LV Bracket w/Nail, New Const.
AC100902	2-Gang, LV Bracket, Face Mount, New Const.
AC100911	1-Gang, LV Bracket, Face Mount, New Const.
AC100912	2-Gang, LV Bracket w/Nail, New Const.
SDV2B	2-Gang, LV Bracket, Face Mount, with Quick/Click'
PDV2B	2-Gang, LV Bracket, Face Mount



## RETROFIT

PART NO.	DESCRIPTION
SLV1W	1-Gang, Metal Wing, with Quick/Click'
AC101001	1-Gang, LV Bracket, Retrofit
SLV2W	2-Gang, Metal Wing, with Quick/Click'
AC101002	2-Gang, LV Bracket, Retrofit
SLV3W	3-Gang, Metal Wing, with Quick/Click'
AC101003	3-Gang, LV Bracket, Retrofit
P100WD	1-Gang LV Bracket Extender

## DIVIDERS AND EXTENDERS

PART NO.	DESCRIPTION
LVDIV1	LV Box Divider (12 Pack)
EXT1	1-Gang, 1/4" Box Extender (10-Pack)
EXT2	2-Gang, 1/4" Box Extender (10-Pack)

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION.



# DATA CONNECTIVITY

## KEYSTONE INSERTS



### PUNCH & GO TOOL

- SEAT AND CUT ALL WIRES AT ONCE WITH A SQUEEZE OF THE HANDLE.
- CONSISTENT TERMINATIONS EVERY TIME.
- NO MORE COMPROMISED CONNECTIONS OR WASTED JACKS.
- NEVER AGAIN PUNCH INTO THE PALM OF YOUR HAND OR THROUGH DRYWALL. THE AC3400 IS FOR USE EXCLUSIVELY WITH OUR LINE OF WP3475, WP3476 AND WP346A QUICK CONNECT JACKS.

## QUICK CONNECT INSERTS

PART NO.	DESCRIPTION
AC3400	<b>Punch &amp; Go Tool</b> IMPROVES TERMINATION SPEEDS, REDUCES COMPROMISED CONNECTIONS AND INCREASES PRODUCTIVITY OF ANY QUICK CONNECT DATA INSERT
WP346aXX	<b>Cat 6a Quick Connect RJ45 Keystone Insert</b>
WP3473XX	<b>RJ25 6-Position, 6-Conductor Telephone Keystone Insert</b> 10 COUNT BULK PACKS IN WH AND LA (WP3473XX10)
COLORS: BK, BR, GY, IV, LA, WH	
WP3475XX	<b>Cat 5e Quick Connect RJ45 Keystone Connector</b> 10 COUNT BULK PACKS IN WH AND LA (WP3475XX10) 50 COUNT BULK PACKS IN WH, LA AND BE (WP3475XX50) 100 COUNT BULK PACKS IN WH (WP3475WH-00)
COLORS: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE	
WP3476XX	<b>Cat 6 Quick Connect RJ45 Keystone Connector</b> 10 COUNT BULK PACKS IN WH, LA (WP3476XX10) 50 COUNT BULK PACKS IN WH, LA AND BE (WP3476XX50) 100 COUNT BULK PACKS IN WH (WP3476WH100)
COLORS: BE, BK, BR, GY, IV, LA, OR, RE, WH	
NOTE: THESE INSERTS ARE COMPATIBLE WITH THE AC3400 PUNCH & GO TOOL WHICH ALLOW FOR ALL WIRES TO BE TERMINATED AT ONCE.	

## OTHER INSERTS




PART NO.	DESCRIPTION
WP3425XX	<b>RJ25 6P6C Keystone Connector</b>
COLORS: BK, BR, IV, LA, WH	
WP3450XX	<b>Cat 5e RJ45 Keystone Connector</b>
COLORS: BE, BK, BR, GY, IV, LA, OR, RE, WH	
WP3451XX	<b>Cat 5e RJ45 Keystone Coupler</b>
COLORS: BK, WH	
WP3458XX	<b>Cat 5e Keyed RJ45 Keystone Connector</b>
COLORS: BK, BR, IV, LA, WH	
WP3460XX	<b>Cat 6 RJ45 Keystone Connector</b>
WP3550XX	<b>Snap &amp; Go Cat 5e Keystone Connector</b>
WP3560XX	<b>Snap &amp; Go Cat 6 Keystone Connector</b>
COLORS: BE, BK, BR, GY, IV, LA, OR, RE, WH	

## COAX VIDEO INSERTS



PART NO.	DESCRIPTION
WP3479XX	<b>Non-Recessed Coax Keystone F-Connector (1 GHz)</b> 10 COUNT BULK PACKS IN WH OR LA (WP3479XX10) 50 COUNT BULK PACK IN WH OR LA (WP3479XX50)
WP3480XX	<b>Recessed Gold F-Connector (3 GHz)</b>
WP3481XX	<b>Recessed Nickle F-Connector (3 GHz)</b> 10 COUNT BULK PACKS IN WH OR LA (WP3481XX10) 50 COUNT BULK PACK IN WH (WP3481WH50)
WP3482XX	<b>Recessed Self-Terminating Keystone F-Connector (1 GHz)</b>
COLORS: BK, BR, IV, LA, WH	

COLOR KEY:



NOTE: Suffixes should be added to the end of all applicable part numbers.

# DATA CONNECTIVITY



WP3461WH



WP3462WH



WP3464WH



WP3466WH



WP124KXX



WP3455WH



WP1215WH



WP3457WH



WP3456WH



WP1220WH

## KEYSTONE AUDIO/VIDEO INSERTS

PART NO.	DESCRIPTION
WP3461XX	White Keystone RCA-to-F Connector
WP3462XX	Red Keystone RCA-to-F Connector
WP3464XX	Blue Keystone RCA-to-F Connector
WP3466XX	Purple Keystone RCA-to-F Connector

COLORS: BK, BR, IV, LA, WH

WP124KXX	4k HDMI™ Cable Keystone Coupler 10 COUNT BULK PACK IN WH (WP124KWH10)
WP3455XX	Blank Keystone Insert
WP1215XX	3.5MM Stereo Coupler
WP3457XX	Audio Keystone Binding Post, Pair
WP3456XX	Speaker Keystone Binding Post


COLORS: BK, BR, IV, LA, WH

## USB & FIBER INSERTS

PART NO.	DESCRIPTION
WP1220XX	USB 2.0 A/A Coupler

COLORS: BK, BR, IV, LA, WH

COLOR KEY:



NOTE: Suffixes should be added to the end of all applicable part numbers.

# DATA CONNECTIVITY

## KEYSTONE WALL PLATES



PART NO.	DESCRIPTION
WP3401XX	<b>1-Gang, 1-Port Wall Plate</b> 10 COUNT BULK PACK IN WH OR LA (WP3401XX10) 25 COUNT BULK PACK IN WH OR LA (WP3401XX25)
WP3402XX	<b>1-Gang, 2-Port Wall Plate</b> 10 COUNT BULK PACK IN WH OR LA (WP3402XX10) 25 COUNT BULK PACK IN WH OR LA (WP3402XX25)
WP3403XX	<b>1-Gang, 3-Port Wall Plate</b> 10 COUNT BULK PACK IN WH (WP3403WH10)
WP3404XX	<b>1-Gang, 4-Port Wall Plate</b> 10 COUNT BULK PACK IN WH (WP3404WH10)
WP3406XX	<b>1-Gang, 6-Port Wall Plate</b> 10 COUNT BULK PACK IN WH (WP3406WH10)

COLORS: BK, BR, IV, LA, WH, GY

WP3212XX	<b>2-Gang, 12-Port Wall Plate</b>
COLORS:	IV, LA, WH
DIMENSIONS:	1-GANG: 2.9375" X 4.6875"    2-GANG: 8.375" X 4.6875"

## STAINLESS STEEL WALL PLATES



PART NO.	DESCRIPTION
WP3401SS	<b>1-Gang, 1-Port Wall Plate, Stainless Steel</b>
WP3402SS	<b>1-Gang, 2-Port Wall Plate, Stainless Steel</b>
WP3403SS	<b>1-Gang, 3-Port Wall Plate, Stainless Steel</b>
WP3404SS	<b>1-Gang, 4-Port Wall Plate, Stainless Steel</b>
WP3406SS	<b>1-Gang, 6-Port Wall Plate Stainless Steel</b>

DIMENSIONS: 1-GANG: 2.9375" X 4.6875"

## OVERSIZED WALL PLATES



PART NO.	DESCRIPTION
WP3300XX	<b>1-Gang, Blank Oversized Wall Plate</b>
WP3301XX	<b>1-Gang, 1-Port Oversized Wall Plate</b> 10 COUNT BULK PACK IN WH (WP3301WH10)
WP3302XX	<b>1-Gang, 2-Port Oversized Wall Plate</b> 10 COUNT BULK PACK IN WH (WP3302WH10)
WP3303XX	<b>1-Gang, 3-Port Oversized Wall Plate</b>
WP3304XX	<b>1-Gang, 4-Port Oversized Wall Plate</b>
WP3306XX	<b>1-Gang, 6-Port Oversized Wall Plate</b>

COLORS: WH, LA  
DIMENSIONS: 1-GANG: 3.3125" X 5.0625"


## LABELED WALL PLATES



PART NO.	DESCRIPTION
KTPDL1XX	<b>1-Gang, 1-Port Keystone Labeled Wall Plate</b>
KTPDL2XX	<b>1-Gang, 2-Port Keystone Labeled Wall Plate</b>

COLORS: I, LA, W  
DIMENSIONS: 1-GANG: 2.9375" X 4.6875"

COLOR KEY:



NOTE: Suffixes should be added to the end of all applicable part numbers.

# DATA CONNECTIVITY

## WALL PLATES




## STANDARD DECORATOR WALL PLATES

PART NO.	DESCRIPTION
TP13XXX	1-Gang Blank Wall Plate
TP23XXX	2-Gang Blank Wall Plate
TP26XXX	1-Gang Decorator Wall Plate
TP262XXX	2-Gang Decorator Wall Plate
TP263XXX	3-Gang Decorator Wall Plate
TP264XXX	4-Gang Decorator Wall Plate

COLORS: BK, I, LA, W, GRY (FOR BROWN, LEAVE BLANK)  
 DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"  
 3-GANG: 6.563" x 4.6875 4-GANG: 8.375" x 4.6875"

## JUMBO DECORATOR WALL PLATES



PART NO.	DESCRIPTION
TPJ13XXX	Jumbo 1-Gang Blank Wall Plate
TPJ26XXX	Jumbo 1-Gang Wall Plate
TPJ262XXX	Jumbo 2-Gang Wall Plate
TPJ263XXX	Jumbo 3-Gang Wall Plate
TPJ264XXX	Jumbo 4-Gang Wall Plate

COLORS: BK, I, LA, W, GRY (FOR BROWN, LEAVE BLANK)  
 DIMENSIONS: 1-GANG: 3.3125" x 5.0625" 2-GANG: 5.125" x 5.0625"  
 3-GANG: 6.9375" x 5.0625" 4-GANG: 8.75" x 5.0625"

## RADIANT WALL PLATES



PART NO.	DESCRIPTION
RWP26XX	Screwless Wall Plate, 1-Gang
RWP262XX	Screwless Wall Plate, 2-Gang
RWP263XX	Screwless Wall Plate, 3-Gang
RWP264XX	Screwless Wall Plate, 4-Gang

COLORS: W, LA, I, GRY, BK, NICC6, DBCC6  
 (FOR BROWN, LEAVE BLANK)

COLOR KEY: NOTE: Suffixes should be added to the end of all applicable part numbers. OMIT COLOR CODE TO ORDER BROWN DEVICE.

# DATA CONNECTIVITY

## STRAPS



WP3410WH



WP3411WH



WP3412WH



WP3413WH



WP3414WH



WP3416WH

PART NO.	DESCRIPTION
WP3410XX	Blank Decorator Outlet Strap
WP3411XX	1-Port Decorator Outlet Strap\ 10 COUNT BULK PACK IN WH (WP3411WH10)
WP3412XX	2-Port Decorator Outlet Strap 10 COUNT BULK PACK IN WH (WP3412WH10)
WP3413XX	3-Port Decorator Outlet Strap 10 COUNT BULK PACK IN WH (WP3413WH10)
WP3414XX	4-Port Decorator Outlet Strap
WP3416XX	6-Port Decorator Outlet Strap

COLORS: BK, BR, IV, LA, WH, GY

## SURFACE MOUNT BOXES



WP3409WH



WP3501WH



WP3502WH



WP3504WH



WP3506WH

PART NO.	DESCRIPTION
WP3409XX	Single Gang Surface Mount Box
WP3501XX	Surface Mount Box 1-Port
WP3502XX	Surface Mount Box 2-Port
WP3504XX	Surface Mount Box 4-Port
WP3506XX	Surface Mount Box 6-Port

COLORS: IV, LA, WH

# DATA CONNECTIVITY

## PRE-MOLDED WALL PLATES & STRAPS



PART NO.	DESCRIPTION
TPTE2XX	Dual 2-Line Telephone Jack Wall Plate (4 Conductor Configuration)
COLORS:	BK, I, LA, W
WMTE14X	Modular Wall Mount Telephone Jack for Hanging Phones
COLORS:	W, LA, I
TPCATVXX	1 GHz Coaxial Connector & Wall Plate
COLORS:	I, LA, W, BK
TPCATV2XX	Dual 1 GHz Coaxial Connector Wall Plate
COLORS:	I, LA, W, BK
TPTELVXX	1 GHz Coaxial Connector & 2-Line Phone Jack Wall Plate
COLORS:	I, LA, W, BK
26TELVCC10	1 GHz Coaxial Connector & 2-Line Phone Jack with 1-Piece Molded Decorator Plate
COLORS:	BK, I, LA, W
WP2002WH	1-Gang 6P6C RJ25 Terminating Wall Phone Plate
COLORS:	WH
WP3467XX	Keystone Wall Phone Plate
COLORS:	WH, SS (STAINLESS STEEL)
26TE14XX	Decorator 2-Line Telephone Jack (4 Conductor Configuration)
COLORS:	I, W
26TE16XX	Decorator 3-Line Telephone Jack (6 Conductor Configuration)
COLORS:	I, W
26CATVXX	Decorator 1GHz Coaxial Connector
COLORS:	I, LA, W

## PRE-MOLDED WALL PLATES & STRAPS



PART NO.	DESCRIPTION
WP3210XX	1-Port Strap, 1RJ45
WP3211XX	2-Port Strap Phone/TV
WP3220XX	2-Port Strap Phone/Data
WP3422XX	4-Port Strap Phone/Data, TV/AUX
COLORS:	BK, LA, WH

COLOR KEY:



NOTE: Suffixes should be added to the end of all applicable part numbers. OMIT COLOR CODE TO ORDER BROWN DEVICE.

# HOME THEATER SOLUTIONS

## HOME THEATER WALL PLATES & STRAPS



F9004WH



F9005WH



F9006WH



F9008WHV1



WP9009XXV1



WP1011WH

PART NO.	DESCRIPTION
F9004XX	5.1 Home Theater Strap
COLORS:	BK, BR, IV, LA, WH
F9005XX	2-Speaker Connection Strap
COLORS:	BK, BR, IV, LA, WH
F9006XX	Single Speaker Connection Strap
COLORS:	BK, BR, IV, LA, WH
F9008XXV1	5.1 Home Theater Strap with Wall Plate
COLORS:	LA, WH
WP9009XXV1	7.1 Home Theater Strap with Wall Plate
COLORS:	DM, LA, WH
WP1011WH	Pre-Configured HDMI™ 2 Port Strap
COLORS:	BK, LA, WH

## CABLE ACCESS WALL PLATES



WP1014WH



WP1014XXV1



WP9001WH



WP9002WH

PART NO.	DESCRIPTION
WP1014XX	Cable Access Strap
	5 Count Bulk Pack in WP1014WH5 (5 Pack)
WP1014XXV1	Cable Access Strap with Wall Plate
COLORS:	BK, LA, WH
WP9001XX	Single Gang Bullnose Wall Plate
COLORS:	BK, LA, WH
WP9002XX	Double Gang Bullnose Wall Plate
COLORS:	BK, LA, WH

## CABLE ACCESS WALL GROMMETS

**NEW**



HT1020WH4PK



HT1015WH10PK



HT3401WH4PK



HT3401SWH2PK



WORKS WITH KEYSTONE INSERTS

PART NO.	DESCRIPTION
HT1020WH4PK	Mini Pass-Through Grommet - White, 4 Pack
	THE MINI PASS-THROUGH GROMMET UTILIZES WING CLAMPS THAT ENGAGE BEHIND THE DRYWALL TO PREVENT SLIP OR FALL OUT.
HT1015WH10PK	Flexible Mini Pass-Through Grommet - White, 10 Pack
	THE FLEXIBLE MINI GROMMET HAS DIRECTIONAL RIBS THAT CREATE A SECURE FRICTION FIT WITH THE DRYWALL OPENING PREVENTING SLIP OR FALL OUT.
HT3401WH4PK	Blank In-Wall Keystone Grommet - White, 4 Pack
	COMPATIBLE WITH KEYSTONE INSERTS, INCLUDING HDMI™, CAT5, CAT5E, CAT6, AND MORE. WALL, CEILING, OR DESK MOUNTED. QUICK AND EASY TO INSTALL.
HT3401SWH2PK	In-Wall Keystone Grommet - White, 2 Pack
	INCLUDES 2 IN-WALL KEYSTONE GROMMETS (BLANK) AND 1 HOLE DRILL SAW ATTACHMENT. COMPATIBLE WITH KEYSTONE INSERTS, INCLUDING HDMI™, CAT5, CAT5E, CAT6, AND MORE. WALL, CEILING, OR DESK MOUNTED.

COLOR KEY:



NOTE: Suffixes should be added to the end of all applicable part numbers. OMIT COLOR CODE TO ORDER BROWN DEVICE.

# DATA CONNECTIVITY



HT2102XXV1



HT21USBWHV1



HT2103WHV1



HT2004WHV1



AC2406BK

## HOME THEATER CONNECTIONS

PART NO.	DESCRIPTION
HT2102XXV1	<b>Flat Panel TV Connection Kit</b> INCLUDES: (1) HDMI™ 2-PORT STRAP, (1) CABLE ACCESS STRAP (2) WALL PLATES, (1) 9FT HIGH SPEED HDMI™ CABLE. NOW AVAILABLE IN WH AND BK
HT21USBWHV1	<b>In-Wall TV Connection Kit with USB</b> INCLUDES: (1) RECESSED BRACKET WITH CABLE ACCESS STRAP, (1) 1-GANGE DECORATOR WALL PLATE, (1) 15 AMP, 125 VOLT USB OUTLET, (1) 1-GANG ELECTRICAL BOX, (1) CUT-OUT TEMPLATE
HT2103WHV1	<b>Home Theater Connection Kit</b> INCLUDES: (1) RECESSED BRACKET WITH CABLE ACCESS STRAP, (1) 1-GANG WALL BOX, (1) TAMPER RESISTANT DECORATOR RECEPTACLE, (1) WALL PLATE
HT2004WHV1	<b>Dual Cable Access Kit</b> INCLUDES (2) CABLE ACCESS BRUSH STRAPS AND (2) CORRESPONDING WALL PLATES

COLOR KEY: BK WH/  
W NOTE: Suffixes should be added to the end of all applicable part numbers.

## TOSLINK

PART NO.	DESCRIPTION
AC2406BK	6 Feet Toslink w/Mini Audio Cable

### BEFORE

### AFTER





# HOME THEATER SOLUTIONS

## IN-WALL TV POWER KITS

PART NO.	DESCRIPTION
HT22U2WHR12	<b>Long Range In-Wall Pro Power and Cable Management Kit White</b>  INCLUDES: (1) UNASSEMBLED POWER OUTPUT MODULE, (1) 12 FT PREWIRED CORD, (2) UNASSEMBLED POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
HT22U2WHR6	<b>Pro TV In-Wall Power &amp; Cable Management Kit, White</b>  INCLUDES: (1) UNASSEMBLED POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) UNASSEMBLED POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
HT22U2BKR6	<b>Pro TV In-Wall Power &amp; Cable Management Kit, Black</b>  (1) UNASSEMBLED POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) UNASSEMBLED POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
HT22U2WHR6C	<b>Pro TV In-Wall Power &amp; Cable Management Kit with (2)10Ft HDMI™</b>  (1) UNASSEMBLED POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) UNASSEMBLED POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE, (2) 10FT HDMI™ CABLES
HT2202WHV1	<b>Pro TV In-Wall Power &amp; Cable Management Kit</b>  POWER OUTPUT MODULE (INCLUDES 6 FT. PRE-WIRED CORD), POWER INPUT MODULE, DRYWALL BRACKET, 6FT POWER CORD, AND CUT-OUT TEMPLATE WITH COMPLETE INSTRUCTION GUIDE
HT2302BWH	<b>In-Wall TV Connection Kit (Blank)</b>  INCLUDES TOP BOX WITH REMOVABLE TRIM RING, 1 GANG OLD-WORK JUNCTION BOX, AND MOUNTING HARDWARE
HT2302CWH	<b>In-Wall TV Connection Kit (CANADA Compliant)</b>  INCLUDES TOP BOX WITH REMOVABLE TRIM RING, 1 GANG OLD-WORK JUNCTION BOX WITH METAL CLIP, AND MOUNTING HARDWARE
HT2302KWH	<b>In-Wall TV Connection Kit (with Pre-Wired Outlet)</b>  INCLUDES TOP BOX WITH REMOVABLE TRIM RING, 1 GANG OLD-WORK JUNCTION BOX, BOTTOM, TAMPER RESISTANT OUTLET, CABLE ACCESS BRUSH STRAP, WALL PLATES AND MOUNTING HARDWARE
CPS306WV1	<b>TV In-Wall Power Kit with Surge, White</b>  INCLUDES: (1) POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
CPU306WV1	<b>TV In-Wall Power Kit with USB, White</b>  INCLUDES: (1) UNASSEMBLED POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) UNASSEMBLED POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
CPT306WV1	<b>TV In-Wall Power Kit, White</b>  INCLUDES: (1) POWER OUTPUT MODULE, (1) 6FT PREWIRED CORD, (1) POWER INPUT MODULE, (1) DRYWALL BRACKET, (1) POWER CORD & CUTOUT TEMPLATE
CPT7526WHR6	<b>Enclosure In-Wall Power Kit, White</b>  INCLUDES: (1) JUNCTION BOX WITH PRE-WIRED OUTLET, (1) 6FT. IN-WALL RATED CABLE, (1)POWER INPUT MODULE, (1) 6FT. POWER CORD, (1) DRYWALL SAW & NECESSARY HARDWARE



# AV CABLING

## HDMI™ CABLES



### 8K ULTRA HIGH SPEED HDMI™ CABLE 48GBPS / 60Hz

PART NO.	DESCRIPTION
AC8K1MBK	1 Meter Ultra High Speed 8K HDMI™ Cable
AC8K2MBK	2 Meter Ultra High Speed 8K HDMI™ Cable
AC8K3MBK	3 Meter Ultra High Speed 8K HDMI™ Cable
AC8K4MBK	4 Meter Ultra High Speed 8K HDMI™ Cable

- SUPPORTS 8K AT 60Hz
- ALL LENGTHS CL3/FT4 RATED FOR IN-WALL USE
- SURE GRIP CONNECTOR PROVIDES A FIRM GRIP TO PREVENT CABLE DAMAGE
- ENHANCED RETENTION CLIPS KEEP CABLE FIRMLY IN PLACE
- GOLD PATED CONNECTOR RESISTS CORROSION AND PROVIDES THE HIGHEST LEVEL OF SIGNAL CONDUCTIVITY
- ENHANCED AUDIO RETURN CHANNEL (EARC): SUPPORTS HIGH-BITRATE AUDIO FORMATS INCLUDING DTS-HD MASTER AUDIO™, DTS:X®, DOLBY® TRUEHD AND DOLBY ATMOS®



### 4K PREMIUM HIGH SPEED HDMI™ CABLE 18.6 GBPS / 60Hz

PART NO.	DESCRIPTION
AC4K1MBK	1 Meter Premium High Speed 4K HDMI™ Cable
AC4K2MBK	2 Meter Premium High Speed 4K HDMI™ Cable
AC4K3MBK	3 Meter Premium High Speed 4K HDMI™ Cable
AC4K4MBK	4 Meter Premium High Speed 4K HDMI™ Cable
AC4K5MBK	5 Meter Premium High Speed 4K HDMI™ Cable
AC4K7MBK	7 Meter Premium High Speed 4K HDMI™ Cable
AC4K2MBK10	2 Meter Premium High Speed 4K HDMI™ Cable - 10 Pack
AC4K3MBK10	3 Meter Premium High Speed 4K HDMI™ Cable - 10 Pack

- SUPPORTS 4K AT 60Hz
- ALL LENGTHS CL3/FT4 RATED FOR IN-WALL USE
- ENHANCED RETENTION CLIPS KEEP CABLE FIRMLY IN PLACE
- GOLD PATED CONNECTOR RESISTS CORROSION AND PROVIDES THE HIGHEST LEVEL OF SIGNAL CONDUCTIVITY
- ENHANCED AUDIO RETURN CHANNEL (EARC): SUPPORTS HIGH-BITRATE AUDIO FORMATS INCLUDING DTS-HD MASTER AUDIO™, DTS:X®, DOLBY® TRUEHD AND DOLBY ATMOS®



### 10GBPS HIGH SPEED HDMI™ CABLES WITH ETHERNET

PART NO.	DESCRIPTION
AC2M01BK	1 Meter HDMI™ Cable w/Ethernet
AC2M02BK	2 Meter HDMI™ Cable w/Ethernet
AC2M03BK	3 Meter HDMI™ Cable w/Ethernet
AC2M04BK	4 Meter HDMI™ Cable w/Ethernet
AC2M05BK	5 Meter HDMI™ Cable w/Ethernet
AC2M07BK	7.5 Meter HDMI™ Cable w/Ethernet
AC2M10BK	10 Meter HDMI™ Cable w/Ethernet
AC2M15BK	15 Meter HDMI™ Cable w/Ethernet
AC2M20BK	20 Meter HDMI™ Cable w/Ethernet

# CAT 6 CABLES


The differences between the types of category patch cables are found in the speed, bandwidth, and the distance the signal can travel.

- 500MHz PATCH CABLE FULLY SUPPORTS 1 GIGABIT ETHERNET SPEEDS UP TO 328 FT.
- UL VERIFIED TO SUPPORT THE CAT 6A PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES 26 AWG STRANDED PATCH CABLE



AC6A07GYV1

- 250MHz PATCH CABLE FULLY SUPPORTS 1 GIGABIT ETHERNET SPEEDS UP TO 328 FT.
- UL VERIFIED TO SUPPORT THE CAT 6 PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 24 AWG STRANDED PATCH CABLE



AC3607BEV1

- 100MHZ PATCH CABLE SUPPORTS 1 GIGABIT ETHERNET SPEEDS UP TO 328FT.
- UL VERIFIED TO SUPPORT THE CAT 5E PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 24 AWG STRANDED PATCH CABLE



AC3507WHV1

## CAT 6a PATCH CABLES

PART NO.	DESCRIPTION
AC6A03GYV1	3 Foot Cat 6a Patch Cable
AC6A07GYV1	7 Foot Cat 6a Patch Cable
AC6A14GYV1	14 Foot Cat 6a Patch Cable
AC6A25GYV1	25 Foot Cat 6a Patch Cable
AC6A50GYV1	50 Foot Cat 6a Patch Cable

## CAT 6 PATCH CABLES


PART NO.	DESCRIPTION
AC3603BEV1	3 Foot Cat 6 Patch Cable
AC3607BEV1	7 Foot Cat 6 Patch Cable
AC3614BEV1	14 Foot Cat 6 Patch Cable
AC3625BEV1	25 Foot Cat 6 Patch Cable
AC3650BEV1	50 Foot Cat 6 Patch Cable

## CAT 5e PATCH CABLES

PART NO.	DESCRIPTION
36320126V1	1 Foot Cat 5e Patch Cable
36320125V1	2 Foot Cat 5e Patch Cable
AC3503WHV1	3 Foot Cat 5e Patch Cable
AC3507WHV1	7 Foot Cat 5e Patch Cable
AC3514WHV1	14 Foot Cat 5e Patch Cable
AC3525WHV1	25 Foot Cat 5e Patch Cable
AC3550WHV1	50 Foot Cat 5e Patch Cable

# CABLE TIES & PATCH PANELS

## CABLE TIES



PART NO.	DESCRIPTION
AC4000100	4.75" Natural, Cable Ties, 100-Pack
AC4001100	4.75" Black, Cable Ties, 100-Pack
AC4002100	7.5" Natural, Cable Ties, 100-Pack
AC4003100	7.5" Black, Cable Ties, 100-Pack
AC4004100	11" Natural, Cable Ties, 100-Pack
AC4005100	11" Black, Cable Ties, 100-Pack
AC4006	Cable Tie Tool

NOTE: FOR CONSISTANT AND CLEAN INSTALLATIONS USE WITH CABLE TIE TOOL, AC4006

## PATCH PANELS



PART NO.	DESCRIPTION
24845C5E	Category 5e 24-Port T568A/B Universal Wiring
48845C5E	Category 5e 48-Port T568A/B Universal Wiring
24845CC6	Category 6 24-Port T568A/B Universal Wiring
48845CC6	Category 6 48-Port T568A/B Universal Wiring

- 24 PORT PATCH PANEL USES 1 RACK MOUNT SPACE
- 48 PORT PATCH PANEL USES 2 RACK MOUNT SPACES
- 110 PUNCHDOWN REAR TERMINATION

WP24RM	24 Port Keystone Blank
WP48RM	48 Port Keystone Blank
AC1902	2 U Wall Mount Rack with Extenders
12845C5E89	12-Port T568A/B Universal Wiring
PS665089V	50-Pair 66 Block, Unwired & Mounting Bracket
PS11050KIT4V	50-Pair 110 Kit with Legs INCLUDES: 110 PUNCH DOWN BLOCK WITH STAND-OFF LEGS, 10 C5 CLIPS, AND LABEL BAR
WP246A	Cat 6A 24 Port Rack Mount Patch Panel
WP486A	Cat 6A 48 Port Rack Mount Patch Panel

# INSTALLATION TOOLS & CONNECTORS

## TOOLS



36455501



AC3007



AC4006

PART NO.	DESCRIPTION
36455501	EZ RJ-45 Modular Plug Hand Tool
AC3007	Adjustable Compression Tool
AC3400	Punch & Go Tool IMPROVES TERMINATION SPEEDS, REDUCES COMPROMISED CONNECTIONS AND INCREASES PRODUCTIVITY OF ANY QUICK CONNECT DATA INSERT
AC4006	Cable Tie Tool



AC3400

## CONNECTORS



36440501



AC3000100



AC345050



AC346025



WP348301



AC300110



AC300210



AC300310



AC300410



AC300510



AC300610



AC300810

PART NO.	DESCRIPTION
36440501	High Performance RJ45 Modular Plugs, 25-Pack
AC3000100	360 Conical Coax F Plug, 100-Pack
AC345050	EZ-RJ45 Modular Cat 5e Plug, 50-Pack
AC346025	EZ-RJ45 Modular Cat 6 Plug, 25-Pack
WP348301	Banana Plugs (Pair)
AC300110	Compression RG6U/Quad F Plug, 10-Pack
AC300210	Compression RG6U/Quad 3 GHz F Jack, 10-Pack
AC300310	Compression RG6U/Quad Shield BNC Plug, 10-Pack
AC300410	Compression RG6U/Quad Shield RCA Plug, 10-Pack 50 PACK ALSO AVAILABLE, AC300450
AC300510	Compression RG6U/Quad Shield Right Angle RCA Plug
AC300610	Nickle F-81 1 GHz Coupler, 10-Pack 50 PACK ALSO AVAILABLE, AC300650
AC300810	Compression RG6U/Quad F Plug, 10-Pack 50 PACK ALSO AVAILABLE, AC300850



# NOTES

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---

---



## CUSTOMER SERVICE

Friendly and knowledgeable, our team can handle a wide variety of needs and requests – from order processing to system registration – and is available Monday through Friday, from 9 am to 6 pm Eastern Time.  
Phone: 844.334.8044 or [legrandav.com](http://legrandav.com)

### **Legrand | AV**

6436 City West Parkway

Eden Prairie, MN 55344

866-977-3901

[www.legrandav.com](http://www.legrandav.com)

9024 Keele Street,

Vaughan, Ontario L4K 2N2

(800) 723-5175

[www.legrand.ca](http://www.legrand.ca)

012025<00> | DM04722

