ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



1104BPC DPST 208-277V 40A

NSI INDUSTRIES

Catalog Number	1104BPC
Manufacturer	NSI INDUSTRIES
Description	Time Switch, Plastic Enclosure Material, 24 h Time Setting Mode, 24 h Time Setting, DPST Contact Configuration, 277 V, 40 A, 1 Pole, Plastic, -40 °F Operating Temperature, +165 °F Operating Temperature, 5-1/16 x 3-1/16 x 8-5/16 in Size, 3.4 lb
Weight per unit	3.4 (lbs/each)
Product Category	Mechanical Time Switches

Features

Base	Screw
Contact Rating	208-277 VAC
Number Of Pins	12 Pair
Phase	Single Phase
Poles	1
Timing Range	24 Hour
Action	DPST

Dimensions and Weight

Size	L=3.062 - H=8.312 - W=5.062

Descriptions

Description	DPST 208-277V 40A
Long Description	TORK 1104B-PC 24 Hr Time Switch 40A
Product Type	24 HR Time Switch 40A 208-277V DPST CLR

Manufacturer Information

Brand	NSi
GTIN	00786261100979
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Weight Per Each	3.4 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Polycarbonate Outdoor with Clear Cover
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to 165 F
Environmental Conditions	-40 to 165 F
Standard	UL-CSA