ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

4WNLEDLD440SLFUN 4WNLED-LD4-40SL-F-UNV-L840-CD1-U

COOPER LIGHTING SOLUTIONS

Catalog Number	4WNLEDLD440SLFUN
Manufacturer	COOPER LIGHTING SOLUTIONS
Description	Utility LED WrapaRound, 120 to 277 V ac, 130 mA, 36 W, Cold Rolled Steel, White, 4000 K, 80, 60000 h Average Life, Dimmable, White Enamel, 4000 lm Brightness (Lumens), 48 in Length, 2-1/2 in Width, 7-5/8 in Height, 9 lb
Weight per unit	11.0 (lbs/each)
Product Category	Led Surface Architectural & Sp

Features

Ballast Type	N/A
Lamp Type	LED
Number Of Lamps	1
Socket Type	N/A
Voltage Rating	120/277V
Amperage Rating	0.13 (at 277V)

Material, Color, and Finish

Style	(blank)

Descriptions

Description	4WNLEDLD440SLFUNVL840CD1U
Long Description	4ft. LED Striplight, 4000 lumens, 4000K, 0 - 10V dimmable driver
Product Type	4WNLED-LD4-40SL-F-Unv-L840-CD1-U
Special Features	4 ft. and 2 ft. product configurations
Extra Long Description	ECL 4WNLED-LD4-40SL-F-UNV-L840-CD1-

Manufacturer Information

Brand	METALUX
	Cooper Lighting Solutions
GTIN	00080083756889
Manufacturers Part Number	4WNLED-LD4-40SL-F-UNV-L840-CD1-U
	4WNLED-LD4-40SL-F-UNV-L840-CD1
UPC	783363

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Wraparound

Packaging

Carton	1
Weight Per Each	11.0 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
Standard	UL/cUL Listed - Damp Location;RoHS Compliant

WSNLED and WNLED

Premium and utility commercial LED wraparound

Metalux



Powering Business Worldwide



WNLED
Utility LED wraparound



WSNLED
Premium LED wraparound

WNLED/WSNLED Commercial LED wraparounds

These two product lines offer traditionally styled wraparound with Eaton's latest market leading LED and energy efficiency driver technologies. Offered in multiple lumen packages, color temperatures and driver options, the **WSNLED** and **WNLED** series enables customers to have the ideal balance with aesthetics, performance and energy efficiency. Additionally, the WSNLED series utilizes premium optical material which enhances the visual aesthetics providing customers with even, clean illumination eliminating lamp image commonly associated with traditional fluorescent solutions.

CELEBRATING 50+ YEARS

Performance

- 4 ft. and 2 ft. product configurations
- Lumen package - WSNLED (15) and WNLED (4)
- Evenly illuminated lens (WSNLED) for premium aesthetic or frost prismatic lens (WNLED)
- Multiple CCT: 3000K, 3500K, 4000K, 5000K at 82+ CRI
- Excellent performance, up to 118 lm/W
- Powered by Fifth Light. 0-10V dimming driver is standard
- Ideal for surface and suspended
- Suitable for use in clothes closets
- L88 at 60,000 hours
- Five-year warranty

Controls

- WNLED and WSNLED luminaires include 0-10V dimming drivers for control using wall dimmers (10% - 100%), daylighting sensors and room controllers from Eaton. Optional 1% dimming available.
- WNLED and WSNLED luminaires are available with native DALI drivers for complete digital energy management using Fifth Light addressable controls.

powered by fifthlight technology

Compliance

- LED modules comply with IESNA LM-79 and LM-80 standards
- cULus listed 1598 for damp locations
- RoHS compliant

Compliance and approvals

c UL us · RoHS Compliant · DLC QPL Listed · **LM79 / LM80 Compliant** · 5 Year Limited Warranty · DAMP LOCATIONS · **Lasts 25 Years** · Efficiency Standards T24 California Title 24 Non-Residential Compliant



Energy and performance

WNLED Utility LED wraparound					
Lumen type	**Length**	**Catalog number**	**Nominal 3500K lumens**	**Wattage**	**lm/W**
Standard	2 ft.	2WNLED-LD4-28SL-F-UNV-L835-CD1-U	2786	27.5	101
Standard	4 ft.	4WNLED-LD4-32SL-F-UNV-L835-CD1-U	3298	28.0	118
Standard	4 ft.	4WNLED-LD4-40SL-F-UNV-L835-CD1-U	4062	36.0	113
Standard	4 ft.	4WNLED-LD4-50SL-F-UNV-L835-CD1-U	4966	46.6	107

WSNLED Premium LED wraparound					
Lumen type	**Length**	**Catalog number**	**Nominal 3500K lumens**	**Wattage**	**lm/W**
Standard	2 ft.	2WSNLED-LD4-20SL-F-UNV-L835-CD1-U	2073	21.7	95
Standard	2 ft.	2WSNLED-LD4-24SL-F-UNV-L835-CD1-U	2390	25.6	93
Standard	2 ft.	2WSNLED-LD4-28SL-F-UNV-L835-CD1-U	2832	31.4	90
Standard	4 ft.	4WSNLED-LD4-20SL-F-UNV-L835-CD1-U	2009	18.3	110
Standard	4 ft.	4WSNLED-LD4-24SL-F-UNV-L835-CD1-U	2393	21.9	109
Standard	4 ft.	4WSNLED-LD4-28SL-F-UNV-L835-CD1-U	2853	26.5	108
Standard	4 ft.	4WSNLED-LD4-32SL-F-UNV-L835-CD1-U	3212	30.0	107
Standard	4 ft.	4WSNLED-LD4-36SL-F-UNV-L835-CD1-U	3653	34.8	105
Standard	4 ft.	4WSNLED-LD4-40SL-F-UNV-L835-CD1-U	4087	39.8	103
Standard	4 ft.	4WSNLED-LD4-44SL-F-UNV-L835-CD1-U	4424	43.8	101
High	4 ft.	4WSNLED-LD4-48HL-F-UNV-L835-CD1-U	4749	47.9	99
High	4 ft.	4WSNLED-LD4-52HL-F-UNV-L835-CD1-U	5138	53.3	96
High	4 ft.	4WSNLED-LD4-56HL-F-UNV-L835-CD1-U	5536	58.8	94
High	4 ft.	4WSNLED-LD4-60HL-F-UNV-L835-CD1-U	6064	66.9	91
High	4 ft.	4WSNLED-LD4-64HL-F-UNV-L835-CD1-U	6490	72.9	89

Lighting Product Lines
Halo
Halo Commercial
Portfolio
Iris
RSA
Metalux
Corelite
Neo-Ray
Fail-Safe
MWS
Ametrix
Shaper
io
Lumark
McGraw-Edison
Invue
Ephesus
Lumière
Streetworks
AtLite
Sure-Lites

Controls Product Lines
Greengate
iLumin
Zero 88
Fifth Light Technology
iLight (International Only)

Connected Lighting Systems
LumaWatt Pro
WaveLinx
Distributed Low-Voltage Power
ConnectWorks



Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. BR519017EN
May 22, 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

Powering Business Worldwide