ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



511015501 22/2 STR WHITE 500'

SOUTHWIRE COMPANY

Catalog Number	511015501
Manufacturer	SOUTHWIRE COMPANY
Description	Burglar Alarm Cable, Stranded, 22 Strands, 300 V, 500 ft Overall Length, 0.11 in Outside Diameter, 0.006 in Insulation Thickness, Copper Conductor Material, Polypropylene/Fr Polypropylene Insulation Material, PVC Jacket Material, Black and Red, -20 °C Operating Temperature, +75 °C Operating Temperature, 0.01 lb/mft
Weight per unit	0.0100 (lbs/ft)
Product Category	Non-Plenum Unshielded Cable

Descriptions

Description	22/2 STR WHITE 500'
Long Description	22 AWG 2/C STRANDED CU N/S CM/CL2 WE 500C
Product Type	Sy 22/2 STR Cu N/S CM/CL2 We 500C
Extra Long Description	SWC 511015501 SY 22/2 STR CU N/S CM

Manufacturer Information

Brand	Cables & Cords Southwire
GTIN	00029892511012
UPC	885800

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC CABLE

Packaging

Carton	500
Weight Per Each	0.0100 (lbs/ft)

Burglar Alarm cable Solid and Stranded CM/CL2 Rated



96222 96238



51101 51112

Intertek

APPLICATIONS — Burglar alarm interconnect cables to comtrols systems, Class 2 Power Limited Circuit Cable and Communications Cable for General Purpose Applications

CONSTRUCTION

A.) CONDUCTOR	22 AWG solid or stranded Bare Copper
B.) INSULATION	Foam Polypropylene
C.) COLOR CODE	See table
D.) SHIELDING	Unshielded
E.) ASSEMBLY	This cable consists of insulated conductors with an overall extruded jacket.
F.) JACKET	Smooth, round, flexible PVC. Colors: White, Gray, Brown, Beige (Other colors available for minimum order)

COMPLIANCE

A.) FLAME TEST	UL 1685 (by UL) / CSA FT1
B.) CABLE TYPE	UL Standard 13 and 444, NEC Articles 725 and 800, CM/CL2
C.) VOLTAGE	300 V RMS Max.
D.) TEMPERATURE	-20°C to 75°C
E.) SUITABLE USE:	General purpose low voltage and power-limited systems. Suitable for use in indoor use, circuits to NEC Article 725 and 800

FEATURES & OPTIONS: Available in 1000ft or 500 ft packages, reels, or pull-boxes where practicable.

Stock #	DESCRIPTION	AWG	#COND	STRANDS	Rating	NOM. DIA. (Inches)	WEIGHT (Lb/Mft)	COLOR CODE
96222	22/2 Conductors BC	22	2	Solid	CM	0.102	7	Red, Green
96238	22/4 Conductors BC	22	4	Solid	CM	0.117	12	Blk, Red, Yel, Grn
51101	22/2 Conductors BC	22	2	Stranded	CM	0.11	9	Blk, Red
51112	22/4 Conductors BC	22	4	Stranded	CM	0.126	13	Blk, Red, Wht, Grn

©2021 Southwire Company, LLC. All Rights Reserved.