Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



651081 2FT LED 4000K WRAP 20W

SATCO

Catalog Number	651081
Manufacturer	SATCO
Description	LED Wrap, 2.92 lb
Weight per unit	2.5 (lbs/each)
Product Category	Led Lighting

Features

Ballast Type	Self
Material	Steel
Number Of Lamps	1
Socket Type	Integrated
Voltage Rating	120 to 277 v
Warranty	5 Year Limited - Fixtures
Wattage	20
Amperage Rating	0.200 to 0.072
Average Life	50000
Lumens	1600

Material, Color, and Finish

Color	White
Style	Utility
Fixture Material	Acrylic

Dimensions and Weight

Height	2.59
Length	24.5
Size	L:24.50 W:5.50 H:2.63
Width	5.5

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	2FT LED 4000K WRAP 20W
Long Description	LED 2' Ceiling Wrap - 20 Watt - 4000K - White Finish - 120-277V
Product Type	2FT Led Ceiling Wrap
Special Features	Amps: 0.200-0.072A;Bulb Included: Integrated;Cct Selectable: False;Color Temp: Cool White;CRI: 90+;Incandescent Equivalent: 100W;Indoor Outdoor: Indoor;JA8 Compliant: False;Location Rating: Damp;Mounting Procedure: Ceiling/Wall;NEC Compliance: Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5);Operating Frequency: 50/60Hz;Operating Temp: -20C (-4F) to +45C (+113F);Power Factor: 0.99;Replaceable Light Source: False;Style: Utility;Warranty: 5-Years;Wattage Selectable: False
Extra Long Description	SATCO 65/1081 2FT LED CEILING WRAP

Manufacturer Information

Brand	Nuvo
GTIN	00045923510816
Manufacturers Part Number	65/1081
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Functional Lighting

Packaging

Carton	1
Weight	2.38
Weight Per Each	2.5 (lbs/each)

Uses, Certifications, and Standards

Application	Linear Strip
Mounting	CEILING/WALL
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Standard	cETLus - Listed

Project Name

Location | Prepared By



NUVO 65-1081

2FT LED CEILING WRAP

Notes

[www] 10-27-2025 05:20:40

General

Status	Transitioning
Substitute	65-1210
Fixture Type	Ceiling Wrap
Finish	White
Wattage	20W
Lumen Output	1600L
CCT (Kelvin)	4000K
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	No
Integrated Camera	No

Specifications

Technology	LED
Color Temperature	Cool White
CRI	90+
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	2.38
Material	Steel

Dimensions

Height (in.)	2.63
Width (in.)	5.5
Length (in.)	24.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
ENERGY STAR	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5-Years

Copyright 2023 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/