Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

651210 2' 20W LED WRAP 27K/30K/35K/40K/50K - WHITE

SATCO

Catalog Number	651210
Manufacturer	SATCO
Description	LED 2 Foot Wrap - 20 Watts - 27K/30K/35K/40K/50K CCT Selectable - White Finish - 120-277 Volt
Weight per unit	2.5 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	Steel
Number Of Lamps	1
Reflector Type	White
Socket Type	Integrated
Voltage Rating	120 to 277 v
Wattage	20
Amperage Rating	0.17
Average Life	50000
Beam Angle	110
Lumens	1600 to 1650

Material, Color, and Finish

Color	White

Dimensions and Weight

Length	24.33
Size	L:24.33 W:5.50 H:2.56

Descriptions

Description	2' 20W LED WRAP 27K/30K/35K/40K/50K - WHITE
Long Description	LED 2 Foot Wrap - 20 Watts - 27K/30K/35K/40K/50K CCT Selectable - White Finish - 120-277 Volt
Product Type	2FT 20W Led Wrap
Special Features	ADA Compliant: True;Amps: 0.170A;Beam Angle (degree): 110;Bulb Included: Integrated;Cct Selectable: True;Color Temp: Warm White to Natural Light;CRI: 90+;Incandescent Equivalent: 100W;Indoor Outdoor: Indoor;JA8 Compliant: False;Lens Finish: White;Lens Material: Polycarbonate (PC);Location Rating: Damp;Mounting Procedure: Ceiling/Wall;NEC Compliance: Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5);Operating Frequency: 50/60Hz;Operating Temp: -20C (-4F) to +40C (+104F);Power Factor: 0.9;Repla
Extra Long Description	SATCO 65/1210 2FT 20W LED WRAP

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Satco
	Nuvo
GTIN	00045923656408
Manufacturers Part Number	65/1210
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	Functional Lighting

Packaging

Carton	1
Weight Per Each	2.5 (lbs/each)

Uses, Certifications, and Standards

Application	Linear Strip
Mounting	CEILING/WALL
Standard	cETLus

Project Name

Location | Prepared By



NUVO 65-1210

2FT 20W LED WRAP

Notes

[www] 03-19-2025 01:43:41

General

Status	Active
Fixture Type	Ceiling Wrap
Finish	White
Wattage	20W
Lumen Output	1600L-1650L
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White to Natural Light
CRI	90+
Voltage	120V-277V
Beam Angle	110
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Non-Dimmable
Lens Material	Polycarbonate (PC)
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	2.16
Material	Steel

Dimensions

Height (in.)	2.56
Width (in.)	5.5
Length (in.)	24.33

Compliance

Safety Listing	cETLus
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures

Copyright 2023 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/