ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



660WG SW SP AC 15A 120V GRD TERMINAL WH

PASS & SEYMOUR/LEGRAND

Catalog Number	660WG
Manufacturer	PASS & SEYMOUR/LEGRAND
Description	Grounding Toggle Switch, 1 Pole, 15 A, 120 V, ThermoPlastic, White, Wall Mount, 1.25 (L) x 1.090 (W) x 3.281 (H) in, 0.11 lb
Weight per unit	0.1126 (lbs/each)
Product Category	Gen Purpose Switches

Features

Contact Rating	15 Amp, 120/125 VAC
Load Rating	15 A @ 120 VAC
Load Type	Fluorescent, Universal, Halogen, Xenon, Incandescent, LED, CFL
Mounting Type	Wall Box
Number Of Gangs	1
Number Of Switches	1.0
Number Of Wires	3
Poles	1
Switch Type	Toggle
Voltage	120.0 V
Voltage Rating	120
Wall Plate Included	NO
Wire Size	4
Amperage Rating	15
Connection	Grounding
Indoor/Outdoor	Indoor
Throw Type	Single Throw

Material, Color, and Finish

Finish	SATIN

Dimensions and Weight

Size	3.3 in

Descriptions

Description	SW SP AC 15A 120V GRD TERMINAL WH
Features	Extra Long Strap
	Single-Pole Switch, 15A, 120 volts
Long Description	Single-Pole Switch, 15A, 120 volts
Product Type	SW SP Ac 15A120V GRD Terminal White
Special Features	Side wire, high impact resistant construction, extra long strap
Extra Long Description	PAS 660WG SW SP AC 15A120V GRD TERM

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Pass and Seymour
	LEGRAND-PASS & SEYMOUR
GTIN	00785007660135
Manufacturers Part Number	660WG
UPC	785007

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	SWITCH

Trade Size

Amperage	15.0

Packaging

Carton	1
Package	100
Weight Per Each	0.1126 (lbs/each)

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting	WALL
Standard	UL, CULUS, UL 498

Pass and Seymour
Trademaster® Grounding Toggle Switch, White
Part No. 660WG



Single-Pole Switch, 15A, 120 volts

Features & Benefits

High impact resistant injection moldeded Thermoplastic

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007660135
Country Of Origin	China	Material	Thermoplastic
Features	Extra Long Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Hospitality, Residential
Wall Plate Included	No	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Switch

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
Product Height US	4.195 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Load Rating	15 A @ 120 VAC	Connection Location	Side Only
Terminal Accommodation	#14 AWG - #12 AWG	Number of Gangs	1
Throw Type	Single Throw	Amperage	15 A
Number of Poles	Single Pole	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Push Wire	Voltage	120.0 V
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		