ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



7043 22/19.5 KW AIRCOOLED STANDBY GEN ALUM ENCLS 200

GENERAC POWER SYSTEMS INC

Catalog Number	7043
Manufacturer	GENERAC POWER SYSTEMS INC
Description	Home Backup Generator, Bisque Color, Powder Coated Finish, 60 Hz Frequency Rating, 29 in;732 mm Height, 1218 mm;48 in Length, Made in USA, Aluminum Material, 240 V Output Voltage Rating, 22/19.5 kW Power Rating, Generac's G-Force Engines;Mobile Link(TM) Remote Monitoring;Tough, Durable All-Aluminum Enclosures;True Power(TM) Technology Special Features, 211 kg;466 lb Weight, 25 in;638 mm Width
Weight per unit	466.0 (lbs/each)
Product Category	Builders Products

Descriptions

Description	22/19.5 KW AIRCOOLED STANDBY GEN ALUM ENCLS 200
Features	Guardian 22kW Home Backup Generator with Whole House Switch WiFi-Enabled
Long Description	22/19.5 kW Air-Cooled Standby Generator, Aluminum Enclosure, 200 SE (not CUL)
Product Type	22KW/19.5KW Standby Generator
Extra Long Description	GEN 7043 22kW/19.5kW Standby Genera

Manufacturer Information

Brand	Generac
	Generac Power Systems, Inc.
GTIN	00696471074215
UPC	955668

Taxonomies, Classifications, and Categories

Category Description	GENERATOR SYSTEMS
	Generators

Packaging

Carton	1
Weight Per Each	466.0 (lbs/each)

9-22 kW
GUARDIAN SERIES
Automatic Home Standby Generators

GENERAC®




The #1 Selling Home Standby Generator Brand

9-22 kW
AUTOMATIC STANDBY GENERATORS

CHOOSE THE #1 SELLING HOME STANDBY GENERATOR BRAND

Generac's Guardian Series generators provide the automatic backup power you need to protect your home and family during a power outage. Connected to your existing LP or natural gas fuel supply, it kicks in within seconds of sensing power loss—automatically—and runs for as long as necessary until utility power returns. Choose from just enough power to cover essential circuits, or all the way up to 22 kW for the most power per kilowatt and whole-house coverage.

** Total harmonic distortion (THD) less than 5.0%—lower than both IEEE standards for utility power and published numbers for competitive air-cooled home standby generators.*



FEATURES

5-Year Limited Warranty for automatic standby generators.

True Power™ Technology delivers best-in-class power quality with less than 5 percent total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.

Generac generators and engines are **Engineered and Built in the USA***
**Built in the USA using domestic and foreign parts*

Generac's G-Force Engines are purpose-built, pressure-lubricated engine capable of handling the rigors of generator use, resulting in power that's more reliable and requires less routine maintenance than any competitive engine.

24/7 • 365 Customer Support Team standing by all day, every day from our headquarters in Wisconsin to answer any questions you might have.

Quiet-Test™ Self-Test Mode runs at a lower RPM for a five or twelve minute test, making generators significantly quieter than other brands while consuming less fuel.

Tough, Durable All-Aluminum Enclosures. Our RhinoCoat™ powder-coated finish helps make corrosion-resistant aluminum perfect for all weather conditions.

Smart, User-Friendly Controls. Generac's Evolution™ Controller features a multilingual LCD display that allows you to monitor battery status and track maintenance intervals to ensure your generator is always in top operating condition.

Mobile Link™ Remote Monitoring allows you to monitor the status of your generator from anywhere in the world using a smartphone, tablet, or PC. Easily access information, such as the current operating status and the generator's maintenance schedule. Connect your account to your authorized service dealer for fast, friendly and convenient assistance. *(Sold Separately).*

7 out of every 10 homeowners choose
Generac when investing in home backup power.

9-22 kW GUARDIAN SERIES
AUTOMATIC HOME STANDBY GENERATORS



SPECIFICATIONS (LP/NG)	9/8 kW	11/10 kW	16/16 kW	20/18 kW	22/19.5 kW
Generator Only Model	7029	7031	7035	7038	7042
Generator / Select Circuit Switch Model	7030 100 Amp Switch	7032 100 Amp Switch	7036 100 Amp Switch	n/a	n/a
Generator / 200 Amp Service Rated Load Shedding Smart Switch Package Model #	n/a	7033	7037	7039	7043
Voltage (Single Phase)	240V				
Amps @ 240V LPG	37.5	45.8	66.6	83.3	91.6
Amps @ 240V NG	33.3	41.7	66.6	75	81.3
Engine/Alternator RPM	3600/3600				
Engine	Generac G-Force				
Engine Displacement	426cc	530cc	999cc	999cc	999cc
Fuel Consumption @ 1/2 Load NG cu. ft/hr	90	107	218	204	216
Fuel Consumption @ Full Load NG cu. ft/hr	120	159	309	301	310
Fuel Consumption @ 1/2 Load LPG cu. ft/hr (gal/hr)	31.6 (0.87)	44.4 (1.22)	91.6 (2.52)	86 (2.37)	93.2 (2.56)
Fuel Consumption @ Full Load LPG cu. ft/hr (gal/hr)	50 (1.37)	71.6 (1.99)	106 (2.94)	129 (3.56)	140 (3.87)
Quiet-Test Mode	No		Yes		
db(A) at Exercise	66	63	58	58	58
db(A) at Normal Operating Load	66	63	66	66	67
Enclosure	Aluminum				
Enclosure Color	Bisque				
Warranty	5-Year Limited				
Dimensions (L" x W" x H")	48 x 25 x 29				
Weight (lbs.) (Steel/Aluminum)	340	348	406	448	466

Nationwide Dealer Service Network

Generac's commitment to service includes scheduled maintenance programs, warranty assistance and emergency service to ensure that Generac customers are never left powerless. The largest nationwide dealer network has factory-trained technicians on staff and maintains large inventories of Generac parts, components and accessories. Find a dealer near you at generac.com.

THE GENERAC PROMISE

USA ENGINEERED & BUILT* · 24/7 • 365 CUSTOMER CARE · FIVE YEAR LIMITED 5 WARRANTY · Mobile Link

* Built in the USA using domestic and foreign parts.

GENERAC

0203010 09/2016
©2016 Generac Power Systems, Inc. All Rights Reserved.
Specifications are subject to change without notice.

Generac Power Systems, Inc.
S45 W29290 Hwy. 59, Waukesha, WI 53189
generac.com 1-888-GENERAC (1-888-436-3722)