ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



AE50 *DISCONTINUED* 50 CFM 0.5 SONES FAN ENERGY STAR

BROAN/NUTONE LLC

Catalog Number	AE50
Manufacturer	BROAN/NUTONE LLC
Description	Ventilation Fan, 26 Gauge Rugged Galvanized Steel, Ceiling Mount, 120 V ac @ 60 Hz, 20 W, 0.2 A, 50 cfm Air Flow, 60 Hz, Round Duct Shape, 4 in Duct Size, White, Polymeric Grill Material, Square Grill Shape, 11-1/2 in (L) x 12 in (W) Grill Size, Rugged 26 Gauge Galvanized Steel Housing Material, Square Housing Shape, 10 in Overall Length, 9-1/4 in Overall Width, 5-3/4 in Overall Height, 4 in Duct Diameter, Exhaust, 8.6 lb
Weight per unit	8.6 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	50 CFM
Current Rating	0.2 Amp
Duct Size	4 Inch Diameter
Grill Size	11-3/8 Inch Length x 12 Inch Width
Sound Level	0.5 Sones
Ventilation Area	45 Square Foot
Voltage Rating	120 Volt 60 Hertz

Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Additional Information	Power Rating 20 Watt; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter
Commodity Description	Exhaust Fans
Description	*DISCONTINUED* 50 CFM 0.5 SONES FAN ENERGY STAR
Long Description	VENTILATION FAN, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL (CANADA AND US), HVI APPROVAL; 120 VOLT 60 HERTZ VOLTAGE RATING; 0.2 AMP CURRENT RATING; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 50 CFM AIR FLOW RATE
	BROAN FAN 50 CFM 0.5 SONES ENERGY STAR
Extra Long Description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL (CANADA AND US), HVI APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.2 AMP CURRENT RATING; 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 50 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 0.5 SONES SOUND LEVEL; 11-3/8 INCH LENGTH X 12 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 45 SQUARE FOOT VENTILATION AREA; INVENT[TM] SERIES, FLEX[TM] SE

Manufacturer Information

Brand	
	InVent[TM], Flex[TM]
	BROAN
GTIN	00026715236466
UPC	781762

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

Packaging

Carton	1
Weight Per Each	8.6 (lbs/each)

Uses, Certifications, and Standards

Approval	UL (Canada and US), HVI