ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



0SD10NV OCCUPANCY SENSOR DT SP/3W 120/277V

EATON WIRING DEVICES

Catalog Number	0SD10NV
Manufacturer	EATON WIRING DEVICES
Description	EATON OCCUPANCY SENSOR SWITCH, DUAL TECH MOTION, FLUSH, 120/277V, WIRE LEAD, IVORY, INC, MLV, ELV, FLR, HALO, ELEC MTR LDS, 1-POLE, 3-WAY, 1-PH, 1000 SQ FT, 2-RLY, 800W (INC/HAL @120V), 1200W (FLR @120V), 2200W (FLR @277V) 717352
Weight per unit	10.0 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

Dimensions	3.0000 IN X 3.3000 IN X 5.1300 IN

Descriptions

Description	OCCUPANCY SENSOR DT SP/3W 120/277V
Features	Enjoy advanced energy savings and state-of-the-art automation with Eaton’s occupancy and vacancy sensors. Eaton's motion sensor lighting controls use advanced Passive Infrared (PIR) and ultrasonic sensing technology to detect your presence and switch lights ON. Then, once you’ve left the room, our sensors turn the lights OFF following a preset period of time. Sensors are the perfect solution for commercial and residential applications where a switch is inconveniently located and in spaces where lights may
Long Description	EATON OCCUPANCY SENSOR SWITCH, DUAL TECH MOTION, FLUSH, 120/277V, WIRE LEAD, IVORY, INC, MLV, ELV, FLR, HALO, ELEC MTR LDS, 1-POLE, 3-WAY, 1-PH, 1000 SQ FT, 2-RLY, 800W (INC/HAL @120V), 1200W (FLR @120V), 2200W (FLR @277V) 717352
Product Type	Occsen DT SP/3W 120/277V N Iv
Special Features	Wallbox occupancy sensor
Extra Long Description	EWD OSD10N-V OccSen DT SP/3W 120/27

Manufacturer Information

Brand	Eaton Wiring Devices
	Eaton
GTIN	00032664717352
Manufacturers Part Number	OSD10N-V
UPC	781430

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy sensor switch

Packaging

Carton	1
Package	100
Weight Per Each	10.0 (lbs/each)

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Standard	NOM,cULus Listed

Product specifications

Eaton OSD10N-V

Catalog Number: OSD10N-V

Eaton occupancy sensor switch, Dual tech motion, Flush, 120/277V, Wire lead, Ivory, Inc, MLV, ELV, Flr, halo, Elec mtr lds, 1-pole, 3-way, 1-ph, 1000 sq ft, 2-rly, 800W (Inc/hal @120V), 1200W (Flr @120V), 2200W (Flr @277V) 717352



General specifications

Product Name
Eaton occupancy sensor switch

Catalog Number
OSD10N-V

UPC
032664717352

Product Length/Depth
3 in

Product Height
5.13 in

Product Width
3.3 in

Product Weight
50.738 lb

Certifications
NOM
cULus Listed

Powering Business Worldwide

Product specifications

Special features

Dual tech motion sensor

Relay

Single

Phase

Single-phase

Load type

MLV

FLR

INC

HAL

Electrical motor loads

ELV

Closure type

Maintained

Color

Ivory

Wiring method

Wire leads

Mounting method

Flush

Range

1000 sq ft

Number Of Poles

Single-pole

Type

Occupancy sensor switch

Sensor type

Occupancy

Power consumption

2200 W (FLR at 277 V)

800 W (INC/HAL at 120 V)

1200 W (FLR at 120 V)

Number of ways

Three-way

Voltage rating

Resources

Brochures

Arrow Hart commercial lighting controls brochure

Specifications and datasheets

Eaton Specification Sheet - OSD10N-V

120/277 V

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia