ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



AYFSQFHWH ARIADNI 1.5A FAN 3WAY 3SP WHITE CLAM

LUTRON

Catalog Number	AYFSQFHWH
Manufacturer	LUTRON
Description	Fan-Speed Control, 1.5 A, 120 V, 180 W, 1 Pole, 1 Phase, Wire Lead Connection, White Switch Color, 0 to +40 °C, Wallbox Mount, 0.45 lb
Weight per unit	0.4500 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

Contact Configuration	N-O
Contact Rating	1.5
Voltage Rating	120
Wattage	180
Actuator	Toggle Switch
Amperage Rating	1.5
Connection	Wire Leads

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Size	4.60 x 2.86

Descriptions

Description	ARIADNI 1.5A FAN 3WAY 3SP WHITE CLAM
Features	Lutron Ariadni fan controls are designed to replace or match your traditional toggle style switches. This control can be used to operate a single 3-speed ceiling fan. This fan control features a smooth, linear slider to adjust the fan's speed and a toggle switch that turns the fan ON/OFF. Use the slider to select between 3-speeds (Low/Med/High) for a favorite preset level. The Ariadni fan control fits into a traditional wall plate opening and can also work with your existing multi-gang wall plates. Availab
Long Description	Ariadni Fan Control, 3-way/single-pole, quiet 3-speed, 120V/1.5A clamshell packaging in white
Product Type	Ariadni Quiet Fan WH Clamshell
Special Features	Controls 1.5 A fan. Toggle turns fan on/off. Slide up to increase speed, down to decrease. 3 quiet fan speeds designed to prevent motor hum (for use with one ceiling paddle fan).
Extra Long Description	LUT AYFSQ-FH-WH ARIADNI QUIET FAN W

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	LUTRON ELECTRONICS
GTIN	00027557706490
UPC	784276

Taxonomies, Classifications, and Categories

Category Description	CEILING FANS AND ACCESSORIES
Type	Fan control, 3-way/single-pole, clamshell packaging

Packaging

Carton	1
Package	6
Weight Per Each	0.4500 (lbs/each)

Uses, Certifications, and Standards

Enclosure	Plastic
Mounting	WALLBOX
Standard	UL, cUL



Shown actual size: Ariadni® preset dimmer and 1-gang Fassada® wallplate in white (WH)

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- fluorescent lighting
- LED lighting
- quiet 3-speed fan controls
- quiet 3-speed fan/light controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

WH	white	**LA**	light almond
IV	ivory	**BR**	brown
AL	almond	**BL**	black

Ariadni® dimmers

product family features

- matches existing switches
- toggle-style switch returns light to suit any activity
- slide adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- eco-dim® model available

Questions on installation or selection? Call Lutron® 24 hours/7 days a week at 1.800.523.9466 or visit www.lutron.com

dimmers



- toggle turns on/off
- slide up to brighten, down to dim
- eco-dim® model guarantees at least 15% energy savings compared to a standard switch

incandescent/halogen

single pole	600 W	**AY-600P-**
single pole	1000 W	**AY-10P-**
3-way	600 W	**AY-603P-**
3-way	1000 W	**AY-103P-**

incandescent/halogen — eco-dim®† NEW

single pole/3-way	600 W	**AY-603PG-**

magnetic low-voltage

single pole	600 VA (450 W)	**AYLV-600P-**
3-way	600 VA (450 W)	**AYLV-603P-**

Suggested maximum lighting load for magnetic low-voltage dimming is 450 W for 600 VA products to allow for transformer losses.

† available in white, ivory, almond, and light almond

dimmers with locator light



- toggle turns on/off
- slide up to brighten, down to dim
- includes locator light
- not available in black

incandescent/halogen

single pole	600 W	**AY-600PNL-**
single pole	1000 W	**AY-10PNL-**
3-way	600 W	**AY-603PNL-**
3-way	1000 W	**AY-103PNL-**

See page 95 for available colors.
To order, add color suffix to model number.
Example: **AY-600P-WH**

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and **Hi-lume® LED**



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- no derating if ganged

fluorescent*

single pole/3-way	120 V	8 A	**AYF-103P-**
single pole/3-way	277 V	6 A	**AYF-103P-277-**

LED with Hi-lume® LED driver only* NEW

single pole/3-way	120 V	8 A	**AYF-103P-**
single pole/3-way	277 V	6 A	**AYF-103P-277-**

LED with GRX-TVI (0-10 VDC sink control)* NEW

single pole/ 3-way	16 A load 30 mA control 120/277 V	**AYF-103P-**

* requires neutral wire connection

See page 95 for available colors.
To order, add color suffix to model number.
Example: **AY-103P-WH**

fan control



- toggle turns on/off
- slide up to increase speed, down to decrease
- 3 quiet fan speeds for increased comfort
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole/3-way	1.5 A	**AYFSQ-F-**

fan/light control



fan control (left)

- slide up to on/increase fan speed, down to off/decrease fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

dimmer (right)

- toggle turns light on/off
- right slider up to brighten, down to dim

quiet 3-speed control & dimmer

single pole fan control	1.5 A (left)	**AY2-LFSQ-**
single pole dimmer	300 W (right)	

See page 95 for available colors.
To order, add color suffix to model number.
Example: **AYFSQ-F-WH**