



## Open Switches T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

OT25FT3  
80432541546  
Active

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
For use in motor controller and motor overload protection applications  
Can be used as an OSHA lockout/tagout disconnect

### General

Style	Door Mounted
Number of Poles	3
Series	Non-fusible

### Approvals

UL Class	UL 508
----------	--------

### Dimension Information

H x W x D (inches)	2.13 x 1.69 x 2.64
--------------------	--------------------

### Specifications

Rated Current (Amps)	25
Rated Voltage AC	600

### Packaging

T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com



## Open Switches T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

OT25FT3  
80432541546  
Active

3 pole, 25 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
For use in motor controller and motor overload protection applications  
Can be used as an OSHA lockout/tagout disconnect

### General

Style Door Mounted  
Number of Poles 3  
Series Non-fusible

### Approvals

UL Class UL 508

### Dimension Information

H x W x D (inches) 2.13 x 1.69 x 2.64

### Specifications

Rated Current (Amps) 25  
Rated Voltage AC 600

### Packaging

T&B Inner Pack 1  
Package in Units 10  
T&B Sold in UOM Each  
T&B Weight Per UOM 0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com