




ELECTRICAL & TELEPHONE BOXES

- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance
- Meets Caltrans #3 1/2 State Specifications

R-Series Concrete Lid No. N09R 20 lbs.





FL09T




N09J

Electrical Box No. N09 BOX 90 lbs.



B09-61D



N09-61J

A high density reinforced concrete box with non-setting shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

| Oldcastle Ordering Code | Item | Approx. Shipping Weight | Description |
|-------------------------|-----------|-------------------------|--|
| N09BOX | BOX | 90 lbs. | N09 Electrical Box (10 1/8" x 16 3/4") - Meets #3-1/2 State Specifications - 28 per pallet |
| N09R | LID | 20 lbs. | Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately) |
| FL09T | LID | 5 lbs. | Fibrelite Lid, Non-Concrete, Bolt Down (Order N90 Bolt Down Kit Separately) |
| N09J | LID | 22 lbs. | Cast Iron Lid Bolt Down, (Order N90 Bolt Down Kit Separately) |
| B09-61D | COVER | 22 lbs. | Steel Checker Plate Cover |
| N09-61J | COVER | 22 lbs. | Steel Checker Plate Cover, Bolt Down (Order N90 Bolt Down Kit Separately) |
| B09X12 | EXTENSION | 87 lbs. | 12" Reinforced Concrete Box Extension - 28 per pallet |
| B09SL | SLAB | 32 lbs. | Reinforced Concrete Slab (13 1/4" x 19 3/4") |

Galvanizing available on all steel covers.



Oldcastle Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806

Copyright © 2017 Oldcastle, Inc.

N09 BOX

FILE NAME: N09_ISO

ISSUE DATE: January, 2011

OldcastleEnclosures.com

N09 ELECTRICAL BOX

10-1/4" x 16-3/4"

CHRISTY


ELECTRICAL & TELEPHONE BOXES

- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance



Cast-In Bolt Down Bracket

HNT-E02 For Bolt Down Application


R-Series Concrete Lid No. N16R 32 lbs.




Electrical Box No. N16 BOX 112 lbs.




N16J



FL16T



B16-61D



N16-61J

A high density reinforced concrete box with non-settling shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

| Oldcastle Ordering Code | Item | Approx. Shipping Weight | Description |
|--|-----------|-------------------------|--|
| N16BOX | BOX | 112 lbs. | N16 Electrical Box (11 $\frac{5}{8}$ " x 22 $\frac{3}{4}$ ") - 20 per pallet |
| N16R | LID | 32 lbs. | Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately) |
| FL16T | LID | 13 lbs. | Fibrelyte Lid, Non-Concrete Bolt Down (Order N90 Bolt Down Kit Separately) |
| N16J | LID | 36 lbs. | Cast Iron Lid Bolt Down (Order N90 Bolt down Kit Separately) |
| B16-61D | COVER | 28 lbs. | Steel Checker Plate Cover |
| N16-61J | COVER | 28 lbs. | Steel Checker Plate Cover, Bolt Down (Order N90 Bolt Down Kit Separately) |
| B16X12 | EXTENSION | 113 lbs. | 12" Reinforced Concrete Box Extension - 20 per pallet |
| B30SL | SLAB | 52 lbs. | Reinforced Concrete Slab (16" x 28") |
| Galvanizing available on all steel covers. | | | |



Oldcastle® Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806

Copyright © 2017 Oldcastle, Inc.

N16 BOX

FILE NAME: N16_ISO

ISSUE DATE: January, 2011

OldcastleEnclosures.com

N16 ELECTRICAL BOX 11-3/4" x 22-1/4"

CHRISTY®


ELECTRICAL & TELEPHONE BOXES

- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance
- Meets Caltrans #3 1/2 State Specifications


R-Series Concrete Lid No. N09R 20 lbs.

Cast-In Bolt
Down Bracket

HNT-E02 For
Bolt Down
Application





FL09T




N09J

Electrical Box No. N09 BOX 90 lbs.



B09-61D



N09-61J

A high density reinforced concrete box with non-setting shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

| Oldcastle Ordering Code | Item | Approx. Shipping Weight | Description |
|-------------------------|-----------|-------------------------|--|
| N09BOX | BOX | 90 lbs. | N09 Electrical Box (10 1/8" x 15 1/2") - Meets #3-1/2 State Specifications - 28 per pallet |
| N09R | LID | 20 lbs. | Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately) |
| FL09T | LID | 5 lbs. | Fibrelyte Lid, Non-Concrete, Bolt Down (Order N90 Bolt Down Kit Separately) |
| N09J | LID | 22 lbs. | Cast Iron Lid Bolt Down, (Order N90 Bolt Down Kit Separately) |
| B09-61D | COVER | 22 lbs. | Steel Checker Plate Cover |
| N09-61J | COVER | 22 lbs. | Steel Checker Plate Cover, Bolt Down (Order N90 Bolt Down Kit Separately) |
| B09X12 | EXTENSION | 87 lbs. | 12" Reinforced Concrete Box Extension - 28 per pallet |
| B09SL | SLAB | 32 lbs. | Reinforced Concrete Slab (13 1/4" x 19 1/4") |

Galvanizing available on all steel covers.

 **Oldcastle** Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806
Copyright © 2017 Oldcastle, Inc.

N09 BOX

FILE NAME: N09_ISO

ISSUE DATE: January, 2011

OldcastleEnclosures.com

N09 ELECTRICAL BOX 10-1/4" x 16-3/4"

CHRISTY


ELECTRICAL & TELEPHONE BOXES

- Etched polypropylene face
- Face anchored in concrete
- Ultra-violet inhibitor
- Exceeds ASTM-D1693 Standards for Environmental Stress Cracking Resistance



Cast-In Bolt Down Bracket

HNT-E02 For Bolt Down Application


R-Series Concrete Lid No. N16R 32 lbs.




Electrical Box No. N16 BOX 112 lbs.




N16J



FL16T



B16-61D



N16-61J

A high density reinforced concrete box with non-settling shoulders positioned to maintain grade and facilitate back filling. Approximate dimensions and weight shown.

| Oldcastle Ordering Code | Item | Approx. Shipping Weight | Description |
|--|-----------|-------------------------|--|
| N16BOX | BOX | 112 lbs. | N16 Electrical Box (11 $\frac{1}{4}$ " x 22 $\frac{1}{4}$ ") - 20 per pallet |
| N16R | LID | 32 lbs. | Reinforced Concrete Lid with Plastic Ring - (Order N90 Bolt Down Kit Separately) |
| FL16T | LID | 13 lbs. | Fibrelyte Lid, Non-Concrete Bolt Down (Order N90 Bolt Down Kit Separately) |
| N16J | LID | 36 lbs. | Cast Iron Lid Bolt Down (Order N90 Bolt down Kit Separately) |
| B16-61D | COVER | 28 lbs. | Steel Checker Plate Cover |
| N16-61J | COVER | 28 lbs. | Steel Checker Plate Cover, Bolt Down (Order N90 Bolt Down Kit Separately) |
| B16X12 | EXTENSION | 113 lbs. | 12" Reinforced Concrete Box Extension - 20 per pallet |
| B30SL | SLAB | 52 lbs. | Reinforced Concrete Slab (16" x 28") |
| Galvanizing available on all steel covers. | | | |



Oldcastle® Enclosure Solutions

Phone: (800) 735-5566 Fax: (800) 486 6806

Copyright © 2017 Oldcastle, Inc.

N16 BOX

FILE NAME: N16_ISO

ISSUE DATE: January, 2011

OldcastleEnclosures.com

N16 ELECTRICAL BOX 11-3/4" x 22-1/4"

CHRISTY®