



## Open Switches

### T&B Catalog Number:

OT40F3

UPC Number:

80432541553

Status:

Active

Description:

3 pole, 40 amps rated at 600 VAC, UL 508, open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism

Extremely compact size

Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects

For use in motor controller and motor overload protection applications

Can be used as an OSHA lockout/tagout disconnect

### General

Number of Poles

3

Series

Non-fusible

### Approvals

UL Class

UL 508

### Dimension Information

H x W x D (inches)

2.13 x 1.38 x 2.20

### Specifications

Rated Current (Amps)

40

Rated Voltage AC

600

### Packaging

T&amp;B Inner Pack

1

Package in Units

10

T&amp;B Sold in UOM

Each

T&amp;B Weight Per UOM

0.23 lbs. Each

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com



## Open Switches

### T&B Catalog Number:

OT40F3

UPC Number:

80432541553

Status:

Active

Description:

3 pole, 40 amps rated at 600 VAC, UL 508, open non-fusible disconnect switch

### Features

---

 Quick make, quick brake mechanism
 

---

 Extremely compact size
 

---

 Finger-proof construction with no hazardous exposed parts
 

---

### Application

---

 Industrial control panel disconnects
 

---

 For use in motor controller and motor overload protection applications
 

---

 Can be used as an OSHA lockout/tagout disconnect
 

---

### General

Number of Poles

3

Series

Non-fusible

### Approvals

UL Class

UL 508

### Dimension Information

H x W x D (inches)

2.13 x 1.38 x 2.20

### Specifications

Rated Current (Amps)

40

Rated Voltage AC

600

### Packaging

T&amp;B Inner Pack

1

Package in Units

10

T&amp;B Sold in UOM

Each

T&amp;B Weight Per UOM

0.23 lbs. Each

### For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com