ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



CCR LED EXIT/EMERGENCY COMBO

HUBBELL LIGHTING/CURRENT HLI

Catalog Number	CCR
Manufacturer	HUBBELL LIGHTING/CURRENT HLI
Description	LED Combination Exit/Emergency Light, ThermoPlastic, Universal Faces, Red Text Color, 90 min Emergency Illumination Time, 120 V ac;277 V ac, 4.12 W @ 120 V ac;3.2 W @ 277 V ac, 4.3 in Depth, 18 in Length, 8.2 in Height, White, Battery Included, Nickel Cadmium (NiCad);Nickel Metal Hydride (NiMh) Battery, 2 yr Warranty, 2.5 lb
Weight per unit	2.5 (lbs/each)
Product Category	Exit Signs

Features

Battery Type	NiCD
Fixture Type	Exit Sign / Emergency Light
Lamp Type	LED
Lamp Wattage	4.12, 3.20
Material	Plastic
Number Of Lamps	2
Voltage Rating	120/277 V
Wattage	4.12/3.2

Material, Color, and Finish

Color	White
Letter Color	RED
Housing Color	White

Dimensions and Weight

Size	3 in x 18 in x 7 in

Descriptions

Description	LED EXIT/EMERGENCY COMBO
Long Description	The Compass combination exit sign/emergency light offers quality and value with a compact and attractive LED based emergency exit sign with red letters and 2 fully adjustable LED lamp-heads. The white housing and lamp-heads are made of high impact, UL flame rated thermoplastic. Snap together canopy, housing and removable chevrons for quick and easy installation. The CCR can be applied in stair-wells, hallways, offices and other commercial applications.
Product Type	Em Exit Combo WHT HSG Red Letter
Special Features	N/A
Extra Long Description	DUAL CCR EM EXIT COMBO WHT HSG RED

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	COMPASS
	DUAL-LITE
GTIN	00856143001400
UPC	785988

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Exit sign / emergency light

Packaging

Carton	1
Weight Per Each	2.5 (lbs/each)

Uses, Certifications, and Standards

Application	Commercial applications;Conditioned Space;Damp location;Hallways;Offices;Retail;Stair-wells
Mounting	Wall or ceiling mount
Environmental Conditions	Damp Location
Standard	UL924 Listed for Damp Location

CC Series

LED Combination Exit/Emergency Light

DESCRIPTION

The CC Series offers quality and value with a compact and attractive LED based combination emergency exit. The white or black housing and lamp-heads are made of high impact UL flame rated thermoplastic. Snap together canopy, housing and removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity unit will run a double-head remote or 2 single-head remotes of either the Compass CIR or COR Series.



APPLICATION

The CC Series can be applied in stair-wells, hallways, offices and other commercial applications.

FEATURES

- LED life-cycle of more than 10 years
- Molded-in template for Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium (NiCad) or Nickel Metal Hydride (NiMh) battery for UL recognized 90 minute emergency lighting
- Remote capacity or extended runtime option
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Provided with test switch and AC-On indicator
- Lamp-heads are fully adjustable
- Canopy included
- Remote Capacity (RC) models have a minimum runtime of 120 minutes when no remotes are installed

WARRANTY

2 year full unit warranty

STANDARDS, CERTIFICATION, AND COMPLIANCE

- UL924 Listed for Damp Location
- NFPA 101 and NFPA 70
- OSHA

SELF-DIAGNOSTIC FEATURES

- Fault identification for battery, charger, LED integral lamps and remotes
- Self-Testing monthly and annual for 90 minutes
- Manual testing for 30 second, 15 minute and 90 minutes

ENERGY CONSUMPTION

	120 VAC	277 VAC
CCR	4.12 W	3.20 W
CCG	3.22 W	3.18 W
CCRRC	4.00 W	4.06 W
CCGRC	4.10 W	4.28 W

ORDERING GUIDE

Catalog Number	Description
CCR	White Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, NiCad Battery, CEC T20 Compliant
CCRB	Black Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, NiCad Battery, CEC T20 Compliant
CCG	White Finish, Combination Exit/Emergency Light, Universal Face, Green Letters, NiCad Battery, CEC T20 Compliant
CCGB	Black Finish, Combination Exit/Emergency Light, Universal Face, Green Letters, NiCad Battery, CEC T20 Compliant
CCRRC	White Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, Remote Capacity, NiMh Batt., CEC T20 Compliant
CCRRCB	Black Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, Remote Capacity, NiMh Batt., CEC T20 Compliant
CCGRC	White Finish, Combination Exit/Emergency Light, Universal Face, Green Letters, Remote Capacity, NiMh Batt., CEC T20 Compliant
CCRSD	White Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, Self-Test/Self-Diagnostics, NiCad Battery, CEC T20 Compliant
CCGSD	White Finish, Combination Exit/Emergency Light, Universal Face, Green Letters, Self-Test/Self-Diagnostics, NiCad Battery, CEC T20 Compliant
CCRRCSD	White Finish, Combination Exit/Emergency Light, Universal Face, Red Letters, Self-Test/Self-Diagnostics, NiMh Batt., Remote Capacity, CEC T20 Compliant
CCGRCSD	White Finish, Combination Exit/Emergency Light, Universal Face, Green Letters, Self-Test/Self-Diagnostics, NiMh Batt., Remote Capacity, CEC T20 Compliant

Note: Remote Capacity Unit will only power the Compass Indoor and Outdoor Remote(CIR and COR Series)

DIMENSIONS





Single Carton Weight: 2.5 lbs.
Master Carton Quantity: 6 each

ACCESSORIES

WGEL Wireguard - 8" H X 20" W X 8" D
CIR Series - Matching LED Indoor Remote Heads
COR Series - Matching LED Outdoor Remote Heads



CIRS CIRD C0RD C0RS

Web: www.compasslightingproducts.com • Tech Support: (866)-313-3909
701 Millennium Blvd. • Greenville, SC 29607 U.S.A.
Copyright © Hubbell Lighting, Inc., All Rights Reserved
Due to our continued efforts to improve our products, specifications are subject to change without notice. • Printed in U.S.A.

0603532 03/18