ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



CWL515P PLUG 15A 125V 2P3W H/L BW

EATON WIRING DEVICES

Catalog Number	CWL515P
Manufacturer	EATON WIRING DEVICES
Description	Locking Plug, 15 A, 125 V, 2 Poles, 3 Wires, Black/White, -40 °C Operating Temperature, +60 °C Operating Temperature, Screw Terminal, 0.33 to 0.66 in (Cord) Diameter, #16 to #12 AWG Wire Size, 0.17 lb
Weight per unit	0.1500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Dimensions	4.2500 IN X 2.0000 IN X 1.7500 IN

Descriptions

Description	PLUG 15A 125V 2P3W H/L BW
Features	Industrial grade locking devices are designed for quick and easy installation and provide reliable performance in tough industrial environments.
Long Description	Eaton Arrow Hart safety grip locking plug, #16-12AWG, 15A, Industrial, 125V, Back wiring, Black, white, Safety grip, L5-15, Two-pole, Three-wire, Nylon, 0.38 to 1 in, -40° to 60°C
Product Type	Plug 15A 125V 2P3W H/L BW
Special Features	Industrial grd plugs & conns
Extra Long Description	EWD CWL515P Plug 15A 125V 2P3W H/L

Manufacturer Information

Brand	Eaton
	COOPER WIRING DEVICES
GTIN	00040893677989
UPC	781430

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Safety grip

Packaging

Carton	10
Package	50
Weight Per Each	0.1500 (lbs/each)

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
Standard	CSA certified,Federal Specification Classification W-C-596F,cULus Listed,RoHS Compliant


Industrial grade 15A locking devices

Product description


2-pole, 3-wire grounding
15A, 125V/AC
NEMA L5-15



L5-15R L5-15P



CWL515C



CWL515PAN



4721N

Industrial grade plugs & connectors

Rating A	V/AC	NEMA	Description	Cord diameter	Color	Plug catalog no.	Connector catalog no.		
15	125	L5-15	Safety grip straight body	0.33-0.66" (8.4-16.7mm)	BK & W	☐ CWL515P	☐ CWL515C	•	•
			Safety grip angled body	0.33-0.66" (8.4-16.7mm)	BK & W	☐ CWL515PAN	☐ CWL515CAN	•	•
			Auto grip	0.33-0.66" (8.4-16.7mm)	BK & W	☐ 4721N	☐ 4731N	•	•

Industrial grade receptacles

Rating A	V/AC	NEMA	Description	Color	Single receptacle	Duplex receptacle		
15	125	L5-15	Standard industrial	BK	☐ CWL515R*	—	•	•
			Standard industrial	BK	—	☐ 4700		•
			Isolated ground	RN	☐ IGL515R*	☐ IG4700*	•	•
		5-15	Combination locking & straight blade	BK	—	☐ 5792*	•	•

*Not Fed Spec

Industrial grade flanged inlet

Rating A	V/AC	NEMA	Description	Color	Flanged inlet		
15	125	L5-15	Standard industrial	BK & W	☐ CWL515FI	•	•

Industrial grade flanged outlet

Rating A	V/AC	NEMA	Description	Color	Flanged outlet		
15	125	L5-15	Standard industrial	BK & W	☐ CWL515FO	•	•

Dimensional information:
C-76-C-78

Plug & connector specification information:
L5-15: C-84
Receptacle specification information:
L5-15: C-86
Isolated ground L5-15: C-86
Flanged inlet & flanged outlet specification information:
L5-15: C-88

Color information:

BK (Black), RN (Orange), W (White)

BK	RN	W
(Black)	(Orange)	(White)

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32