ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



DVFSQFLA DIVA 1.5A FAN 3WAY 3SP LIGHT ALMOND

LUTRON

Catalog Number	DVFSQFLA
Manufacturer	LUTRON
Description	Fan-Speed Control, 1.5 A, 120 V, 180 W, 1 Pole, 1 Phase, Wire Lead Connection, Light Almond Switch Color, 0 to +40 °C, Wallbox Mount, 0.25 lb
Weight per unit	0.2500 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

Contact Configuration	N-O
Contact Rating	1.5
Voltage Rating	120
Wattage	180
Actuator	Paddle Switch
Amperage Rating	1.5
Connection	Wire Leads

Material, Color, and Finish

Color	Light Almond
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94

Descriptions

Description	DIVA 1.5A FAN 3WAY 3SP LIGHT ALMOND
Features	The Lutron Diva 3-Speed Fan Switch helps achieve the ideal comfort level for any home by controlling a single fan up to 1.5 Amps. The intuitive rocker switch turns the fan on/off to a preset and the linear slider adjusts between 3 speeds (Low, Medium and, High). Install with Lutron Claro Switches in 3-way applications. Coordinating Claro wall plates and 3-way switches sold separately. Available in 20+ colors to consistently match any Lutron device.
Long Description	Lutron Diva 3-Speed 1.5A Fan Control, Single-Pole/3-Way, Light Almond
Product Type	Diva Fan Speed Quiet Single
Special Features	Controls 1.5 A fan. Paddle turns on/off. Slide up to increase speed, down to decrease speed. 3 quiet fan speeds for increased comfort. For use with only one ceiling paddle fan. Does not include locator light. Designed to prevent motor hum.
Extra Long Description	LUT DVFSQ-F-LA DIVA FAN SPEED QUIET

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	LUTRON ELECTRONICS
GTIN	00027557366403
UPC	784276

Taxonomies, Classifications, and Categories

Category Description	CEILING FANS AND ACCESSORIES
Type	Fan control, 3-way/single-pole

Packaging

Carton	1
Weight Per Each	0.2500 (lbs/each)

Uses, Certifications, and Standards

Application	Fan Control
Enclosure	Plastic
Mounting	WALLBOX
Standard	UL, CSA, NOM


3691042g 1 07.27.22

Diva Fan-Speed Controls


The designer fan-speed control that matches your paddle switches.

Features

- On/off rocker switch with a captive slider
- Quiet 3-speed control of ceiling fan
- Requires separate wires at the wallbox for independent control of the fan and the light
- No neutral is required at the wallbox
- No nightlight
- 100% factory-tested
- Coordinating Claro and Stainless Steel wallplates are available separately
- Fan-only version can be wired as a single pole or 3-way



DVFSQ-F
(Wallplates sold separately)



DVFSQ-LF
(Wallplates sold separately)

Model Numbers

Model Number	Description		Maximum Capacity	
DVFSQ-F-XX [1,2,3,4,7] DVFSQ-F-XX-CSA [1,2,3,4,5,7]	Gloss finishes Preset fan-speed control Single-pole/3-way, 3 speed		1.5 A	
DVSCFSQ-F-YY [1,3,4,7]	Satin finishes Preset fan-speed control Single-pole/3-way, 3 speed		1.5 A	
DVWFSQ-FH-XX [1,3,4,6,7] DVWFSQ-FH-XX-CSA [1,3,4,5,6,7]	Gloss finishes Preset fan-speed control Single-pole/3-way, 3 speed Clamshell packaging Wallplate included		1.5 A	
DVFSQ-LF-XX [1,2,4] DVFSQ-LF-XX-C [1,2,4,5]	Gloss finishes Light switch/ Fan-speed control Single-pole light and fan	Single-pole switch	Incandescent/ Halogen	2 A
			CFL/LED	1 A
		Fan (3-speed with Off)	1.5 A	
DVSCFSQ-LF-YY [1,4]	Satin finishes Light switch/ Fan-speed control Single-pole light and fan	Single-pole switch	Incandescent/ Halogen	2 A
			CFL/LED	1 A
		Fan (3-speed with Off)	1.5 A	
DVFSQ-F-HO-XX [1,3,4,7]	For Hunter Original Series fans Gloss finishes Preset fan-speed control Single-pole/3-way, 3 speed		2 A	

1 "XX" or "YY" in the model number represents color/finish code; see **Colors and Finishes** section.
2 For clamshell packaging, add "H" after "F" or "LF". Call Lutron Customer Assistance for color availability.
3 For 3-way and 4-way switching, use Claro switches or other mechanical switches.
4 No derating required.
5 Canadian packaged product.
6 These products include a wallplate.
7 Fan-only controls not intended for use in controlling lighting loads.

Job Name:	Model Numbers:
Job Number:	

3691042g 2 07.27.22

Specifications

Regulatory Approvals

- DVFSQ-LF: cULus Listed
- DVFSQ-F: UL/CSA
- NOM certified

Power and Ratings

- 120 V~ 60 Hz

Environment

- For indoor use only.
- Operating temperatures 32 °F to 104 °F (0 °C to 40 °C).


Performance

- Power-failure memory
- Captive linear slider
- Electrostatic discharge tested
- Precise color matching with Claro wallplates
- Mechanical air-gap switch to disconnect load power

Warranty

- 1 Year Limited Warranty
  For additional Warranty information, please visit www.lutron.com/TechnicalDocumentLibrary/369-119_Wallbox_Warranty.pdf

Dimensions





Note: Requires a U.S. wallbox 2½ in (64 mm) deep minimum. Overall width and height dimensions shown are with a Claro wallplate (sold separately).

Job Name:	Model Numbers:
Job Number:	

Ganging*

When installing more than one fan-speed control in the same wallbox, it may be necessary to remove some side sections prior to wiring **(see diagram)**.






* No derating required.


Wiring Diagrams

Single-Pole Wiring

DVFSQ-F




DVFSQ-LF




3-Way Wiring

DVFSQ-F - Line-Side



OR

DVFSQ-F - Load-Side





Job Name:	Model Numbers:
Job Number:	


3691042g 4 07.27.22


Colors and Finishes


Gloss Finishes



White
WH



Ivory
IV


Almond
AL



Light Almond
LA



Gray
GR



Brown
BR



Black
BL


Satin Finishes



Brilliant White
BW



Glacier White
GL



Snow
SW


Architectural White
RW


Lunar Gray
LG



Mist
MI



Pebble
PB


Cobblestone
CS


Slate
SL



Midnight
MN



Biscuit
BI


Sand
SD


Taupe
TP


Pumice
PM


Clay
CY


Sage
SA


Espresso
EP


Truffle
TF


Deep Sea
DE


Signal Red
SR

- Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.
- Color chip keychains are available for more precise color matching:
  Gloss Finishes: DG-CK-1
  Satin Finishes: SF-CK-1
- For coordinating wallplates and accessories, visit lutron.com/claro

Job Name:	Model Numbers:
Job Number:	


Colors and Finishes (*continued*)


Satin Colors (while supplies last)


Hot
HT



Merlot
MR


Plum
PL



Palladium
PD



Eggshell
ES


Sienna
SI



Terracotta
TC



Greenbriar
GB



Bluestone
BG


Mocha Stone
MS


Goldstone
GS


Desert Stone
DS


Stone
ST


Limestone
LS

- Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.
- Color chip keychains are available for more precise color matching:
  Satin Colors: SC-CK-1 (while supplies last)

The Lutron logo, Lutron, Claro, Satin Colors, and Diva are trademarks or registered trademarks of Lutron Electronics Co., Inc. in the US and/or other countries.
All other product names, logos, and brands are property of their respective owners.

Job Name:	Model Numbers:
Job Number:	