Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



ENTRA 14W/11W/7W LED WALL MOUNT ENTRY LIGHT 3K/4K/5K BRZ

RAB LIGHTING

Catalog Number	ENTRA
Manufacturer	RAB LIGHTING
Description	Wall Packs 1284 Lumens Entra Doorway 12W 5000K Bronze
Weight per unit	4.0 (lbs/each)
Product Category	Led Wall Mounted Architectural

Features

Voltage Rating	120/277
Wattage	12
Average Life	100,000
Lumens	1284

Descriptions

Description	14W/11W/7W LED WALL MOUNT ENTRY LIGHT 3K/4K/5K BRZ
Long Description	Wall Packs 1284 Lumens Entra Doorway 12W 5000K Bronze
Product Type	Entra 12W Cool 120V to 277wall
Extra Long Description	RAB ENTRA12 ENTRA 12W COOL 120V TO

Manufacturer Information

Brand	Rab Lighting
	RAB Lighting Inc
GTIN	00019813107059
Manufacturers Part Number	ENTRA
	ENTRA12
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Wallpack

Packaging

Carton	1
Weight Per Each	4.0 (lbs/each)

Uses, Certifications, and Standards

Mounting	CEILING

ENTRA12



Affordable, high-performance, low-maintenance LED doorway light. Suitable for mounting heights up to 10', and replaces 70W high pressure sodium. 100,000-Hour LED lifespan. 5-year, no-compromise warranty.

Color: Bronze

Weight: 2.9 lbs

Project:	Type:
Prepared By:	Date:

Driver Info

Type	Constant Current
120V	0.3A
208V	0.3A
240V	0.3A
277V	0.3A
Input Watts	14.4W

LED Info

Watts	12W
Color Temp	5000K (Cool)
Color Accuracy	70 CRI
L70 Lifespan	100,000 Hours
Lumens	1,284 lm
Efficacy	89.2 lm/W

Technical Specifications

Compliance

UL Listed:
Suitable for wet locations as downlight. Suitable for mounting within 4ft (1.2m) of the ground.

IP Rating:
Ingress protection rating of IP66 for dust and water

ADA Compliant:
ENTRA™ is ADA Compliant

IESNA LM-79 & LM-80 Testing:
RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

LED Characteristics

LED:
12W multi-chip, long life LED

Color Stability:
LED color temperature is warrantied to shift no more than 200K in color temperature over a 5-year period

Color Consistency:
7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Performance

Lifespan:
100,000-Hour LED lifespan based on IES LM-80 results and TM-21 calculations

Wattage Equivalency:
50W HPS

Construction

Cold Weather Starting:
The minimum starting temperature is -40°C (-40°F)

Maximum Ambient Temperature:
Suitable for use in up to 40°C (104°F)

Back Housing:
Die-cast aluminum

Lens/Housing Cover:
Vandal resistant polycarbonate molded housing cover and lens

Mounting:
Heavy die cast aluminum with 1/2" back knockout and mounting template for mounting to 4" box

Recommended Mounting Height:
Up to 10 ft

Reflectors (2):
White aluminum reflector topped with vacuum-metalized polycarbonate LED reflector

Gaskets:
High-temperature silicone

Finish:
Formulated for high durability and long-lasting color

Green Technology:
Mercury and UV free. RoHS-compliant components.

Other

Patents:
The design of the ENTRA™ is protected by patents pending in US, Canada, China, Taiwan and Mexico

Warranty:
RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

Technical Specifications (continued)

Buy American Act Compliance:
RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Electrical

Driver:
Constant Current, Class 2, 100-277V, 50/60Hz, 4kV Surge Protection, 350mA, 100-240VAC: 0.3 - 0.15 A, 277VAC: 0.15 A, Power Factor: 98.5%.

THD:
9.9% at 120V

Dimensions



Features

- Save over $700 in energy costs over life of fixture
- Equivalent to 70W high pressure sodium
- Durable vandal-resistant polycarbonate housing
- Low-profile and ADA compliant
- 100,000-hour LED lifespan
- 5-Year, No-Compromise Warranty

Ordering Matrix

Family	Wattage	Color Temp	Finish	Options	Other Options
ENTRA	12				
	12 = 12W	**Blank =** 5000K Cool **N =** 4000K Neutral **Y =** 3000K Warm	**Blank =** Bronze **W =** White	**Blank =** No Options **/PC =** 120V Button **/PC2 =** 277V Button **/PCS =** 120V Swivel **/PCS2 =** 277V Swivel	**Blank =** Standard

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice