ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F66G90E 6X6 N1 90D HC Elb

Hoffman Enclosures, Inc.

Catalog Number	F66G90E
Manufacturer	Hoffman Enclosures, Inc.
Description	Elbow 90-Degree Lay-In Wireway, 6.00X6.00, Gray, Mild Steel
Weight per unit	17.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Painted;Powder Coat

Dimensions and Weight

Height	6
Width	6

Descriptions

Description	6X6 N1 90D HC ELB
extra long description	NVENT HOF F66G90E 90 Elbow
Features	Lay-in Painted 90-Degree Elbows have all removable sides, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.
Long Description	Elbow 90-Degree Lay-in Wireway, 6.00x6.00, Gray, Mild Steel
Product Type	90 Elbow
Short Description	90 Elbow

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510525309
Manufacturers Part Number	F66G90E
UPC	783510525309

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Elbow

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	17

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1 Indoor, electrical protection