ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



G600041A 14/2C SOL BC N/S FPLP RED

SOUTHWIRE COMPANY

Catalog Number	G600041A
Manufacturer	SOUTHWIRE COMPANY
Description	Portable Cord, Red, 14 AWG Conductor Size, Made in USA, 2 - Conductors, Carton Package Type, Solid Solid/Strand
Weight per unit	0.1210 (lbs/each)
Product Category	Wire

Features

Media	Yes

Descriptions

Description	14/2C SOL BC N/S FPLP RED
Long Description	14 AWG 2/C UNSHIELDED FPLP/CMP/CL3P CABLE
Product Type	Fa 14/2SOLCU N/S FPLP RD 1000R
Short Description	FA 14/2C SOL BC NS FPLP RD 10
Extra Long Description	SWC G60004-1A FA 14/2SOLCU N/S FPLP

Manufacturer Information

Brand	Cables & Cords Southwire
GTIN	00032886881503
Manufacturers Part Number	G60004-1A
UPC	885800

Taxonomies, Classifications, and Categories

Category Description	Portable Cords, Voice, Data, Video Wire & Cable

Packaging

Carton	1000
Weight Per Each	0.1210 (lbs/each)

FPLP - FIRE ALARM SOLID OR STRANDED Plenum Rated LS-PVC



APPLICATIONS — Fire protective signaling circuits. Also for smoke detectors, voice communications, audio control and initiating circuits. Article 760 of the NEC. For use in plenum spaces.

CONSTRUCTION

- A.) CONDUCTOR — Solid Bare Copper or Stranded Bare Copper
- B.) INSULATION — LS-PVC
- C.) COLOR CODE — Black, Red, Green, Yellow.
- E.) ASSEMBLY — Cabled with ripcord, and jacketed
- F.) JACKET — LS-PVC
- G.) Both insulation and jacket materials are silicone free

COMPLIANCE

- A.) UL 1424 FPLP, NEC article 760
- B.) UL 13 CL3P, NEC article 725
- C.) UL 444 CMP, NEC article 800
- D.) FLAME TEST — NFPA 262
- E.) VOLTAGE — 300V
- F.) TEMPERATURE — 75C
- G.) SUITABLE USE: — Fire protectice signaling circuits, smoke detectors, audio, control, and initiating circuits.
- H.) QA — (UL) Listed / (UL) FPLP Directive (EU) 2015/863 – RoHS 3

FEATURES & OPTIONS: — Available in 1000ft or 500 ft packages, reels, or pull-boxes where practicable. Optional: other colors, jackets with extruded stripes, and composite cables for multiple services, jacketed, or armored as permitted.

Stock #	DESCRIPTION	Cable Type	AWG	#COND	STRANDED/ SOLID	BC/ TD	SHIELD	UL/NEC	SPEC#
Solid BC									
G40005-1	18/2C SOL BC N/S FPLP	FPLP	18	2	SOL	BC	N/S	FPLP	SPEC 70329 G40005-1
G40505-1	18/4C SOL BC N/S FPLP		18	4					SPEC 70330 G40505-1
G50032-1	16/2C SOL BC N/S FPLP		16	2					SPEC 70332 G50032-1
G50370-1	16/4C SOL BC N/S FPLP		16	4					SPEC 70333 G50370-1
G60004-1	14/2C SOL BC N/S FPLP		14	2					SPEC 70334 G60004-1
G60347-1	14/4C SOL BC N/S FPLP		14	4					SPEC 70335 G60347-1
G70009-1	12/2C SOL BC N/S FPLP		12	2					SPEC 70336 G70009-1
G40006-1	18/2C SOL BC SHLD FPLP	FPLP	18	2	SOL	BC	SHLD	FPLP	SPEC 70337 G40006-1
G40504-1	18/4C SOL BC SHLD FPLP		18	4					
G50013-1	16/2C SOL BC SHLD FPLP		16	2					SPEC 70338 G50013-1
G50369-1	16/4C SOL BC SHLD FPLP		16	4					SPEC 70339 G50369-1
G60025-1	14/2C SOL BC SHLD FPLP		14	2					SPEC 70340 G60025-1
G60346-1	14/4C SOL BC SHLD FPLP		14	4					SPEC 70341 G60346-1
G70019-1	12/2C SOL BC SHLD FPLP		12	2					SPEC 70342 G70019-1
Stranded BC									
G40172-1	18/2C STR BC N/S FPLP	FPLP	18	2	STR	BC	N/S	FPLP	
G50359-1	16/2C STR BC N/S FPLP		16	2					
G60210-1	14/2C STR BC N/S FPLP		14	2					
G40178-1	18/2C STR BC SHLD FPLP	FPLP	18	2	STR	BC	SHLD	FPLP	
G50360-1	16/2C STR BC SHLD FPLP		16	2					
G60337-1	14/2C STR BC SHLD FPLP		14	2					

©2021 Southwire Company, LLC. All Rights Reserved.