ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



J2159CRTP HYBRID PLIERS - CRIMPER/PULLER/STRIPPER

KLEIN TOOLS

Catalog Number	J2159CRTP
Manufacturer	KLEIN TOOLS
Description	Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and t
Weight per unit	0.6813 (lbs/each)
Product Category	Tools & Testers

Features

Handle Length	5.01" (12.7 cm)
Jaw Length	2.04" (0 cm)
Jaw Width	1.154" (0 cm)
Material	Chrome-Vanadium Steel
Overall Height	0.75" (2 cm)
Overall Width	2.25" (6 cm)
Jaw Thickness	0.6" (1.5 cm)
Knife Length	0.8" (2 cm)
Media	Yes
Tether Capable	No

Material, Color, and Finish

Handle Color	Gray/Black

Dimensions and Weight

Overall Length	8.98" (22.8 cm)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Descriptions

Description	HYBRID PLIERS - CRIMPER/PULLER/STRIPPER
Features	Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and t
Long Description	Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and t
Product Type	Multi-Purpose Hybrid Pliers
Special Features	High-Leverage Design
Extra Long Description	KLE J2159CRTP Multi-Purpose Hybrid

Manufacturer Information

Brand	Klein Tools
GTIN	00092644701511
Manufacturers Part Number	J2159CRTP
UPC	783523

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Side Cutting

Packaging

Carton	1
Package	6
Weight	10.9 oz (308 g)
Weight Per Each	0.6813 (lbs/each)

Uses, Certifications, and Standards

Application	Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire

Hybrid Pliers with Crimper, Fish Tape Puller and Wire Stripper



Pliers strip, cut, pull, twist, shear and crimp with one tool. These hybrid pliers feature a built-in channel to pull steel fish tape without damaging the wire. With full length, induction hardened knives and a high-leverage design, these hybrid pliers provide more cutting power on hard wire. It easily strips 10-14 AWG solid and 12-16 stranded wire. The wide, knurled head easily grabs and twists wires. Convenient holes for shearing 6-32 and 8-32 bolts plus a crimper for non-insulated connectors, lugs and terminals make this a must-have tool for your bag.

Specifications

Type:	High Leverage Stripping Crimping Shearing Side-Cut Hybrid Plier	**Application:**	Strip (10-14 SLD)(12-16 STR), Bolt Shear #6-32 and #8-32, Crimps Non-Insulated Connectors, Lugs and Terminals, Cuts Screws, Nails and Most Hardened Wire
Special Features:	High-Leverage Design	**Overall Length:**	8.981" (22.8 cm)
Overall Height:	0.75" (2 cm)	**Overall Width:**	2.25" (6 cm)
Material:	Chrome-Vanadium Steel	**Nose Type:**	Square
Jaw Length:	2.04" (0 cm)	**Jaw Width:**	1.154" (0 cm)
Jaw Thickness:	0.6" (1.5 cm)	**Jaw Capacity:**	1.5" (3.8 cm)
Cutting Knives:	Yes	**Knife Length:**	0.8" (2 cm)
Cut Style:	Side Cut	**Strips and Cuts AWG Solid:**	10-14
Strips and Cuts AWG Stranded:	12-16	**Screw Shearing:**	6-32, 8-32
Joint Type:	Solid	**Handle Color:**	Gray/Black
Handle Finish:	Journeyman™ Dual Material	**Handle Length:**	5" (13 cm)
Insulated:	No	**Tether Capable:**	No
Weight:	10.9 oz (308 g)		