ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



LR15 1/2" ALU LR SR5 CONDUIT BODY

CROUSE-HINDS

Catalog Number	LR15
Manufacturer	CROUSE-HINDS
Description	Conduit Outlet Body, Epoxy Powder Painted (Body);Natural (Gasket), 1/2 in Trade Size, Threaded/Set Screw Connection, 4.35 cu.in Capacity, 90 ° Angle, 1/2 in Hub Size, 4.40 in Length, 2.06 in Width, 1.4 in Height, 0.25 lb/EA
Weight per unit	0.2500 (lbs/each)
Product Category	Alum

Features

Form	Series 5
Connection	Threaded / Set Screw
Dimensions	4.4000 IN X 1.4000 IN X 2.0600 IN

Material, Color, and Finish

Color	Gray
Finish	Epoxy Powder Coat

Dimensions and Weight

Height	1.40
Length	4.40
Width	2.06

Descriptions

Description	1/2" ALU LR SR5 CONDUIT BODY
Features	Eaton's Crouse-Hinds Division Series 5 die cast copper-free aluminum conduit bodies, covers and gaskets are available for use with rigid or EMT conduit (with set screw). Conduit bodies are available in trade sizes 1/2" to 4", in the most popular conduit body shapes (C, LB, LL, LR, T) and 1/2" to 2" in TB and X shapes. The Series 5 family is available as components or pre-packaged in various configurations as a SnapPack assembly. In addition, Series 5 is completely interchangeable with other manufacturer
Long Description	Eaton Crouse-Hinds series Condulet Series 5 conduit outlet body, Rigid/IMC, Copper-free aluminum, LR shape, 1/2"
Product Type	1/2 RGD LR Cond Body Al
Extra Long Description	CRH LR15 1/2 RGD LR COND BODY AL

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Eaton
	Eaton Crouse-Hinds
GTIN	00784564140111
UPC	782274

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit outlet body

Packaging

Carton	10
Weight Per Each	0.2500 (lbs/each)

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure	Condulet
Mounting	Conduit
Standard	UL, cUL

Product specifications

Eaton LR15



Catalog Number: LR15

Eaton Crouse-Hinds series Condulet Series 5 conduit outlet body, Rigid/IMC, Copper-free aluminum, LR shape, 1/2"

General specifications

Product Name	**Catalog Number**
Eaton Crouse-Hinds series Condulet Series 5 conduit outlet body	LR15
	UPC
	784564140111
Product Length/Depth	**Product Height**
4.4 in	2.06 in
Product Width	**Product Weight**
1.4 in	0.26 lb

Powering Business Worldwide

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Shape

LR

Conduit type

Rigid/IMC

Trade size

1/2"

Material

Copper-free aluminum

Resources

Brochures

Crouse-Hinds series Series 5 brochure

Catalogs

Crouse-Hinds series Series 5 catalog page

Certification reports

Condulet Series 5 Conduit Outlet Bodies UL certification

Condulet Series 5 Conduit Outlet Bodies Canadian certification

Specifications and datasheets

Eaton Specification Sheet - LR15

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia