



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250T172 JMB MSHD PB R

*Eaton Corp*

Catalog Number	10250T172
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 10250T, 30.5 MM, Heavy-Duty, 65 MM, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Momentary, Jumbo Mushroom , Red Actuator, Chrome Bezel, Anodized Aluminum Actuator
Weight per unit	0.3000 (lbs/each)
Product Category	Push Button Components

### Features

action	Red
actuator	Jumbo mushroom
media	Yes

### Dimensions and Weight

Depth	2.4
Height	3.2
Size	65 mm
Width	2.1

### Descriptions

Description	JMB MSHD PB R
extra long description	ETN 10250T172 JMB MSHD PB R
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 65 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Jumbo mushroom , Red actuator, Chrome bezel, Anodized aluminum actuator
Product Type	JMB MSHD PB R

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113203393
Manufacturers Part Number	10250T172
Model	Pushbutton
UPC	782113203393



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... OILTIGHT OPERATORS.30MM .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 0.3 .....

## Uses, Certifications, and Standards

Application ..... Stationary Machinery and Equipment Outside Factory -  
..... Stationary Machinery and Equipment Outside Factory - Other .....

standard ..... UL Listed,CSA Certified,CE Marked .....