



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T197LGP2A Ind Light FV 120VAC Green Led - Plastic Lens

Eaton Corp

Catalog Number	10250T197LGP2A
Manufacturer	Eaton Corp
Description	Eaton Heavy-Duty Watertight and Oiltight Selector Switch, Heavy-Duty Watertight and Oiltight, Standard Actuator, Led, Full Voltage, Nema 3, 3R, 4, 4X, 12, 13, Green, Plastic, 120 V, 30.5 MM
Weight per unit	0.4000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

Features

dimensions	0.2400 IN X 2.1000 IN X 3.2000 IN
media	Yes

Material, Color, and Finish

Style	30.5 mm
-------	---------

Descriptions

Description	IND LIGHT FV 120VAC GREEN LED - PLASTIC LENS
extra long description	ETN 10250T197LGP2A IND LIGHT FV 120
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton Heavy-duty watertight and oiltight selector switch, Heavy-duty watertight and oiltight, Standard actuator, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Green, Plastic, 120 V, 30.5 mm
Product Type	Ind Light FV 120VAC GN Led-Plastic Lens

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114711156
Manufacturers Part Number	10250T197LGP2A
UPC	782114711156

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Listed, CSA Certified, CE Marked