ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



PS40725WT 4IN 7GA 25FT POLE WLD TENON

RAB LIGHTING

Catalog Number	PS40725WT
Manufacturer	RAB LIGHTING
Description	Poles Ps4 Square Pole 4 Inch 7 Gauge 25 Feet Welded Tenon
Weight per unit	240.0 (lbs/each)
Product Category	Lighting Poles

Material, Color, and Finish

Color	Bronze

Dimensions and Weight

Size	25

Descriptions

Description	4IN 7GA 25FT POLE WLD TENON
Long Description	Poles Ps4 Square Pole 4 Inch 7 Gauge 25 Feet Welded Tenon
Product Type	Pole 4 Inch Square 7 Gauge 25FT Welded
Special Features	25 ft
Extra Long Description	RAB PS4-07-25WT POLE 4 Inch SQUARE

Manufacturer Information

Brand	RAB Lighting Inc
	Rab Lighting
GTIN	00019813181721
Manufacturers Part Number	PS4-07-25WT
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	Poles & Accessories
Type	POLES

Packaging

Carton	1
Weight Per Each	240.0 (lbs/each)

Uses, Certifications, and Standards

Application	Pole
Mounting	CEILING
Standard	7" gauge

PS4-07-25WT



Square steel poles with welded tenon included for use with floodlights. Designed for ground mounting. Poles are stocked nationwide for quick shipment. Protective packaging ensures poles arrive at the job site good as new.

Color: Bronze

Weight: 240.0 lbs

Project:	Type:
Prepared By:	Date:

Technical Specifications

Compliance

CSA Listed:
Suitable for wet locations

Construction

Shaft:
46,000 p.s.i. minimum yield.

Hand Holes:
Reinforced with grounding lug and removable cover

Base Plates:
36,000 p.s.i. minimum yield.

Shipping Protection:
All poles are shipped in individual corrugated cartons to prevent finish damage

Color:
Bronze powder coating

Height:
25 ft

Gauge:
7

Wall Thickness:
3/16"

Shaft Size:
4"

Hand Hole Dimensions:
3" x 5"

Bolt Circle:
8 1/2"

Base Dimension:
8"

Weight:
272 lbs

Anchor Bolt:
Galvanized anchor bolts and galvanized hardware and anchor bolt template. All bolts have a 3" hook.

Anchor Bolt Templates:
WARNING Template must be printed on 11" x 17" sheet for actual size. CHECK SCALE BEFORE USING. Templates shipped with anchor bolts and available online.

Pre-Shipped Anchor Bolts:
Bolts can be pre-shipped upon request for additional freight charge

Max EPA's/Max Weights:
70MPH 9.0 ft/330 lb.
80MPH 5.2 ft/325lb.
90MPH 2.6 ft/325 lb.
100MPH 0.8 ft/310 lb

Other


Terms of Sale:
Pole Terms of Sale is available online.

Buy American Act Compliance:
RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

PS4-07-25WT

Dimensions



Features

- Designed for ground mounting
- Heavy duty TGIC polyester coating
- Reinforced hand holes with grounding lug and removable cover for easy wiring access
- Pole caps, base covers & bolts are sold separately
- Custom manufactured for each application

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice