ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



PS41120D2 4IN 11GA 20' POLE DRILLED

RAB LIGHTING

Catalog Number	PS41120D2
Manufacturer	RAB LIGHTING
Description	Poles Ps4 Square Pole 4 Inch 11 Gauge 20 Feet Drilled
Weight per unit	136.7 (lbs/each)
Product Category	Lighting Poles

Material, Color, and Finish

Color	Bronze

Dimensions and Weight

Size	20

Descriptions

Description	4IN 11GA 20' POLE DRILLED
Long Description	Poles Ps4 Square Pole 4 Inch 11 Gauge 20 Feet Drilled
Product Type	Pole 4 Inch Square 11 Gauge 20FT Drille
Special Features	20 ft
Extra Long Description	RAB PS4-11-20D2 POLE 4 Inch SQUARE

Manufacturer Information

Brand	RAB Lighting Inc
	Rab Lighting
GTIN	00019813013459
Manufacturers Part Number	PS4-11-20D2
UPC	885360

Taxonomies, Classifications, and Categories

Category Description	Poles & Accessories
Type	POLES

Packaging

Carton	1
Weight Per Each	136.7 (lbs/each)

Uses, Certifications, and Standards

Application	Pole
Mounting	CEILING
Standard	11" gauge

PS4-11-20D2



Square steel poles drilled for 2 Area Lights at 180°. Designed for ground mounting. Poles are stocked nationwide for quick shipment. Protective packaging ensures poles arrive at the job site good as new.

Color: Bronze

Weight: 136.7 lbs

Project:	Type:
Prepared By:	Date:

Technical Specifications

Compliance

CSA Listed:
Suitable for wet locations

Construction

Shaft:
46,000 p.s.i. minimum yield.

Hand Holes:
Reinforced with grounding lug and removable cover

Base Plates:
Slotted base plates 36,000 p.s.i.

Shipping Protection:
All poles are shipped in individual corrugated cartons to prevent finish damage

Color:
Bronze powder coating

Height:
20 ft

Weight:
137 lbs

Gauge:
11

Wall Thickness:
1/8"

Shaft Size:
4"

Hand Hole Dimensions:
3" x 5"

Bolt Circle:
8 1/2"

Base Dimension:
8"

Anchor Bolt:
Galvanized anchor bolts and galvanized hardware and anchor bolt template. All bolts have a 3" hook.

Anchor Bolt Templates:
WARNING Template must be printed on 11" x 17" sheet for actual size. CHECK SCALE BEFORE USING. Templates shipped with anchor bolts and available online.

Pre-Shipped Anchor Bolts:
Bolts can be pre-shipped upon request for additional freight charge

Max EPA's/Max Weights:
70MPH 10.7 ft/360 lb.
80MPH 7.0 ft/350 lb.
90MPH 4.3 ft/350 lb.
100MPH 2.5 ft/350 lb.
110MPH 1.1 ft/350 lb.
120MPH 0.1 ft/340lb

Other

Terms of Sale:
Pole Terms of Sale is available online.

Buy American Act Compliance:
RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice

PS4-11-20D2

Dimensions



Features

- Designed for ground mounting
- Heavy duty TGIC polyester coating
- Reinforced hand holes with grounding lug and removable cover for easy wiring access
- Pole caps, base covers & bolts are sold separately
- Custom manufactured for each application

Copyright © 2024 RAB Lighting All Rights Reserved Note: Specifications are subject to change at any time without notice