
ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685




# PVC2 SCH 40 2" 10' PVC CONDUIT

*HERITAGE PLASTICS*

| | |
|---|---|
| Catalog Number | PVC2 |
| Manufacturer | HERITAGE PLASTICS |
| Description | PVC Conduit, Underground or Aboveground Application, Gray Color, 2.021 in Conduit Inner Diameter, 2.375 in Conduit Outer Diameter, 10 ft Length, Made in USA, +90 °C Maximum Operating Temperature, 1400 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex ETL Listed US;UL 651 and NEMA TC2 Standards Met, 2 in Trade Size, 0.154 in Wall Thickness, 0.6989 lb Weight |
| Weight per unit | 0.7300 (lbs/ft) |
| Product Category | PVC Sch 40 Conduit |

## Features

| | |
|---|---|
| Material | PVC |
| Wall Thickness | 0.154 |
| Outside Diameter | 2.375 |

## Dimensions and Weight

| | |
|---|---|
| Diameter | 2" |
| Height | 2.375 |
| Length | 120 |
| Width | 2.375 |

## Descriptions

| | |
|---|---|
| Description | SCH 40 2" 10' PVC CONDUIT |
| Features | Atkore provides the full range of PVC electrical conduit in diameters 1/2" through 8". |
| Long Description | 2 in x 10 ft PVC Schedule 40 Conduit, Belled End |
| Product Type | PVC SCH40 2 X 10 Ul Be |
| Short Description | PVC SCH40 2 x 10 UL BE |
| Extra Long Description | AL-TUBE 8108 PVC SCH40 2 x 10 UL BE |

## Manufacturer Information

| | |
|---|---|
| Brand | ATKORE - ALLIED TUBE & CONDUIT |
| GTIN | 00091111081088 |
| Manufacturers Part Number | A52CA12<br>8108 |
| UPC | 887562 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Conduit & Raceways - Pvc Conduit, Fittings, & Boxes |
| | PVC & ENT |
| | PVC Schedule 40 Conduit |
| Type | PVC - Sch 40/80 |

## Trade Size

| | |
|---|---|
| Trade Size | 2 |

## Availability

| | |
|---|---|
| Minimum Qty | 10 |

## Packaging

| | |
|---|---|
| Carton | 10 |
| Package | 1400 |
| Weight | 0.73 |
| Weight Per Each | 0.7300 (lbs/ft) |


## Uses, Certifications, and Standards

| | |
|---|---|
| Standard | UL651 |

# PVC Rigid Schedule 40 Conduit

Atkore
Allied Tube & Conduit

- Conforms to UL 651 and NEMA TC 2
- Sunlight resistant per UL 651
- Listed for 90° C conductors or cable
- Product manufactured with one integral solvent-weld bell standard per length




| Trade Size | 10-foot Length | | 20-foot Length | | Approximate Weight per 100' (lbs) |
|---|---|---|---|---|---|
| | Part Number | Crate Quantity (ft) | Part Number | Crate Quantity (ft) | |
| ½ | 4005010 | 6,000 | 4005020 | 12,000 | 17 |
| ¾ | 4007510 | 4,400 | 4007520 | 8,800 | 22 |
| 1 | 4010010 | 3,600 | 4010020 | 7,200 | 33 |
| 1¼ | 4012510 | 3,300 | 4012520 | 6,600 | 44 |
| 1½ | 4015010 | 2,250 | 4015020 | 4,500 | 53 |
| 2 | 4020010 | 1,400 | 4020020 | 2,800 | 73 |
| 2½ | 4025010 | 930 | 4025020 | 1,860 | 116 |
| 3 | 4030010 | 880 | 4030020 | 1,760 | 161 |
| 3½ | 4035010 | 630 | 4035020 | 12,60 | 194 |
| 4 | 4040010 | 570 | 4040020 | 1,140 | 229 |
| 5 | 4050010 | 380 | 4050020 | 760 | 311 |
| 6 | 4060010 | 260 | 4060020 | 520 | 403 |
| 8* | 4080010 | 140 | 4080020 | 280 | 607 |

| Trade Size | Dimensions (in) | | | | | |
|---|---|---|---|---|---|---|
| | Average OD | Minimum Average ID | Minimum Wall Thickness, T | Bell Entrance A | Bell Bottom B | Bell Length C |
| ½ | 0.840 | 0.578 | 0.109 | 0.852 | 0.836 | 1.75 |
| ¾ | 1.050 | 0.780 | 0.113 | 1.064 | 1.046 | 2.25 |
| 1 | 1.315 | 1.004 | 0.133 | 1.330 | 1.310 | 2.25 |
| 1¼ | 1.660 | 1.335 | 0.140 | 1.677 | 1.655 | 2.25 |
| 1½ | 1.900 | 1.564 | 0.145 | 1.918 | 1.894 | 2.75 |
| 2 | 2.375 | 2.021 | 0.154 | 2.393 | 2.369 | 4.00 |
| 2½ | 2.875 | 2.414 | 0.203 | 2.890 | 2.868 | 4.00 |
| 3 | 3.500 | 3.008 | 0.216 | 3.515 | 3.492 | 4.00 |
| 3½ | 4.000 | 3.486 | 0.226 | 4.015 | 3.992 | 4.00 |
| 4 | 4.500 | 3.961 | 0.237 | 4.515 | 4.491 | 5.00 |
| 5 | 5.563 | 4.975 | 0.258 | 5.593 | 5.553 | 5.75 |
| 6 | 6.625 | 5.986 | 0.280 | 6.658 | 6.614 | 6.50 |
| 8* | 8.625 | 7.853 | 0.322 | 8.670 | 8.610 | 6.50 |

*UL 651 does not include 8"

Intertek