



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T722BK BK KB 2P MT SS-Xo, Ox-Classi/Div 2

Eaton Corp

Catalog Number	10250T722BK
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 10250T, 30.5 MM, Class I Division 2, Nema 3, 3R, 4, 4X, 12, 13, Nec Class I Division 2, Groups B, C and D, Non-Illuminated, Two-Position, Knob, Black Actuator, 1NO-1NC
Weight per unit	0.5000 (lbs/each)
Product Category	Selector Switch Complete Assem

Features

action	Black
actuator	Knob
Contact Configuration	1 NO-1 NC
media	Yes

Dimensions and Weight

Depth	2.5
Height	4
Width	2.5

Descriptions

Description	BK KB 2P MT SS-XO,OX-CLASSI/DIV 2
extra long description	ETN 10250T722BK BK Kb 2P Mt SS;XO,O
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 10250T, 30.5 mm, Class I Division 2, NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Non-illuminated, Two-position, Knob, Black actuator, 1NO-1NC
Product Type	BK KB 2P MT SS;Xo, Ox;Classi/Div 2

Manufacturer Information

Brand	Eaton
GTIN	00782114505953
Manufacturers Part Number	10250T722BK
Model	Pushbutton
UPC	782114505953



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description OILTIGHT OPERATORS.30MM

Packaging

Carton 1

Weight Per each 0.5

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies and
EOEMs - OtherCommercial / Institutional Buildings / Structures -
Power Distribution and Controls

standard UL 505,CSA Certified,CE Marked