
ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



S60300SW00 3/8" SS316 SQUARE WASHER

CALBRITE

Catalog Number	S60300SW00
Manufacturer	CALBRITE
Description	Stainless Steel 316 Square Washer 3/8"
Weight per unit	0.1700 (lbs/ft)
Product Category	Rigid Conduit Fittings - Steel

Features

Inside Diameter	0.38
Wall Thickness	0.25

Material, Color, and Finish

Color	Polished Silver
Finish	#4 Polished Finish

Dimensions and Weight

Length	1.6
Width	1.6

Descriptions

Description	3/8" SS316 SQUARE WASHER
Features	Stainless steel square washers are designed for connecting stainless steel strut and a variety of stainless strut accessories.
Long Description	Stainless Steel 316 Square Washer 3/8"
Product Type	3/8 SS316 SQ WSH
Short Description	SS_SQ WSHR_316
Extra Long Description	CAL S60300SW00 3/8 SS316 SQ WSH

Manufacturer Information

Brand	CALBRITE
	ATKORE - CALBRITE
GTIN	00847656005542
Manufacturers Part Number	S60300SW00
UPC	892933

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	RIGID

Trade Size

Trade Size	3/8

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	1
Weight	0.16
Weight Per Each	0.1700 (lbs/ft)

Atkore™
Calbrite

STAINLESS STEEL LOCK WASHER


Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard “brite” finish to increase corrosion resistance and aesthetic appearance
- Provides excellent strength and durability to service a variety of installation requirements
- No package quantity required



Applications:

Calbrite’s stainless steel Lock Washers are used with nuts, bolts and screws to provide additional security and prevent loosening.



Part Number	Trade Size (in)	A (ID)	B (OD)	T Thickness (in)	Weight per each (lb)
S60200LW00	½	0.250	0.500	0.072	0.005
S60300LW00	⅜	0.375	0.675	0.105	0.010
S60500LW00	½	0.500	0.860	0.140	0.010
S60600LW00	⅝	0.625	1.050	0.158	0.020

All dimensions are for informational purposes only *Tolerances +/- 5%