ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



S60700MH00 3/4" SS316 MINI HANGER

CALBRITE

Catalog Number	S60700MH00
Manufacturer	CALBRITE
Description	Stainless Steel 316 Mini Hanger 3/4" for Rigid/IMC
Weight per unit	0.0600 (lbs/ft)
Product Category	Rigid Conduit Fittings - Steel

Features

Material	Stainless Steel - 316

Material, Color, and Finish

Color	Silver
Finish	#4 Polished Finish

Dimensions and Weight

Length	2.35
Width	0.87

Descriptions

Description	3/4" SS316 MINI HANGER
Features	Heavy duty type 316 stainless steel conduit hangers are great for securing and mounting Rigid and IMC conduit in corrosive environments.
Long Description	Stainless Steel 316 Mini Hanger 3/4" for Rigid/IMC
Product Type	3/4 SS316 Mni HGR
Short Description	SS_MINI HNGR_316
Extra Long Description	CAL S60700MH00 3/4 SS316 MNI HGR

Manufacturer Information

Brand	CALBRITE
	ATKORE - CALBRITE
GTIN	00847656002961
Manufacturers Part Number	S60700MH00
UPC	892933

Taxonomies, Classifications, and Categories

Category Description	CONDUIT HANGERS/STAND OFF STRAPS
Type	CLAMP

Trade Size

Trade Size	3/4

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	1
Weight	0.084
Weight Per Each	0.0600 (lbs/ft)

Atkore™
Calbrite

STAINLESS STEEL CONDUIT HANGER

Features:

- Manufactured in type 316 stainless steel to meet any stringent sanitary condition
- Polished with standard “brite” finish to increase corrosion resistance and aesthetic appearance
- Designed for use with stainless rigid, stainless IMC
- Type 316 stainless steel nut and bolt (carriage) included
- No package quantity required




Applications:

Heavy duty type 316 stainless steel conduit hangers are great for securing and mounting conduit tubing and cable in corrosive environments.

Certifications:

- UL / CSA 2239 Listed
- UL File # E529659
- CSA C22.2 No.18.4-15
- NFPA 70 Certified



Part Number	Trade Size (in)	A (in)	B (in)	C (in)	Nut & Bolt Size/ Bolt Hole Size (in)	Weight per each (lb)
S60500MH00	½	1.900	⅞	0.850	¼	0.060
S60700MH00	¾	2.350	1 5/16	0.870	¼	0.080
S61000MH00	1	2.630	1⅛	0.870	¼	0.100
S61200MH00	1¼	3.300	1⅜	0.870	¼	0.120
S61500MH00	1½	3.380	1 7/16	1.250	¼	0.200
S62000MH00	2	4.150	2	1.250	¼	0.220
S62500MH00	2½	4.600	2 1/16	1.250	¼	0.260
S63000MH00	3	5.450	2 11/16	1.250	¼	0.300
S64000MH00	4	6.700	3 3/16	1.250	¼	0.360

All dimensions are for informational purposes only *Tolerances +/- 5%