ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



S8420 32W T8 48" 41K 85CRI MED BIPIN

SATCO

Catalog Number	S8420
Manufacturer	SATCO
Description	FLuorescent Lamp, Medium Bi-Pin Base, T8 Bulb Shape, 85, 24000 h Average Life, 4100 k, White, 32 W, 3050 lm Brightness (Lumens), 1 in Diameter, 48 in Length
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Ballast Type	Type A
Material	Glass; Aluminum
Shape	T8
Socket Type	G13
Warranty	Avg. Rated Hour Limited
Wattage	32
Average Life	24000
Beam Angle	360
Lumens	2950
Start Type	Instant Start

Material, Color, and Finish

Color	GLOSS WHITE
Color Rendering Index (Cri)	85+
Color Temperature	4100

Dimensions and Weight

Diameter	1.00
Length	47.78

Descriptions

Description	32W T8 48" 41K 85CRI MED BIPIN
Long Description	Fluorescent T8 Linear Lamp, Designation: F32T8/841/ENV, 32 WTT, T8 Shape, G13 Medium Bi Pin Base, 24000 HR, Lumens: 3050 LM Initial, Lumens: 2900 LM Mean, 4100 DEG K Color Temperature, Cool White 85 CRI, 47-25/32 IN Length, 1 IN Diameter
Product Type	F32T8/841/Env
Special Features	ANSI Base: G13;Color Temp: Cool White;DLC Approved: False;Efficacy: 92.19 LPW;Hg Content: 3.2;Location Rating: Damp;Material: Aluminum / Glass;Operating Temp: Ballast Dependent;T24 Compliant: False;Warranty: 3-Years
Extra Long Description	SATCO S8420 F32T8/841/ENV

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

GTIN	00045923084201
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Fluorescent Linear

Packaging

Carton	30
Weight Per Each	0.4500 (lbs/each)

Uses, Certifications, and Standards

Application	Fluorescent
Operating Temperature	Ballast Dependent
Standard	RoHS Compliant

S8420

F32T8/841/ENV
32 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base

Features
- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8420

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8420	045923084201	32	T8	Medium Bi Pin	G13	F32T8/841/ENV	1.00"

MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2950	2800	24000	4100	Cool White	30

CRI	RoHS Compliant
85	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051