Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



S8421 32W T8 48" 50K 82 CRI MED BIPIN

SATCO

Catalog Number	S8421
Manufacturer	SATCO
Description	Fluorescent T8 Linear Lamp, Designation: F32T8/850/ENV, 32 WTT, T8 Shape, G13 Medium Bi Pin Base, 24000 HR, Lumens: 3000 LM Initial, Lumens: 2850 LM Mean, 5000 DEG K Color Temperature, Natural Light 85 CRI, 47-25/32 IN Length, 1 IN Diameter
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Ballast Type	Type A
Shape	T8
Socket Type	G13
Warranty	Avg. Rated Hour Limited
Wattage	32
Average Life	24000
Beam Angle	360
Lumens	2900
Start Type	Instant Start

Material, Color, and Finish

Color	GLOSS WHITE
Color Rendering Index (Cri)	85+
Color Temperature	5000

Dimensions and Weight

Diameter	1.00
Length	47.78

Descriptions

Description	32W T8 48" 50K 82 CRI MED BIPIN
Long Description	Fluorescent T8 Linear Lamp, Designation: F32T8/850/ENV, 32 WTT, T8 Shape, G13 Medium Bi Pin Base, 24000 HR, Lumens: 3000 LM Initial, Lumens: 2850 LM Mean, 5000 DEG K Color Temperature, Natural Light 85 CRI, 47-25/32 IN Length, 1 IN Diameter
Product Type	F32T8/850/Env
Special Features	ANSI Base: G13;Color Temp: Natural Light;DLC Approved: False;Efficacy: 90.63 LPW;Hg Content: 3.2;Operating Temp: Ballast Dependent;T24 Compliant: False;Warranty: 3-Years
Extra Long Description	SATCO S8421 F32T8/850/ENV

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	HYGRADE
	Satco
GTIN	00045923084218
Manufacturers Part Number	S8421
UPC	885860

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Fluorescent Linear

Packaging

Carton	30
Weight Per Each	0.4500 (lbs/each)

Uses, Certifications, and Standards

Application	Fluorescent
Operating Temperature	Ballast Dependent
Standard	RoHS Compliant

S8421

F32T8/850/ENV
32 watt; T8; Fluorescent; 5000K Natural Light; 85 CRI; Medium Bi Pin base

Features
- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8421

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8421	045923084218	32	T8	Medium Bi Pin	G13	F32T8/850/ENV	1.00"

MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
47.78"	48"	2900	2750	24000	5000	Natural Light	30

CRI	RoHS Compliant
85	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051